

# Enclosure Subpanels

## 1418FS and HN4FS Freestanding Enclosures



### Construction

- Formed from 10-gauge or 12-gauge steel.
- All-double door width panels are 10-gauge steel.
- Width panels are available in full or half height.
- Side-mount panels are available in full height only.
- Includes all mounting hardware and center support where required.
- Half panel can be mounted in the top or bottom half of the enclosure.
- Steel subpanels finished in RAL9003 white powder coat.

### Side Mount Panels

| Part Number            | Price  | Dimensions HxW             | For Use With                                      | Drawing Link        |
|------------------------|--------|----------------------------|---------------------------------------------------|---------------------|
| <a href="#">60FD14</a> | 233.00 | 48.00 x 14.00 [1219 x 356] | 60in (H) 1418xxxx and HN4FS60xxxx                 | <a href="#">PDF</a> |
| <a href="#">72FD9</a>  | 244.00 | 60.00 x 9.00 [1524 x 229]  | 72in (H) 1418xxxx and HN4FS72xxxx                 | <a href="#">PDF</a> |
| <a href="#">72FD14</a> | 264.00 | 60.00 x 14.00 [1524 x 356] | 72in (H) x min. 18in (D) 1418xxxx and HN4FS72xxxx | <a href="#">PDF</a> |
| <a href="#">72FD20</a> | 324.00 | 60.00 x 20.00 [1524 x 508] | 72in (H) x min. 24in (D) 1418xxxx and HN4FS72xxxx | <a href="#">PDF</a> |
| <a href="#">90FD9</a>  | 359.00 | 78.00 x 9.00 [1981 x 229]  | 90in (H) 1418xxxx and HN4FS90xxxx                 | <a href="#">PDF</a> |
| <a href="#">90FD14</a> | 380.00 | 78.00 x 14.00 [1981 x 356] | 90in (H) x min. 18in (D) 1418xxxx and HN4FS90xxxx | <a href="#">PDF</a> |
| <a href="#">90FD20</a> | 394.00 | 78.00 x 20.00 [1981 x 508] | 90in (H) x min. 24in (D) 1418xxxx and HN4FS90xxxx | <a href="#">PDF</a> |
| <a href="#">72FD26</a> | 498.00 | 60.00 x 26.00 [1524 x 660] | 72in (H) x 36in (D) 1418xxx36 and HN4FS72xx36xx   | <a href="#">PDF</a> |
| <a href="#">90FD26</a> | 579.00 | 78.00 x 26.00 [1981 x 660] | 90in (H) x 36in (D) 1418xxx36 and HN4FS90xx36xx   | <a href="#">PDF</a> |

Note: Dimensions in inches [millimeters].

### Single-Door Subpanels

| Painted                | Price  | Galvanized              | Price  | Type       | Dimensions HxW             | For Use With                                 | Drawing Link        |
|------------------------|--------|-------------------------|--------|------------|----------------------------|----------------------------------------------|---------------------|
| <a href="#">60TWFW</a> | 383.00 | <a href="#">60TWFWG</a> | 402.00 | Full Panel | 48.00 x 20.00 [1219 x 508] | 60x24 (HxW) 1418TW18 and HN4FS602418xx       | <a href="#">PDF</a> |
| <a href="#">72WFW</a>  | 428.00 | <a href="#">72WFWG</a>  | 451.00 |            | 60.00 x 20.00 [1524 x 508] | 72x24/72x25 (HxW) 1418xxxx and HN4FS72xxxxxx | <a href="#">PDF</a> |
| <a href="#">90YWFW</a> | 498.00 | <a href="#">90YWFWG</a> | 520.00 |            | 78.00 x 20.00 [1981 x 508] | 90x24 (HxW) 1418YW20 and HN4FS902420xx       | <a href="#">PDF</a> |
| <a href="#">72XFW</a>  | 498.00 | <a href="#">72XFWG</a>  | 520.00 |            | 60.00 x 26.00 [1524 x 660] | 72x30/72x31 (HxW) 1418xxxx and HN4FS72xxxxxx | <a href="#">PDF</a> |
| <a href="#">60TYFW</a> | 491.00 | <a href="#">60TYFWG</a> | 518.00 |            | 48.00 x 32.00 [1219 x 813] | 60x36 (HxW) 1418TY24 and HN4FS603624SS       | <a href="#">PDF</a> |
| <a href="#">72YFW</a>  | 567.00 | <a href="#">72YFWG</a>  | 594.00 |            | 60.00 x 32.00 [1524 x 813] | 72x36/72x37 (HxW) 1418xxxx and HN4FS72xxxxxx | <a href="#">PDF</a> |
| <a href="#">90YFW</a>  | 676.00 | <a href="#">90YFWG</a>  | 709.00 |            | 78.00 x 32.00 [1981 x 813] | 90x36 (HxW) 1418YYxx and HN4FS9036xxxx       | <a href="#">PDF</a> |
| <a href="#">60TWHW</a> | 257.00 | <a href="#">60TWHWG</a> | 268.00 | Half Panel | 24.87 x 20.00 [632 x 508]  | 60x24 (HxW) 1418TW18 and HN4FS602418xx       | <a href="#">PDF</a> |
| <a href="#">72WHW</a>  | 277.00 | <a href="#">72WHWG</a>  | 291.00 |            | 30.87 x 20.00 [784 x 508]  | 72x24/72x25 (HxW) 1418xxxx and HN4FS72xxxxxx | <a href="#">PDF</a> |
| <a href="#">90YWHW</a> | 312.00 | <a href="#">90YWHWG</a> | 327.00 |            | 39.87 x 20.00 [1013 x 508] | 90x24 (HxW) 1418YW20 and HN4FS902420xx       | <a href="#">PDF</a> |
| <a href="#">72XHW</a>  | 312.00 | <a href="#">72XHWG</a>  | 327.00 |            | 30.87 x 26.00 [784 x 660]  | 72x30/72x31 (HxW) 1418xxxx and HN4FS72xxxxxx | <a href="#">PDF</a> |
| <a href="#">60TYHW</a> | 312.00 | <a href="#">60TYHWG</a> | 327.00 |            | 24.87 x 32.00 [632 x 813]  | 60x36 (HxW) 1418TY24 and HN4FS603624SS       | <a href="#">PDF</a> |
| <a href="#">72YHW</a>  | 348.00 | <a href="#">72YHWG</a>  | 365.00 |            | 30.87 x 32.00 [784 x 813]  | 72x36/72x37 (HxW) 1418xxxx and HN4FS72xxxxxx | <a href="#">PDF</a> |
| <a href="#">90YHW</a>  | 402.00 | <a href="#">90YHWG</a>  | 423.00 |            | 39.87 x 32.00 [1013 x 813] | 90x36 (HxW) 1418YYxx and HN4FS9036xxxx       | <a href="#">PDF</a> |

Note: Dimensions in inches [millimeters].

# Enclosure Subpanels

## 1418FS and HN4FS Freestanding Enclosures



| Two-Door Subpanels                        |          |                         |          |             |                             |                      |                     |
|-------------------------------------------|----------|-------------------------|----------|-------------|-----------------------------|----------------------|---------------------|
| Painted                                   | Price    | Galvanized              | Price    | Type        | Dimensions HxW              | For Use With         | Drawing Link        |
| <a href="#">60AWFW</a>                    | 787.00   | <a href="#">60AWFWG</a> | 828.00   | Full Height | 48.00 x 44.00 [1219 x 1118] | 60x48 (HxW) 1418AW18 | <a href="#">PDF</a> |
| <a href="#">72ZWFW</a>                    | 892.00   | <a href="#">72ZWFWG</a> | 935.00   |             | 60.00 x 44.00 [1524 x 1118] | 72x48 (HxW) 1418ZWxx | <a href="#">PDF</a> |
| <a href="#">72ZXFW</a>                    | 1,035.00 | <a href="#">72ZXFWG</a> | 1,087.00 |             | 60.00 x 56.00 [1524 x 1422] | 72x60 (HxW) 1418ZXxx | <a href="#">PDF</a> |
| <a href="#">72ZYFW</a>                    | 1,175.00 | <a href="#">72ZYFWG</a> | 1,293.00 |             | 60.00 x 68.00 [1524 x 1727] | 72x72 (HxW) 1418ZYxx | <a href="#">PDF</a> |
| <a href="#">90BFWF</a>                    | 1,048.00 | <a href="#">90BFWFG</a> | 1,100.00 |             | 78.00 x 44.00 [1981 x 1118] | 90x48 (HxW) 1418BW20 | <a href="#">PDF</a> |
| <a href="#">90BYFW</a>                    | 1,417.00 | <a href="#">90BYFWG</a> | 1,560.00 |             | 78.00 x 68.00 [1981 x 1727] | 90x72 (HxW) 1418BYxx | <a href="#">PDF</a> |
| <a href="#">60AHHW</a>                    | 491.00   | <a href="#">60AHHWG</a> | 554.00   | Half Height | 24.87 x 44.00 [632 x 1118]  | 60x48 (HxW) 1418AW18 | <a href="#">PDF</a> |
| <a href="#">72ZHHW</a>                    | 573.00   | <a href="#">72ZHHWG</a> | 598.00   |             | 30.87 x 44.00 [784 x 1118]  | 72x48 (HxW) 1418ZWxx | <a href="#">PDF</a> |
| <a href="#">72ZXHW</a>                    | 642.00   | <a href="#">72ZXHWG</a> | 674.00   |             | 30.87 x 56.00 [784 x 1422]  | 72x60 (HxW) 1418ZXxx | <a href="#">PDF</a> |
| <a href="#">72ZYHW</a>                    | 716.00   | <a href="#">72ZYHWG</a> | 753.00   |             | 30.87 x 68.00 [784 x 1727]  | 72x72 (HxW) 1418ZYxx | <a href="#">PDF</a> |
| <a href="#">90BHHW</a>                    | 649.00   | <a href="#">90BHHWG</a> | 681.00   |             | 39.87 x 44.00 [1013 x 1118] | 90x48 (HxW) 1418BW20 | <a href="#">PDF</a> |
| <a href="#">90BYHW</a>                    | 834.00   | <a href="#">90BYHWG</a> | 878.00   |             | 39.87 x 68.00 [1013 x 1727] | 90x72 (HxW) 1418BYxx | <a href="#">PDF</a> |
| Note: Dimensions in inches [millimeters]. |          |                         |          |             |                             |                      |                     |

# Freestanding Enclosure 19 in Swing-Out Frame



## 1418FS and HN4FS Enclosures



### Construction

- Formed from 10-gauge steel, frames are drilled and tapped to EIA requirements for mounting standard 19 in [483 mm] rack accessories.
- Designed for installation in 72 in [1829 mm] and 90 in [2286 mm] high enclosures. The swing frame pivots on 0.5 in [12.7 mm] pins within the enclosure for easy access to the rear of rack mounted equipment.
- The frame positions at any depth within the enclosure and is fastened in the closed position with 1/4-turn fasteners.
- Swing frames may be mounted in 30 in [762 mm] and 36 in [914 mm] wide enclosures, or in 60 in [1524 mm] and 72 in [1829 mm] wide enclosures with an optional center panel support.
- One or two frames may be mounted in 30 in [762 mm] and 36 in [914 mm] wide enclosures with dual access, and 1, 2, 3 or 4 frames may be mounted in 60 in [1524 mm] and 72 in [1829 mm] wide dual access enclosures.
- Finished in black powder coat.

| Freestanding Enclosure 19 in [483 mm] Swing-Out Frame |          |              |            |                     |
|-------------------------------------------------------|----------|--------------|------------|---------------------|
| Part Number                                           | Price    | For Use With | Rack Units | Drawing Link        |
| <a href="#">1418SFYY</a>                              | 1,042.00 | 90x36in      | 44         | <a href="#">PDF</a> |
| <a href="#">1418SFY</a>                               | 988.00   | 72x36in      | 33         | <a href="#">PDF</a> |
| <a href="#">1418SFX</a>                               | 916.00   | 72x30in      | 33         | <a href="#">PDF</a> |

### Dimensions

