

Enclosure Subpanels

1418FS and HN4FS Freestanding Enclosures



Construction

- Formed from 10-gauge or 12-gauge steel.
- All-double door width panels are 10-gauge steel.
- Width panels are available in full or half height.
- Side-mount panels are available in full height only.
- Includes all mounting hardware and center support where required.
- Half panel can be mounted in the top or bottom half of the enclosure.
- Steel subpanels finished in RAL9003 white powder coat.

Side Mount Panels

Part Number	Price	Dimensions HxW	For Use With	Drawing Link
60FD14	\$233.00	48.00 x 14.00 [1219 x 356]	60in (H) 1418xxxx and HN4FS60xxxx	PDF
72FD9	\$244.00	60.00 x 9.00 [1524 x 229]	72in (H) 1418xxxx and HN4FS72xxxx	PDF
72FD14	\$264.00	60.00 x 14.00 [1524 x 356]	72in (H) x min. 18in (D) 1418xxxx and HN4FS72xxxx	PDF
72FD20	\$324.00	60.00 x 20.00 [1524 x 508]	72in (H) x min. 24in (D) 1418xxxx and HN4FS72xxxx	PDF
90FD9	\$359.00	78.00 x 9.00 [1981 x 229]	90in (H) 1418xxxx and HN4FS90xxxx	PDF
90FD14	\$380.00	78.00 x 14.00 [1981 x 356]	90in (H) x min. 18in (D) 1418xxxx and HN4FS90xxxx	PDF
90FD20	\$394.00	78.00 x 20.00 [1981 x 508]	90in (H) x min. 24in (D) 1418xxxx and HN4FS90xxxx	PDF
72FD26	\$498.00	60.00 x 26.00 [1524 x 660]	72in (H) x 36in (D) 1418xxx36 and HN4FS72xx36xx	PDF
90FD26	\$579.00	78.00 x 26.00 [1981 x 660]	90in (H) x 36in (D) 1418xxx36 and HN4FS90xx36xx	PDF

Note: Dimensions in inches [millimeters].

Single-Door Subpanels

Painted	Price	Galvanized	Price	Type	Dimensions HxW	For Use With	Drawing Link
60TWFW	\$383.00	60TWFWG	\$402.00	Full Panel	48.00 x 20.00 [1219 x 508]	60x24 (HxW) 1418TW18 and HN4FS602418xx	PDF
72WFW	\$428.00	72WFWG	\$451.00		60.00 x 20.00 [1524 x 508]	72x24/72x25 (HxW) 1418xxxx and HN4FS72xxxxxx	PDF
90YWFW	\$498.00	90YWFWG	\$520.00		78.00 x 20.00 [1981 x 508]	90x24 (HxW) 1418YW20 and HN4FS902420xx	PDF
72XFW	\$498.00	72XFWG	\$520.00		60.00 x 26.00 [1524 x 660]	72x30/72x31 (HxW) 1418xxxx and HN4FS72xxxxxx	PDF
60TYFW	\$491.00	60TYFWG	\$518.00		48.00 x 32.00 [1219 x 813]	60x36 (HxW) 1418TY24 and HN4FS603624SS	PDF
72YFW	\$567.00	72YFWG	\$594.00		60.00 x 32.00 [1524 x 813]	72x36/72x37 (HxW) 1418xxxx and HN4FS72xxxxxx	PDF
90YFW	\$676.00	90YFWG	\$709.00		78.00 x 32.00 [1981 x 813]	90x36 (HxW) 1418YYxx and HN4FS9036xxxx	PDF
60TWHW	\$257.00	60TWHWG	\$268.00	Half Panel	24.87 x 20.00 [632 x 508]	60x24 (HxW) 1418TW18 and HN4FS602418xx	PDF
72WHW	\$277.00	72WHWG	\$291.00		30.87 x 20.00 [784 x 508]	72x24/72x25 (HxW) 1418xxxx and HN4FS72xxxxxx	PDF
90YWHW	\$312.00	90YWHWG	\$327.00		39.87 x 20.00 [1013 x 508]	90x24 (HxW) 1418YW20 and HN4FS902420xx	PDF
72XHW	\$312.00	72XHWG	\$327.00		30.87 x 26.00 [784 x 660]	72x30/72x31 (HxW) 1418xxxx and HN4FS72xxxxxx	PDF
60TYHW	\$312.00	60TYHWG	\$327.00		24.87 x 32.00 [632 x 813]	60x36 (HxW) 1418TY24 and HN4FS603624SS	PDF
72YHW	\$348.00	72YHWG	\$365.00		30.87 x 32.00 [784 x 813]	72x36/72x37 (HxW) 1418xxxx and HN4FS72xxxxxx	PDF
90YHW	\$402.00	90YHWG	\$423.00		39.87 x 32.00 [1013 x 813]	90x36 (HxW) 1418YYxx and HN4FS9036xxxx	PDF

Note: Dimensions in inches [millimeters].

Enclosure Subpanels

1418FS and HN4FS Freestanding Enclosures



Two-Door Subpanels							
Painted	Price	Galvanized	Price	Type	Dimensions HxW	For Use With	Drawing Link
<u>60AWFW</u>	\$787.00	<u>60AWFWG</u>	\$828.00	Full Height	48.00 x 44.00 [1219 x 1118]	60x48 (HxW) 1418AW18	<u>PDF</u>
<u>72ZWFW</u>	\$892.00	<u>72ZWFWG</u>	\$935.00		60.00 x 44.00 [1524 x 1118]	72x48 (HxW) 1418ZWxx	<u>PDF</u>
<u>72ZXFW</u>	\$1,035.00	<u>72ZXFWG</u>	\$1,087.00		60.00 x 56.00 [1524 x 1422]	72x60 (HxW) 1418ZXxx	<u>PDF</u>
<u>72ZYFW</u>	\$1,175.00	<u>72ZYFWG</u>	\$1,293.00		60.00 x 68.00 [1524 x 1727]	72x72 (HxW) 1418ZYxx	<u>PDF</u>
<u>90BFWF</u>	\$1,048.00	<u>90BFWFG</u>	\$1,100.00		78.00 x 44.00 [1981 x 1118]	90x48 (HxW) 1418BW20	<u>PDF</u>
<u>90BYFW</u>	\$1,417.00	<u>90BYFWG</u>	\$1,560.00		78.00 x 68.00 [1981 x 1727]	90x72 (HxW) 1418BYxx	<u>PDF</u>
<u>60AHHW</u>	\$491.00	<u>60AHHWG</u>	\$554.00	Half Height	24.87 x 44.00 [632 x 1118]	60x48 (HxW) 1418AW18	<u>PDF</u>
<u>72ZWHW</u>	\$573.00	<u>72ZWHWG</u>	\$598.00		30.87 x 44.00 [784 x 1118]	72x48 (HxW) 1418ZWxx	<u>PDF</u>
<u>72ZXHW</u>	\$642.00	<u>72ZXHWG</u>	\$674.00		30.87 x 56.00 [784 x 1422]	72x60 (HxW) 1418ZXxx	<u>PDF</u>
<u>72ZYHW</u>	\$716.00	<u>72ZYHWG</u>	\$753.00		30.87 x 68.00 [784 x 1727]	72x72 (HxW) 1418ZYxx	<u>PDF</u>
<u>90BWHW</u>	\$649.00	<u>90BWHWG</u>	\$681.00		39.87 x 44.00 [1013 x 1118]	90x48 (HxW) 1418BW20	<u>PDF</u>
<u>90BYHW</u>	\$834.00	<u>90BYHWG</u>	\$878.00		39.87 x 68.00 [1013 x 1727]	90x72 (HxW) 1418BYxx	<u>PDF</u>
Note: Dimensions in inches [millimeters].							

Freestanding Enclosure 19 in Swing-Out Frame



1418FS and HN4FS Enclosures



Construction

- Formed from 10-gauge steel, frames are drilled and tapped to EIA requirements for mounting standard 19 in [483 mm] rack accessories.
- Designed for installation in 72 in [1829 mm] and 90 in [2286 mm] high enclosures. The swing frame pivots on 0.5 in [12.7 mm] pins within the enclosure for easy access to the rear of rack mounted equipment.
- The frame positions at any depth within the enclosure and is fastened in the closed position with 1/4-turn fasteners.
- Swing frames may be mounted in 30 in [762 mm] and 36 in [914 mm] wide enclosures, or in 60 in [1524 mm] and 72 in [1829 mm] wide enclosures with an optional center panel support.
- One or two frames may be mounted in 30 in [762 mm] and 36 in [914 mm] wide enclosures with dual access, and 1, 2, 3 or 4 frames may be mounted in 60 in [1524 mm] and 72 in [1829 mm] wide dual access enclosures.
- Finished in black powder coat.

Freestanding Enclosure 19 in [483 mm] Swing-Out Frame				
Part Number	Price	For Use With	Rack Units	Drawing Link
1418SFYY	\$1,042.00	90x36in	44	PDF
1418SFY	\$988.00	72x36in	33	PDF
1418SFX	\$916.00	72x30in	33	PDF

Dimensions

