

# Non-Insulated Connector Crimping Tool

The DN-CT-ID1 series crimping tools are for non-insulated connectors, available up to AWG4, side feeded, Indent-Crimp. For connectors to DIN 46234.


- High-strength, through hardened alloy steel construction
- Unique mechanism significantly reduces hand force requirement over competing crimping tools
- Versatile and easy to customize for right hand or left hand users.
- Non-slip pad holds tool in place when leveraging on a work surface
- Full cycle crimp mechanism to ensure consistent, reliable crimp
- Ratchet release mechanism to clear miscrimps and obstructions
- Precision eccentric adjustment for consistent performance and ability to calibrate
- Hole in handle allows attachment of safety strap
- Each tool has a unique serial number for traceability




**DN-CT-ID1**

Non-Insulated Connector Crimping Tool		
Part Number	Description	Price
<b>DN-CT-ID1</b>	AutomationDirect wire crimping tool, indent profile, 8-4 AWG capacity, compatible with non-insulated connectors.	\$233.00

Non-Insulated Connector Crimping Tool Specifications	
<b>Length</b>	10.08 in [256mm]
<b>Width</b>	0.87 in [22mm]
<b>Height</b>	3.15 in [80mm]
<b>Weight</b>	1.23 lb [559g]
<b>Capacity</b>	10 - 25 mm <sup>2</sup> / AWG 8-4
<b>Crimp Profile</b>	Indent
<b>Crimp Dimensions</b>	AWG 8/AWG 6/AWG 4 [10 mm <sup>2</sup> /16 mm <sup>2</sup> /25 mm <sup>2</sup> ]
<b>Connector</b>	Non-insulated connectors
<b>Lifespan</b>	Tested to 50,000 cycles



**Die Profile**



**Crimp Profile**

**DN-CT-ID1**