

## iX7NH System Non-Brake Motor Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
<a href="#">APCS-PN03LSX-AD</a>	\$48.00	N	3m [9.8 ft]		<a href="#">PDF</a>	FBL/FCL series motors
<a href="#">APCS-PN05LSX-AD</a>	\$53.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10LSX-AD</a>	\$65.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20LSX-AD</a>	\$94.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03LSX-AD</a>	\$55.00	Y	3m [9.8 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PF05LSX-AD</a>	\$65.00		5m [16.4 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PF10LSX-AD</a>	\$93.00		10m [32.8 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PF20LSX-AD</a>	\$146.00		20m [65.6 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PN03HSX1-AD</a>	\$48.00	N	3m [9.8 ft]		<a href="#">PDF</a>	APM-FE15A series motors without brake
<a href="#">APCS-PN05HSX1-AD</a>	\$55.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10HSX1-AD</a>	\$72.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20HSX1-AD</a>	\$108.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03HSX1-AD</a>	\$56.00	Y	3m [9.8 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PF05HSX1-AD</a>	\$68.00		5m [16.4 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PF10HSX1-AD</a>	\$100.00		10m [32.8 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PF20HSX1-AD</a>	\$158.00		20m [65.6 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PN03HSX-AD</a>	\$44.00	N	3m [9.8 ft]		<a href="#">PDF</a>	APM-FE16D and APM-FE22D series motors without brake
<a href="#">APCS-PN05HSX-AD</a>	\$53.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10HSX-AD</a>	\$74.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20HSX-AD</a>	\$116.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03HSX-AD</a>	\$57.00	Y	3m [9.8 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PF05HSX-AD</a>	\$74.00		5m [16.4 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PF10HSX-AD</a>	\$116.00		10m [32.8 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PF20HSX-AD</a>	\$200.00		20m [65.6 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PN03ISX-AD</a>	\$49.00	N	3m [9.8 ft]		<a href="#">PDF</a>	APM-FF35D motors without brake
<a href="#">APCS-PN05ISX-AD</a>	\$57.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10ISX-AD</a>	\$79.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20ISX-AD</a>	\$120.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03ISX-AD</a>	\$63.00	Y	3m [9.8 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PF05ISX-AD</a>	\$80.00		5m [16.4 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PF10ISX-AD</a>	\$124.00		10m [32.8 ft]	<a href="#">PDF</a>		
<a href="#">APCS-PF20ISX-AD</a>	\$213.00		20m [65.6 ft]	<a href="#">PDF</a>		

NOTE: These parts available for sale to North American locations only



APCS-PxxLSX series power cable



APCS-PxxHSX1 series power cable



APCS-PxxHSX series power cable



# iX7NH Series Accessories

## Accessories, continued

### iX7NH System Brake Motor Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
Note: For FBL/FCL 100W-1kW motors with brake, use the power cables on the previous page AND separate brake cable APCS-BxxxQS-AD from page tMNC-282. This is for FBL/FCL motors only. FE and FF motors have brake wiring incorporated into the power cable (below).						
<a href="#">APCS-PN03NBX1-AD</a>	\$58.00	N	3m [9.8 ft]		<a href="#">PDF</a>	APM-FE15A series motors with brakes
<a href="#">APCS-PN05NBX1-AD</a>	\$68.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10NBX1-AD</a>	\$94.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20NBX1-AD</a>	\$144.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03NBX1-AD</a>	\$72.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF05NBX1-AD</a>	\$91.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10NBX1-AD</a>	\$139.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20NBX1-AD</a>	\$237.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN03NBX-AD</a>	\$51.00	N	3m [9.8 ft]		<a href="#">PDF</a>	APM-FE16D and APM-FE22D series motors with brakes
<a href="#">APCS-PN05NBX-AD</a>	\$61.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10NBX-AD</a>	\$86.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20NBX-AD</a>	\$137.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03NBX-AD</a>	\$67.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF05NBX-AD</a>	\$89.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10NBX-AD</a>	\$137.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20NBX-AD</a>	\$243.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN03PBX-AD</a>	\$70.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	APM-FF35D series motors with brakes
<a href="#">APCS-PN05PBX-AD</a>	\$82.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10PBX-AD</a>	\$117.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20PBX-AD</a>	\$184.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03PBX-AD</a>	\$89.00	N	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF05PBX-AD</a>	\$117.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10PBX-AD</a>	\$182.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20PBX-AD</a>	\$315.00		20m [65.6 ft]		<a href="#">PDF</a>	



**APCS-PxxNBX1 series power cable**



**APCS-PxxNBX series power cable**



**APCS-PxxPBX series power cable**