

## iX7NH System Non-Brake Motor Power Cables

| Part Number                      | Price    | Flex Rated | Length        | Gauge | Drawing             | Compatible Motors                                   |
|----------------------------------|----------|------------|---------------|-------|---------------------|---|
| <a href="#">APCS-PN03LSX-AD</a>  | \$49.50  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | FBL/FCL series motors                               |
| <a href="#">APCS-PN05LSX-AD</a>  | \$55.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN10LSX-AD</a>  | \$67.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN20LSX-AD</a>  | \$97.00  |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF03LSX-AD</a>  | \$57.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF05LSX-AD</a>  | \$67.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF10LSX-AD</a>  | \$96.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF20LSX-AD</a>  | \$150.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN03HSX1-AD</a> | \$49.50  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | APM-FE15A series motors without brake               |
| <a href="#">APCS-PN05HSX1-AD</a> | \$57.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN10HSX1-AD</a> | \$74.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN20HSX1-AD</a> | \$111.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF03HSX1-AD</a> | \$58.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF05HSX1-AD</a> | \$70.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF10HSX1-AD</a> | \$103.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF20HSX1-AD</a> | \$163.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN03HSX-AD</a>  | \$45.50  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | APM-FE16D and APM-FE22D series motors without brake |
| <a href="#">APCS-PN05HSX-AD</a>  | \$55.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN10HSX-AD</a>  | \$76.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN20HSX-AD</a>  | \$119.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF03HSX-AD</a>  | \$59.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF05HSX-AD</a>  | \$76.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF10HSX-AD</a>  | \$119.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF20HSX-AD</a>  | \$206.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN03ISX-AD</a>  | \$50.00  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | APM-FF35D motors without brake                      |
| <a href="#">APCS-PN05ISX-AD</a>  | \$59.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN10ISX-AD</a>  | \$81.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN20ISX-AD</a>  | \$124.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF03ISX-AD</a>  | \$65.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF05ISX-AD</a>  | \$82.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF10ISX-AD</a>  | \$128.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF20ISX-AD</a>  | \$219.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |

NOTE: These parts available for sale to North American locations only



APCS-PxxLSX series power cable



APCS-PxxHSX1 series power cable



APCS-PxxHSX series power cable



# iX7NH Series Accessories

## Accessories, continued

### iX7NH System Brake Motor Power Cables

| Part Number   | Price    | Flex Rated | Length        | Gauge | Drawing             | Compatible Motors                                 |
|---|----------|------------|---------------|-------|---------------------|---|
| Note: For FBL/FCL 100W–1kW motors with brake, use the power cables on the previous page AND separate brake cable APCS-BxxxQS-AD from page tSRV-82. This is for FBL/FCL motors only. FE and FF motors have brake wiring incorporated into the power cable (below). |          |            |               |       |                     |   |
| <a href="#">APCS-PN03NBX1-AD</a>  | \$60.00  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | APM-FE15A series motors with brakes               |
| <a href="#">APCS-PN05NBX1-AD</a>  | \$70.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN10NBX1-AD</a>  | \$97.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN20NBX1-AD</a>  | \$148.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF03NBX1-AD</a>  | \$74.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF05NBX1-AD</a>  | \$94.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF10NBX1-AD</a>  | \$143.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF20NBX1-AD</a>  | \$244.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN03NBX-AD</a>   | \$53.00  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | APM-FE16D and APM-FE22D series motors with brakes |
| <a href="#">APCS-PN05NBX-AD</a>   | \$63.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN10NBX-AD</a>   | \$89.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN20NBX-AD</a>   | \$141.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF03NBX-AD</a>   | \$69.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF05NBX-AD</a>   | \$92.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF10NBX-AD</a>   | \$141.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF20NBX-AD</a>   | \$250.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN03PBX-AD</a>   | \$72.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | APM-FF35D series motors with brakes               |
| <a href="#">APCS-PN05PBX-AD</a>   | \$84.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN10PBX-AD</a>   | \$121.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PN20PBX-AD</a>   | \$190.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF03PBX-AD</a>   | \$92.00  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF05PBX-AD</a>   | \$121.00 |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF10PBX-AD</a>   | \$187.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |   |
| <a href="#">APCS-PF20PBX-AD</a>   | \$324.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |   |



**APCS-PxxNBX1 series power cable**



**APCS-PxxNBX series power cable**



**APCS-PxxPBX series power cable**