

Accessories, *continued*

NOTE: These parts available for sale to North American locations only

L7C/L7P/iX7NH System Motor Brake Power Cables

| Part Number | Price | Flex Rated | Length | Gauge | Drawing | Compatible Motors |
|---------------------------------------|----------|------------|---------------|-------|----------------------------|--|
| <u>APCS-BN03QS-AD</u> | \$52.00 | N | 3m [9.8 ft] | 18AWG | <u>PDF</u> | APMC FBL/FCL brake motors (100W – 1kW) |
| <u>APCS-BN05QS-AD</u> | \$55.00 | | 5m [16.4 ft] | | <u>PDF</u> | |
| <u>APCS-BN10QS-AD</u> | \$61.00 | | 10m [32.8 ft] | | <u>PDF</u> | |
| <u>APCS-BN20QS-AD</u> | \$74.00 | | 20m [65.6 ft] | | <u>PDF</u> | |
| <u>APCS-BF03QS-AD</u> | \$58.00 | Y | 3m [9.8 ft] | | <u>PDF</u> | |
| <u>APCS-BF05QS-AD</u> | \$63.00 | | 5m [16.4 ft] | | <u>PDF</u> | |
| <u>APCS-BF10QS-AD</u> | \$79.00 | | 10m [32.8 ft] | | <u>PDF</u> | |
| <u>APCS-BF20QS-AD</u> | \$108.00 | | 20m [65.6 ft] | | <u>PDF</u> | |



APCS-BN series brake cable

LS ELECTRIC L7C Series AC Servo Systems

Accessories, *continued*

NOTE: These parts available for sale to North American locations only

L7C System Motor Power Cables

| Part Number | Price | Flex Rated | Length | Gauge | Drawing | Compatible Motors |
|---------------------------------|----------|------------|---------------|-------|---------------------|---|
| APCS-PN03LSC-AD | \$40.00 | N | 3m [9.8 ft] | 18AWG | PDF | APMC FBL/FCL motors (100W – 1kW) used with L7C drives |
| APCS-PN05LSC-AD | \$48.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PN10LSC-AD | \$62.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PN20LSC-AD | \$85.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PF03LSC-AD | \$52.00 | Y | 3m [9.8 ft] | | PDF | |
| APCS-PF05LSC-AD | \$68.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PF10LSC-AD | \$96.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PF20LSC-AD | \$151.00 | | 20m [65.6 ft] | | PDF | |



APCS-PN series motor cable

L7P System Non-Brake Motor Power Cables

| Part Number | Price | Flex Rated | Length | Gauge | Drawing | Compatible Motors |
|---------------------------------|----------|------------|---------------|-------|---------------------|--|
| APCS-PN03LS-AD | \$42.00 | N | 3m [9.8 ft] | 18AWG | PDF | FBL/FCL series motors |
| APCS-PN05LS-AD | \$46.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PN10LS-AD | \$57.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PN20LS-AD | \$80.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PF03LS-AD | \$53.00 | Y | 3m [9.8 ft] | | PDF | |
| APCS-PF05LS-AD | \$62.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PF10LS-AD | \$90.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PF20LS-AD | \$145.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PN03HS-AD | \$45.00 | N | 3m [9.8 ft] | 14AWG | PDF | APM-FE series motors without brake |
| APCS-PN05HS-AD | \$54.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PN10HS-AD | \$76.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PN20HS-AD | \$119.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PF03HS-AD | \$62.00 | Y | 3m [9.8 ft] | | PDF | |
| APCS-PF05HS-AD | \$80.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PF10HS-AD | \$127.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PF20HS-AD | \$222.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PN03IS-AD | \$61.00 | N | 3m [9.8 ft] | 14AWG | PDF | 230VAC APM-FF35D and 460VAC APM-FFP35D motors without brakes |
| APCS-PN05IS-AD | \$77.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PN10IS-AD | \$119.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PN20IS-AD | \$199.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PF03IS-AD | \$77.00 | Y | 3m [9.8 ft] | | PDF | |
| APCS-PF05IS-AD | \$103.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PF10IS-AD | \$169.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PF20IS-AD | \$305.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PN03JS-AD | \$68.00 | N | 3m [9.8 ft] | 10AWG | PDF | 230VAC APM-FF55D motors without brake |
| APCS-PN05JS-AD | \$90.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PN10JS-AD | \$139.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PN20JS-AD | \$258.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PF03JS-AD | \$97.00 | Y | 3m [9.8 ft] | | PDF | |
| APCS-PF05JS-AD | \$137.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PF10JS-AD | \$237.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PF20JS-AD | \$440.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PF03JS1-AD | \$82.00 | Y | 3m [9.8 ft] | 12AWG | PDF | 460VAC APM-FFP55D and APM-FFP75D motors without brakes |
| APCS-PF05JS1-AD | \$111.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PF10JS1-AD | \$186.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PF20JS1-AD | \$339.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PN03JS2-AD | \$117.00 | N | 3m [9.8 ft] | 8AWG | PDF | 230VAC APM-FF75D motors without brake |
| APCS-PN05JS2-AD | \$163.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PN10JS2-AD | \$276.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PN20JS2-AD | \$499.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PF03JS2-AD | \$169.00 | Y | 3m [9.8 ft] | | PDF | |
| APCS-PF05JS2-AD | \$247.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PF10JS2-AD | \$439.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PF20JS2-AD | \$824.00 | | 20m [65.6 ft] | | PDF | |

NOTE: These parts available for sale to North American locations only



APCS-PxxLS series power cable



APCS-PxxHS series power cable



APCS-PxxIS series power cable



APCS-PxxJS series power cable

Accessories, continued

L7P System Brake Motor Power Cables

| Part Number | Price | Flex Rated | Length | Gauge | Drawing | Compatible Motors |
|---|----------|------------|---------------|-------|---------------------|---|
| Note: For FBL/FCL 100W-1kW motors with brake, use the power cables on page tMNC-234 (APCS-PxxxLS-AD) AND separate brake cable APCS-BxxxQS-AD from page tMNC-232. This is for FBL/FCL motors only. FE and FF motors have brake wiring incorporated into the power cable (below). | | | | | | |
| APCS-PN03NB-AD | \$49.00 | N | 3m [9.8 ft] | 14AWG | PDF | 230VAC and 460 VAC APM-FE series motors with brakes |
| APCS-PN05NB-AD | \$58.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PN10NB-AD | \$84.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PN20NB-AD | \$137.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PF03NB-AD | \$71.00 | Y | 3m [9.8 ft] | | PDF | |
| APCS-PF05NB-AD | \$95.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PF10NB-AD | \$153.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PF20NB-AD | \$274.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PN03PB-AD | \$69.00 | N | 3m [9.8 ft] | 14AWG | PDF | 230VAC APM-FF35D and 460VAC APM-FFP35D motors with brakes |
| APCS-PN05PB-AD | \$87.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PN10PB-AD | \$133.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PN20PB-AD | \$229.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PF03PB-AD | \$88.00 | Y | 3m [9.8 ft] | | PDF | |
| APCS-PF05PB-AD | \$120.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PF10PB-AD | \$198.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PF20PB-AD | \$359.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PN03LB-AD | \$77.00 | N | 3m [9.8 ft] | 8AWG | PDF | 230VAC APM-FF55D motors with brake |
| APCS-PN05LB-AD | \$99.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PN10LB-AD | \$153.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PN20LB-AD | \$265.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PF03LB-AD | \$114.00 | Y | 3m [9.8 ft] | | PDF | |
| APCS-PF05LB-AD | \$160.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PF10LB-AD | \$275.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PF20LB-AD | \$510.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PF03LB1-AD | \$95.00 | Y | 3m [9.8 ft] | 12AWG | PDF | 460VAC APM-FFP55D and APM-FFP75D motors with brakes |
| APCS-PF05LB1-AD | \$130.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PF10LB1-AD | \$220.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PF20LB1-AD | \$400.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PN03LB2-AD | \$130.00 | N | 3m [9.8 ft] | 8AWG | PDF | 230VAC APM-FF75D motors with brake |
| APCS-PN05LB2-AD | \$177.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PN10LB2-AD | \$300.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PN20LB2-AD | \$540.00 | | 20m [65.6 ft] | | PDF | |
| APCS-PF03LB2-AD | \$187.00 | Y | 3m [9.8 ft] | | PDF | |
| APCS-PF05LB2-AD | \$272.00 | | 5m [16.4 ft] | | PDF | |
| APCS-PF10LB2-AD | \$479.00 | | 10m [32.8 ft] | | PDF | |
| APCS-PF20LB2-AD | \$906.00 | | 20m [65.6 ft] | | PDF | |



APCS-PxxNB series power cable



APCS-PxxPB series power cable



APCS-PxxLB series power cable