


STABLE™ Motor Slide Bases

Mounting Slide Bases for 56 to 449T NEMA Motors Features

- Allows adjustment of motor mounting position
- Slide direction is perpendicular to motor shaft
- Double adjusting screws for frames 182T-449T
- Manufactured to precise dimensional standards
- Dimensionally interchangeable with existing major makes
- Heavy-duty steel construction
- Painted with oven-baked primer for better adhesion of customer's paint
- All "D" bolts (motor mounting bolts) are fixed to the exact motor foot pattern
- All "D" bolts are welded into position to prevent spinning and dropping from slots
- Nuts and washers are provided for securing the motor to the slide base



STABLE Motor Slide Bases for 3-Phase Motors

Part Number (MTA-BASE- xxx)	Price	Fits Frame Type	Product Wt. (lb)	Fits Motor						Drawing Links
				IronHorse	Leeson®	WEG (Part number ending in...)	Marathon			
					WashGuard®		microMAX, Max+, Black Max, Blue Max, SyMAX	XRI GP & NEMA Premium, Jet Pump	Globetrotter	
W56	\$14.00	56*	2.8	MTPM-P3x-1x18		(...)56-S (...)56C-S				PDF
				MTPM-P5x-1x18						
				MTPM-P7x-1x18						
				MTPM-0xx-1x18						
				MTPM-1xx-1x18						
				MTR(2)(P)-xxx-xxxxx*						
				MTRJ(P)-xxx-xxxxxx						
				MTSN-P33-3BD18						
				MTSN-P33-3BD18R						
				MTSN-P33-3BD36						
				MTSP-P33-3BD18						
				MTSP-P33-3BD18R						
				MTSP-P33-3BD36						
				MTSP-P33-3BD36R						
				MTSN-P50-3BD18						
				MTSN-P50-3BD18R						
				MTSN-P50-3BD36						
				MTSP-P50-3BD12						
				MTSP-P50-3BD18						
				MTSP-P50-3BD18R						
				MTSP-P50-3BD36						
				MTSP-P50-3BD36R						
				MTSN-P75-3BD18						
				MTSN-P75-3BD18R						
				MTSN-P75-3BD36						
				MTSP-P75-3BD12						
				MTSP-P75-3BD18						
				MTSP-P75-3BD18R						
				MTSP-P75-3BD36						
				MTSP-P75-3BD36R						
				MTSN-001-3BD18						
				MTSN-001-3BD18R						
				MTSN-001-3BD36						
				MTSP-001-3BD18						
				MTSP-001-3BD18R						
				MTSP-001-3BD36						
				MTSP-001-3BD36R						
				MTSN-1P5-3BD18						
				MTSN-1P5-3BD18R						
				MTSN-1P5-3BD36						
				MTSP-1P5-3BD18						
				MTSP-1P5-3BD18R						
				MTSP-1P5-3BD36						
				MTSP-1P5-3BD36R						
				MTSN-002-3BD18						
				MTSN-002-3BD18R						
				MTSN-002-3BD36						
				MTSP-002-3BD18						
				MTSP-002-3BD18R						
				MTSP-002-3BD36						
				MTSP-002-3BD36R						

* IronHorse MTR2 56HC motors have double-punched bases to fit on slide base **MTA-BASE-W56**.

STABLE™ Motor Slide Bases

STABLE Motor Slide Bases for 3-Phase Motors										
Part Number (MTA-BASE- xxx)	Price	Fits Frame Type	Product Wt. (lb)	Fits Motor						Drawing Links
				IronHorse	Leeson®	WEG (Part number ending in...)	Marathon			
					WashGuard®		microMAX, Max +, Black Max, Blue Max, SyMAX	XRI GP & NEMA Premium, Jet Pump	Globetrotter	
W143T	\$26.00	143T/ TC	4.6	MTCP2-001-3BD18(C) MTCP2-1P5-3BD36 MTSN-1P5-3BD36-14 MTSP-1P5-3BD36-14 MTSP-1P5-3BD36R-14	191487.00 191565.00	(....)145T-S (....)145TC-S	Y536(-A772)	E2001A E2003	-	PDF
W145T	\$26.00	145T/ TC	5.1	MTCP2-001-3BD12 MTCP2-1P5-3BD18(C) MTCP2-002-3BD18(C) MTCP2-002-3BD36 MTSP-001-3BD12 MTSN-1P5-3BD18-14 MTSN-1P5-3BD18R-14 MTSP-1P5-3BD18-14 MTSP-1P5-3BD18R-14 MTSN-002-3BD18-14 MTSN-002-3BD18R-14 MTSN-002-3BD36-14 MTSP-002-3BD18-14 MTSP-002-3BD18R-14 MTSP-002-3BD36-14 MTSP-002-3BD36R-14	121866.00 121868.00 121870.00 122182.00 122184.00 122185.00 191490.00 191491.00 191570.00		Y366 Y368 Y284 Y285 Y537 Y538(-A772) Y551(-A772)	E2002 E2004A E2007A	-	PDF
W182T	\$35.50	182T/ TC	9.2	MTCP2-1P5-3BD12 MTCP2-003-3BD18(C) MTCP2-003-3BD36 MTSP-1P5-3BD12 MTSN-003-3BD18-18 MTSN-003-3BD36-18 MTSP-003-3BD18-18 MTSP-003-3BD36-18	132196.00 132198.00		Y1999 Y286A Y541A(-A772) SY036 SY066	E2009 E2010	GT0010A GT1010A	PDF
W184T	\$35.50	184T/ TC	10	MTCP2-002-3BD12 MTCP2-005-3BD18(C) MTCP2-005-3BD36 MTF-00x-1C18 MTSP-002-3BD12 MTSP-005-3BD18 MTSP-005-3BD36	132197.00 132200.00 132201.00 132440.00		Y1372 Y287A Y540(-A772) Y543A(-A772) E2012 E2013 SY007A SY067	-	GT0013A GT1013A GT1210A GT1212A GT1213A	PDF
W213T	\$52.00	213T/ TC	13	MTCP2-003-3BD12 MTCP2-7P5-3BD18(C) MTCP2-7P5-3BD36 MTSP-003-3BD12 MTSP-7P5-3BD18	140819.00 140822.00 141266.00		Y994 Y542(-A772) Y545(-A772) E2011 E2016A E2011A E2016B SY068	-	GT0016A GT1016A GT1216A	PDF
W215T	\$52.00	215T/ TC	15	MTCP2-005-3BD12 MTCP2-010-3BD18(C) MTCP2-010-3BD36 MTSP-005-3BD12 MTSP-010-3BD18	140820.00 140821.00		Y996 Y544(-A772) Y547(-A772) E2018 E2014A E2018A SY069	-	GT0019A GT1019A GT1218A GT1219A	PDF
W254T	\$71.00	254T/ TC	18	MTCP2-7P5-3BD12 MTCP2-015-3BD18(C) MTCP2-015-3BD36 MTSP-015-3BD18	-		Y546(-A772) Y549(-A772)	-	GT0059 GT1022A GT1222A	PDF

* IronHorse MTR2 56HC motors have double-punched bases to fit on slide base [MTA-BASE-W56](#).

STABLE™ Motor Slide Bases

STABLE Motor Slide Bases for 3-Phase Motors										
Part Number (MTA-BASE- xxx)	Price	Fits Frame Type	Product Wt. (lb)	Fits Motor					Drawing Links	
				IronHorse	Leeson®	WEG (Part number ending in...)	Marathon			
					WashGuard®		microMAX, Max+, Black Max, Blue Max, SyMAX	XRI GP & NEMA Premium, Jet Pump		Globetrotter
W256T	\$71.00	256T/ TC	19	MTCP2-010-3BD12 MTCP2-020-3BD18(C) MTCP2-020-3BD36 MTSP-020-3BD18	–		Y548(-A772) Y552	–	GT0062 GT1025A GT1225A	PDF
W284T	\$79.00	284T/ TC	20	MTCP2-015-3BD12 MTCP2-025-3BD18(C)	–		–	–	GT0065 GT1028A	PDF
W286T	\$79.00	286T/ TC	21	MTCP2-020-3BD12 MTCP2-030-3BD18(C)	–		–	–	GT0067 GT1031A	PDF
W324T	\$116.00	324T/ TC	30	MTCP2-040-3BD18(C)	–		Y571(-A774) Y513(-A775)	–	GT0073 GT1034A	PDF
W326T	\$116.00	326T/ TC	31	MTCP2-050-3BD18(C)	–		Y572(-A774) Y514(-A775)	–	GT0077 GT1037A	PDF
W364T	\$158.00	364T/ TC	43	MTCP2-060-3BD18(C)	–		Y573(-A774) Y515(-A775)	–	GT1040A	PDF
W365T	\$158.00	365T/ TC	43	MTCP2-075-3BD18(C)	–		Y574(-A774) Y516(-A775)	–	GT1043A	PDF
W404T	\$193.00	404T/ TC	58	–	–		–	–	–	PDF
W405T	\$193.00	405T/ TC	60	MTCP2-100-3BD18(C)	–		Y575(-A774) Y517(-A775)	–	GT1046A	PDF
W444T	\$219.00	444T	63	MTCP2-125-3BD18	–		–	–	GT1049A	PDF
W445T	\$219.00	445T	65	MTCP2-150-3BD18	–		–	–	GT1052A	PDF
W447T	\$288.00	447T	89	MTCP2-200-3BD18	–		–	–	GT1055A	PDF
W449T	\$288.00	449T	94	MTCP2-250-3D18 MTCP2-300-3D18	–		–	–	–	PDF

* IronHorse MTR2 56HC motors have double-punched bases to fit on slide base [MTA-BASE-W56](#).

STABLE™ Motor Slide Bases

Mounting Slide Bases for 56 to 215T NEMA Motors Features

STABLE Motor Slide Bases for 1-phase Motors									
Part Number	Price	Fits Frame Type	Product Wt. (lb)	Fits Motor					
				IronHorse	Leeson®	Marathon			
					Washguard®	Marathon DP GP (NEMA Service Factor)	Marathon DP Air Compressor	Fan & Blower	Marathon TE GP 4-in-1
<u>MTA-BASE-W56</u>	\$14.00	56*	2.8	MTR2-xxx-1AB18 MTR2-xxx-1AB36 MTPM-xxx-1L18 MTPM-xxx-1M18	112431.00 112527.00 112528.00 112529.00 113583.00 114311.00 114313.00 114317.00 191475.00 191477.00 191479.00	<u>C158A</u> <u>G915A</u> <u>C175A</u> <u>C167A</u> <u>C179A</u> <u>G937A</u> <u>C185A</u> <u>C187A</u> <u>C193A</u> <u>E261A</u> <u>E268A</u> <u>EG277A</u>	<u>D010</u> <u>C169</u> <u>C704</u> <u>D017</u>	<u>C216</u> <u>C1153</u> <u>C1155</u> <u>B319</u> <u>D118</u> <u>C1158</u> <u>C235</u> <u>D115</u> <u>C1160</u> <u>C1161</u> <u>B352</u>	<u>G570</u> <u>D311</u> <u>G571</u> <u>D312</u> <u>G572</u> <u>D313</u> <u>G573</u> <u>D314</u> <u>G574</u> <u>D315</u> <u>G575</u> <u>D316</u>
<u>MTA-BASE-W143T</u>	\$26.00	143T / TC	4.6	–	–	<u>C188A</u>	–	–	–
<u>MTA-BASE-W145T</u>	\$26.00	145TC / TC	5.1	–	–	<u>C191</u> <u>I127</u> <u>C194</u>	–	–	–
<u>MTA-BASE-W182T</u>	\$35.50	182T / TC	9.2	–	–	–	–	–	–
<u>MTA-BASE-W184T</u>	\$35.50	184 / TC	10	MTF-00x-1C18	–	–	<u>Z502</u>	–	–
<u>MTA-BASE-W213T</u>	\$52.00	213T / TC	13	–	–	–	–	–	–
<u>MTA-BASE-W215T</u>	\$52.00	215T T TC	15	–	–	–	–	–	–

* IronHorse MTR2 56HC motors have double-punched bases to fit on slide base [MTA-BASE-W56](#).