

# NEMA 12 and 13 Small Continuous Hinge Wall-Mount



## Applications

Intended for use as electrical junction boxes, terminal wiring boxes, and instrument housings. Hinged door provides convenient access. Provides protection from dust, dirt, oil, and water.



## Construction

- Bodies fabricated from 14-gauge steel
- Doors fabricated from 16-gauge steel
- Continuously-welded seams ground smooth, less knockouts or holes
- Lids are sealed with closed-cell oil-resistant neoprene gasket
- External mounting plates on top and bottom of enclosure
- Weldnuts provided for mounting optional subpanels securely on models 6 x 4 in [152 x 102 mm] and larger
- External screw clamps are quick and easy to operate
- Standard continuous hinge
- Grounding provisions provided
- Uses WAN12RA clamp

## Finish


- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

## Listings

- UL 50, 12 and 13 [UL Files E6924]
- NEMA/EEMAC 12 and 13
- JIC EL-1-71



## Dimensions



### NOTES:

1. PANELS ARE 14GA STEEL.
2. PANEL SCREWS ARE #10-32 PAN HEAD.
3. TWO CLAMPS ARE USED IF  $W=8$ " OR MORE.

# NEMA 12 and 13 Small Continuous Hinge Wall-Mount



## Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 12 and 13 Small Continuous Hinge Wall-Mount				
Part Number	Price	Enclosure SizeHxWxD	Painted Steel Subpanel	Stainless Steel Subpanel
<a href="#">B040403CH</a>	\$63.00	4.31 x 4.31 x 3.14 [109 x 109 x 80]	—	—
<a href="#">B040404CH</a>	\$65.00	4.31 x 4.31 x 4.14 [109 x 109 x 105]	—	—
<a href="#">B060403CH</a>	\$72.00	6.31 x 4.31 x 3.14 [160 x 109 x 80]	<a href="#">P0604</a>	<a href="#">P0604SS</a>
<a href="#">B060404CH</a>	\$76.00	6.31 x 4.31 x 4.14 [160 x 109 x 105]	<a href="#">P0604</a>	<a href="#">P0604SS</a>
<a href="#">B060604CH</a>	\$81.00	6.31 x 6.31 x 4.14 [160 x 160 x 105]	<a href="#">P0606</a>	<a href="#">P0606SS</a>
<a href="#">B080603CH</a>	\$86.00	8.31 x 6.31 x 3.64 [211 x 160 x 92]	<a href="#">P0806</a>	<a href="#">P0806SS</a>
<a href="#">B080606CH</a>	\$102.00	8.31 x 6.31 x 6.14 [211 x 160 x 156]	<a href="#">P0806</a>	<a href="#">P0806SS</a>
<a href="#">B080804CH</a>	\$98.00	8.31 x 8.31 x 4.14 [211 x 211 x 105]	<a href="#">P0808</a>	—
<a href="#">B100804CH</a>	\$107.00	10.31 x 8.31 x 4.14 [262 x 211 x 105]	<a href="#">P1008</a>	<a href="#">P1008SS</a>
<a href="#">B100804CHS</a>	\$106.00	8.31 x 10.31 x 4.14 [211 x 262 x 105]	<a href="#">P1008</a>	<a href="#">P1008SS</a>
<a href="#">B100806CH</a>	\$121.00	10.31 x 8.31 x 6.14 [262 x 211 x 156]	<a href="#">P1008</a>	<a href="#">P1008SS</a>
<a href="#">B101006CH</a>	\$133.00	10.31 x 10.31 x 6.14 [262 x 262 x 156]	<a href="#">P1010</a>	—
<a href="#">B120604CH</a>	\$107.00	12.31 x 6.31 x 4.14 [313 x 160 x 105]	<a href="#">P1206</a>	—
<a href="#">B121005CH</a>	\$137.00	12.31 x 10.31 x 5.14 [313 x 262 x 131]	<a href="#">P1210</a>	<a href="#">P1210SS</a>
<a href="#">B121005CHS</a>	\$135.00	10.31 x 12.31 x 5.14 [262 x 313 x 131]	<a href="#">P1210</a>	<a href="#">P1210SS</a>
<a href="#">B121008CH</a>	\$167.00	12.31 x 10.31 x 8.14 [313 x 262 x 207]	<a href="#">P1210</a>	<a href="#">P1210SS</a>
<a href="#">B121206CH</a>	\$159.00	12.31 x 12.31 x 6.14 [313 x 313 x 156]	<a href="#">P1212</a>	<a href="#">P1212SS</a>
<a href="#">B140806CH</a>	\$146.00	14.31 x 8.31 x 6.14 [363 x 211 x 156]	<a href="#">P1408</a>	—
<a href="#">B141206CH</a>	\$176.00	14.31 x 12.31 x 6.14 [363 x 313 x 156]	<a href="#">P1412</a>	<a href="#">P1412SS</a>
<a href="#">B141206CHS</a>	\$171.00	12.31 x 14.31 x 6.14 [313 x 363 x 156]	<a href="#">P1412</a>	<a href="#">P1412SS</a>
<a href="#">B141208CH</a>	\$198.00	14.31 x 12.31 x 8.14 [363 x 313 x 207]	<a href="#">P1412</a>	<a href="#">P1412SS</a>
<a href="#">B161006CH</a>	\$175.00	16.31 x 10.31 x 6.14 [414 x 262 x 156]	<a href="#">P1610</a>	—
<a href="#">B161406CH</a>	\$204.00	16.31 x 14.31 x 6.14 [414 x 363 x 156]	<a href="#">P1614</a>	<a href="#">P1614SS</a>
<a href="#">B161406CHS</a>	\$202.00	14.31 x 16.31 x 6.14 [363 x 414 x 156]	<a href="#">P1614</a>	<a href="#">P1614SS</a>
<a href="#">B161408CH</a>	\$226.00	16.31 x 14.31 x 8.14 [414 x 363 x 207]	<a href="#">P1614</a>	<a href="#">P1614SS</a>
<a href="#">B161410CH</a>	\$256.00	16.31 x 14.31 x 10.14 [414 x 363 x 258]	<a href="#">P1614</a>	<a href="#">P1614SS</a>

Notes: Subpanels must be ordered separately.  
Dimensions in inches [millimeters].  
Letters in table correspond to letters on dimensional drawings.

# Enclosure Subpanels



## Subpanels

Subpanels are not included with most enclosures and must be purchased separately.

The specifications table for each enclosure family list the part number of the subpanel that goes with each enclosure.

## Subpanels for Small NEMA 12 (B) and NEMA 4 (BN4) Enclosures

- 14-gauge (painted, stainless, and galvanized)
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels fit the following enclosures: B, B\_CH, BN4, BN4\_CH, BN4\_CHQT, BN4\_SS, BN4\_CHSS, BN4\_CHSSA, BN4\_CHQTSS, BN4\_CHQTSSA ("\_" refers to dimensions).



Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
Color indicates shipping lead time in business days.				

Subpanels for B and BN4 Enclosures					
Painted Steel	Price	304 Stainless Steel	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
<b>P0604</b>	\$5.00	<b>P0604SS</b>	\$16.75	6 x 4	4.88 x 2.88 [124 x 73]
<b>P0606</b>	\$6.00	<b>P0606SS</b>	\$20.50	6 x 6	4.88 x 4.88 [124 x 124]
<b>P0806</b>	\$6.75	<b>P0806SS</b>	\$24.50	8 x 6	6.88 x 4.88 [175 x 124]
<b>P0808</b>	\$8.00	—	—	8 x 8	6.88 x 6.88 [175 x 175]
<b>P1008</b>	\$8.75	<b>P1008SS</b>	\$35.50	10 x 8	8.88 x 6.88 [226 x 175]
<b>P1010</b>	\$11.00	—	—	10 x 10	8.88 x 8.88 [226 x 226]
<b>P1206</b>	\$8.75	—	—	12 x 6	10.88 x 4.88 [276 x 124]
<b>P1210</b>	\$12.75	<b>P1210SS</b>	\$50.00	12 x 10	10.88 x 8.88 [276 x 226]
<b>P1212</b>	\$15.00	<b>P1212SS</b>	\$58.00	12 x 12	10.88 x 10.88 [276 x 276]
<b>P1408</b>	\$12.00	—	—	14 x 8	12.88 x 6.88 [327 x 175]
<b>P1412</b>	\$16.50	<b>P1412SS</b>	\$67.00	14 x 12	12.88 x 10.88 [327 x 276]
<b>P1610</b>	\$16.25	—	—	16 x 10	14.88 x 8.88 [378 x 226]
<b>P1614</b>	\$22.00	<b>P1614SS</b>	\$88.00	16 x 14	14.88 x 12.88 [378 x 327]

Notes: Dimensions in inches [millimeters].  
Letters in table correspond to letters on dimensional drawing.

## Dimensions

