

30mm Pushbutton with 2.5 in Hole Spacing NEMA 12 and 13 Wall-Mount



Applications

Designed to hold 30mm [1.18 in] oil-tight pushbuttons, switches and pilot lights with extra size to allow 2.5 in [63.5 mm] between centers of pushbutton holes. Provides protection from dirt, dust, oil and water.

Construction

- Fabricated from 14-gauge steel
- Closed-cell oil-resistant neoprene gasket
- Continuously-welded seams ground smooth
- Cover held in place by continuous hinge
- Subpanel included with enclosure
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells
- Standard "4-way" pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Grounding provisions provided

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Included subpanels are white polyester powder over phosphatized surfaces

Listings

- UL 508 12 and 13 [UL File E64791]
- NEMA/EEMAC 12 and 13



30mm Pushbutton with 2.5 in Hole Spacing NEMA 12 and 13 Wall-Mount


Part Number	Price	# Holes	Enclosure Size HxWxD
<u>PBYX4S</u>	\$172.00	4	8.82 x 7.88 x 6.33 [224 x 200 x 161]
<u>PBYX6</u>	\$202.00	6	11.32 x 7.88 x 6.33 [288 x 200 x 161]
<u>PBYX9</u>	\$236.00	9	11.32 x 10.38 x 6.33 [288 x 264 x 161]
<u>PBYX12</u>	\$267.00	12	13.82 x 10.38 x 6.33 [351 x 264 x 161]
<u>PBYX16</u>	\$304.00	16	13.82 x 12.88 x 6.33 [351 x 327 x 161]
<u>PBYX20</u>	\$341.00	20	16.32 x 12.88 x 6.33 [415 x 327 x 161]
<u>PBYX25</u>	\$384.00	25	16.32 x 15.38 x 6.33 [415 x 391 x 161]
<u>PBYX30</u>	\$418.00	30	18.82 x 15.38 x 6.33 [478 x 391 x 161]
<u>PBYX36</u>	\$473.00	36	18.82 x 17.88 x 6.33 [478 x 454 x 161]
<u>PBYX42</u>	\$518.00	42	21.32 x 17.88 x 6.33 [542 x 454 x 161]

Note: Dimensions in inches [millimeters].

30mm Pushbutton with 2.5 in Hole Spacing NEMA 12 and 13 Wall-Mount



Dimensions



PBYX HOLE ARRANGEMENTS

