

W1C NEMA 12 and 13 Operator Consoles



Applications

Designed to house electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches, etc. can be mounted on sloping control surfaces. Interior components can be mounted on standard subpanel. Heavy-duty construction provides protection from dirt, dust, oil and water.

Construction

- Bodies and doors fabricated from 14-gauge steel
- Continuously-welded seams ground smooth, without knockouts, holes or cutouts
- 3-point keylocking handle is provided on front, main door
- Main door on console is raised
- Control panels are hinged along bottom edge
- Controls panels, access panels and instrument panels have captivated screws that thread into sealed wells
- Door stops provided to hold control panel open
- Closed-cell neoprene gasket
- Removable subpanel included with enclosure
- Grounding provisions provided
- Uses WAL2 series handles and WAL2KEY replacement key

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Included painted steel subpanel is white polyester powder over phosphatized surfaces

Listings

- UL 508 12 and 13 [UL File E64791]
- NEMA/EEMAC 12 and 13



W1C NEMA 12 and 13 Operator Consoles			
Console	Price	Console Size HxWxD	Subpanel Size
W1C24	\$1,955.00	40.41 x 24.00 x 21.03 [1026 x 610 x 534]	30.00 x 21.00 [762 x 533]
W1C30	\$2,259.00	40.41 x 30.00 x 21.03 [1026 x 762 x 534]	30.00 x 27.00 [762 x 686]
W1C36	\$2,548.00	40.41 x 36.00 x 21.03 [1026 x 914 x 534]	30.00 x 33.00 [762 x 838]
W1C42*	\$3,116.00	40.41 x 42.00 x 21.03 [1026 x 1067 x 534]	30.00 x 39.00 [762 x 991]
W1C48*	\$3,333.00	40.41 x 48.00 x 21.03 [1026 x 1219 x 534]	30.00 x 45.00 [762 x 1143]
Notes: Dimensions in inches [millimeters]. Letters in table correspond to letters on dimensional drawings Subpanel included with enclosure. *Two door units.			

W1C NEMA 12 and 13 Operator Consolets



Dimensions

