

NEMA 1, 4, 4X, and 12 Hinged Cover Stainless Steel Wiring Trough



Applications

Designed to protect internal components and wiring from dust, dirt, and water. This trough can be used indoors or outdoors, as well as in corrosive environments.

Construction

- Trough and cover fabricated from 14 gauge, 304 stainless steel
- #3 intermediate polished finish or polyester powder coat
- Seams are continuously-welded and ground smooth
- External clamps and continuous hinge provided
- External mounting feet included
- Cover is sealed with poured-in-place gasket

Listings

- UL 870 1, 4, 4X and 12
- IEC 60529, IP66



- UL Files E32576, E470978

Note: For current listings, please see www.automationdirect.com

NEMA 1, 4, 4X, and 12 Hinged Cover Wiring Trough			
Stainless Steel	Price	Enclosure Overall Size HxWxD	Drawing Link
T2212CHSS	\$267.00	2.50 x 2.50 x 12.00 [64 x 64 x 305]	PDF
T2224CHSS	\$309.00	2.50 x 2.50 x 24.00 [64 x 64 x 610]	PDF
T2236CHSS	\$344.00	2.50 x 2.50 x 36.00 [64 x 64 x 914]	PDF
T2248CHSS	\$416.00	2.50 x 2.50 x 48.00 [64 x 64 x 1219]	PDF
T2272CHSS	\$503.00	2.50 x 2.50 x 72.00 [64 x 64 x 1829]	PDF
T4412CHSS	\$310.00	4.00 x 4.00 x 12.00 [102 x 102 x 305]	PDF
T4424CHSS	\$421.00	4.00 x 4.00 x 24.00 [102 x 102 x 610]	PDF
T4436CHSS	\$506.00	4.00 x 4.00 x 36.00 [102 x 102 x 914]	PDF
T4448CHSS	\$567.00	4.00 x 4.00 x 48.00 [102 x 102 x 1219]	PDF
T4472CHSS	\$712.00	4.00 x 4.00 x 72.00 [102 x 102 x 1829]	PDF
T6612CHSS	\$368.00	6.00 x 6.00 x 12.00 [152 x 152 x 305]	PDF
T6624CHSS	\$511.00	6.00 x 6.00 x 24.00 [152 x 152 x 610]	PDF
T6636CHSS	\$601.00	6.00 x 6.00 x 36.00 [152 x 152 x 914]	PDF
T6648CHSS	\$728.00	6.00 x 6.00 x 48.00 [152 x 152 x 1219]	PDF
T6672CHSS	\$996.00	6.00 x 6.00 x 72.00 [152 x 152 x 1829]	PDF
T8812CHSS	\$495.00	8.00 x 8.00 x 12.00 [203 x 203 x 305]	PDF
T8824CHSS	\$591.00	8.00 x 8.00 x 24.00 [203 x 203 x 610]	PDF
T8836CHSS	\$945.00	8.00 x 8.00 x 36.00 [203 x 203 x 914]	PDF
T8848CHSS	\$1,111.00	8.00 x 8.00 x 48.00 [203 x 203 x 1219]	PDF
T121224CHSS	\$818.00	12.00 x 12.00 x 24.00 [305 x 305 x 610]	PDF
T121236CHSS	\$1,201.00	12.00 x 12.00 x 36.00 [305 x 305 x 914]	PDF
T121248CHSS	\$1,516.00	12.00 x 12.00 x 48.00 [305 x 305 x 1219]	PDF
Note: Dimensions in inches [millimeters].			



NEMA 1, 4, 4X, and 12 Hinged Cover Stainless Steel Wiring Trough



Dimensions

