

NEMA 1 Single-Door Wall-Mount with Knockouts



Applications

Designed for use as surface-mounted junction box, service box, switch box and cutout box.

Construction

- Bodies and doors fabricated from 14- or 16-gauge steel
- 3.0in [76mm] depth enclosures furnished with formed steel hinge non-removable cover
- 4.0in [103mm] and 6.0in [152mm] depth enclosures furnished with clamp style hinges allowing for removable/replaceable covers
- Various sizes of removable concentric knockouts are furnished on all four sides of standard cutout enclosures
- Mounting holes on back of enclosure

Finish

- ANSI 61 gray polyester powder inside and out

Listings

- UL 50, 1 [UL File E6924]
- NEMA/EEMAC 1



A Series NEMA 1 Single-Door Wall-Mount with Knockouts					
Part Number	Price	Body/Door Steel Gauge	Enclosure Size HxWxD	Knockout Pattern	
				Width Side	Height Side
A040604	\$15.25	16/16	6.44 x 4.44 x 4.38 [164 x 113 x 111]	A-A	A-B-A
A060603	\$17.50	16/16	6.37 x 6.37 x 3.06 [162 x 162 x 78]	A-B-A	A-B-A
A060604	\$18.50	16/16	6.37 x 6.37 x 4.38 [162 x 162 x 111]	A-A	A-B-A
A060606	\$22.50	16/16	6.37 x 6.37 x 6.38 [162 x 162 x 162]	A-B-A	A-B-A
A060804	\$21.50	16/16	8.25 x 6.25 x 4.38 [210 x 159 x 111]	A-B-A	A-B-A
A080804	\$25.50	16/16	8.37 x 8.37 x 4.38 [213 x 213 x 111]	A-B-A	A-B-A
A080806	\$30.50	16/16	8.37 x 8.37 x 6.38 [213 x 213 x 162]	A-B-A	A-B-A
A081004	\$29.00	16/16	10.37 x 8.37 x 4.38 [263 x 213 x 111]	A-B-A	B-A-F-F-A
A081006	\$34.50	16/16	10.37 x 8.37 x 6.38 [263 x 213 x 162]	A-B-A	B-A-F-F-A
A081204	\$33.00	16/16	12.25 x 8.25 x 4.38 [311 x 210 x 111]	A-B-A	B-A-F-F-A-B
A101004	\$33.50	16/16	10.25 x 10.25 x 4.38 [260 x 260 x 111]	B-A-F-F-A	B-A-F-F-A
A101006	\$39.50	16/16	10.25 x 10.25 x 6.38 [260 x 260 x 162]	B-A-F-F-A	B-A-F-F-A
A101204	\$37.50	16/16	12.25 x 10.25 x 4.38 [311 x 260 x 111]	B-A-F-F-A	B-A-F-F-A-B
A101206	\$44.50	16/16	12.25 x 10.25 x 6.38 [311 x 260 x 162]	B-A-F-F-A	B-A-F-F-A-B
A121204	\$43.00	16/16	12.25 x 12.25 x 4.38 [311 x 311 x 111]	B-A-F-F-A-B	B-A-F-F-A-B
A121206	\$50.00	16/16	12.25 x 12.25 x 6.38 [311 x 311 x 162]	B-A-F-F-A-B	B-A-F-F-A-B
A121504	\$50.00	16/16	15.25 x 12.25 x 4.38 [387 x 311 x 111]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
A121604	\$52.00	16/16	16.25 x 12.25 x 4.38 [413 x 311 x 111]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
A121606	\$60.00	16/16	16.25 x 12.25 x 6.38 [413 x 311 x 162]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
A121804	\$58.00	16/16	18.25 x 12.25 x 4.38 [464 x 311 x 111]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
A121806	\$67.00	16/16	18.25 x 12.25 x 6.38 [464 x 311 x 162]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
A151506	\$77.00	16/16	15.25 x 15.25 x 6.38 [387 x 387 x 162]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
Notes: Subpanels must be ordered separately. Dimensions in inches [millimeters].					

Table continued on next page

NEMA 1 Single-Door Wall-Mount with Knockouts



Table continued from previous page

A Series NEMA 1 Single-Door Wall-Mount with Knockouts						
Part Number	Price	Body/Door Steel Gauge	Enclosure Size HxWxD	Knockout Pattern		
				Width Side	Height Side	
A151804	\$83.00	16/16	18.25 x 15.25 x 4.38 [464 x 387 x 111]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A	
A161606	\$70.00	16/16	16.25 x 16.25 x 6.38 [413 x 413 x 162]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A	
A181806	\$90.00	16/16	18.25 x 18.25 x 6.38 [464 x 464 x 162]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A	
A182406	\$146.00	14/14	24.25 x 18.25 x 6.39 [616 x 464 x 162]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A	
A242406	\$181.00	14/14	24.25 x 24.25 x 6.39 [616 x 616 x 162]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A	

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].

Dimensions

