

# NEMA 3 and 4 Gasketed Screw Cover Wall-Mount



## Application

Designed for use as a wiring box, junction box, pull box and terminal box in many indoor or outdoor applications where dust or moisture is a problem.

## Construction

- Bodies and covers fabricated from 12- or 14-gauge carbon steel
- Seams are continuously-welded and ground smooth
- Cover contains closed-cell oil-resistant neoprene gasket
- Enclosure comes with stainless steel cover screws which thread into sealed wells to prevent liquid, dust, etc., from entering into the enclosure through the screw holes
- Ground stud located in door
- No holes, knockouts, or rear mounting holes

## Finish

- ANSI 61 gray polyester powder inside and out

## Listings

- UL50, 3 and 4 [UL File E23553]
- NEMA/EEMAC 3 and 4



Note: For current listings, please see [www.automationdirect.com](http://www.automationdirect.com)

NEMA 3 and 4 Gasketed Screw Cover			
ANSI 61 Gray Light-Textured	Price	Body/Door Steel Gauge	Enclosure Size HxWxD
<a href="#">WA060604GSC</a>	\$80.00	14/14	6.13 x 6.13 x 4.36 [156 x 156 x 111]
<a href="#">WA060606GSC</a>	\$81.00		6.13 x 6.13 x 6.36 [156 x 156 x 162]
<a href="#">WA060804GSC</a>	\$84.00		6.13 x 8.13 x 4.36 [156 x 207 x 111]
<a href="#">WA060806GSC</a>	\$89.00		6.13 x 8.13 x 6.36 [156 x 207 x 162]
<a href="#">WA080804GSC</a>	\$98.00		8.13 x 8.13 x 4.36 [207 x 207 x 111]
<a href="#">WA080806GSC</a>	\$102.00		8.13 x 8.13 x 6.36 [207 x 207 x 162]
<a href="#">WA081004GSC</a>	\$106.00		8.13 x 10.13 x 4.36 [207 x 257 x 111]
<a href="#">WA101004GSC</a>	\$116.00		10.13 x 10.13 x 4.36 [257 x 257 x 111]
<a href="#">WA101006GSC</a>	\$129.00		10.13 x 10.13 x 6.36 [257 x 257 x 162]
<a href="#">WA101206GSC</a>	\$147.00		10.13 x 12.13 x 6.36 [257 x 308 x 162]
<a href="#">WA121204GSC</a>	\$154.00		12.13 x 12.13 x 4.36 [308 x 308 x 111]
<a href="#">WA121206GSC</a>	\$162.00		12.13 x 12.13 x 6.36 [308 x 308 x 162]
<a href="#">WA121606GSC</a>	\$169.00		12.13 x 16.13 x 6.36 [308 x 410 x 162]
<a href="#">WA121608GSC</a>	\$174.00		12.13 x 16.13 x 8.36 [308 x 410 x 212]
<a href="#">WA161606GSC</a>	\$181.00		16.13 x 16.13 x 6.36 [410 x 410 x 162]
<a href="#">WA161608GSC</a>	\$189.00		16.13 x 16.13 x 8.36 [410 x 410 x 212]
<a href="#">WA181806GSC</a>	\$190.00		18.13 x 18.13 x 6.36 [461 x 461 x 162]
<a href="#">WA202008GSC</a>	\$294.00		20.13 x 20.13 x 8.36 [511 x 511 x 212]
<a href="#">WA202408GSC</a>	\$333.00		20.13 x 24.13 x 8.36 [511 x 613 x 212]
<a href="#">WA242408GSC</a>	\$378.00		24.13 x 24.13 x 8.36 [613 x 613 x 212]
<a href="#">WA303012GSC</a>	\$914.00	12/12	30.25 x 30.25 x 12.41 [768 x 768 x 315]
<a href="#">WA363612GSC</a>	\$934.00		36.25 x 36.25 x 12.41 [921 x 921 x 315]
Note: Dimensions in inches [millimeters].			

# NEMA 3 and 4 Gasketed Screw Cover Galvanized Steel Wall-Mount



## Application

Designed for use as a wiring box, junction box, pull box and terminal box in many indoor or outdoor applications where dust or moisture is a problem.

## Construction

- Bodies and covers fabricated from G-90 grade galvanized steel
- Seams are continuously-welded and ground smooth
- Cover contains closed-cell oil-resistant neoprene gasket
- Enclosure comes with stainless steel cover screws which thread into sealed wells to prevent liquid, dust, etc., from entering into the enclosure through the screw holes
- Ground stud located in door
- Galvanized box welded corners protected by zinc-rich coating
- No holes, knockouts, or rear mounting holes

## Finish

- G-90 pregalvanized steel

## Listings

- UL50, 3 and 4 [UL File E23553]
- NEMA/EEMAC 3 and 4
- CSA Certified 3 and 4 [CSA File LL66078]



Note: For current listings, please see [www.automationdirect.com](http://www.automationdirect.com)

NEMA 3 and 4 Gasketed Screw Cover – Galvanized Steel			
Galvanized	Price	Body/Door Steel Gauge	Enclosure Size HxWxD
<a href="#">WA060604GSCG</a>	\$80.00	14/14	6.13 x 6.13 x 4.40 [156 x 156 x 112]
<a href="#">WA060606GSCG</a>	\$81.00		6.13 x 6.13 x 6.40 [156 x 156 x 163]
<a href="#">WA060804GSCG</a>	\$84.00		6.13 x 8.13 x 4.40 [156 x 207 x 112]
<a href="#">WA060806GSCG</a>	\$89.00		6.13 x 8.13 x 6.40 [156 x 207 x 163]
<a href="#">WA080804GSCG</a>	\$98.00		8.13 x 8.13 x 4.40 [207 x 207 x 112]
<a href="#">WA080806GSCG</a>	\$102.00		8.13 x 8.13 x 6.40 [207 x 207 x 163]
<a href="#">WA081004GSCG</a>	\$106.00		8.13 x 10.13 x 4.40 [207 x 257 x 112]
<a href="#">WA101004GSCG</a>	\$116.00		10.13 x 10.13 x 4.40 [257 x 257 x 112]
<a href="#">WA101006GSCG</a>	\$129.00		10.13 x 10.13 x 6.40 [257 x 257 x 163]
<a href="#">WA101206GSCG</a>	\$147.00		10.13 x 12.13 x 6.40 [257 x 308 x 163]
<a href="#">WA121204GSCG</a>	\$154.00		12.13 x 12.13 x 4.40 [308 x 308 x 112]
<a href="#">WA121206GSCG</a>	\$162.00		12.13 x 12.13 x 6.40 [308 x 308 x 163]
Note: Dimensions in inches [millimeters].			

# NEMA 3, 4, and 4X Gasketed Screw Cover Stainless Steel Wall-Mount



## Application

Designed for use as a wiring box, junction box, pull box and terminal box in many indoor or outdoor applications where dust or moisture is a problem.

## Construction

- Bodies and covers fabricated from 304 stainless steel
- Seams are continuously-welded and ground smooth
- Cover contains closed-cell oil-resistant neoprene gasket
- Enclosure comes with stainless steel cover screws which thread into sealed wells to prevent liquid, dust, etc., from entering into the box through the screw holes
- Ground stud located in door
- No holes, knockouts, or rear mounting holes

## Finish

- Cover and outside of enclosure have #3 intermediate polished finish

## Listings

- UL50, 3, 4, and 4X [UL File E23553]
- NEMA/EEMAC 3, 4, and 4X



Note: For current listings, please see [www.automationdirect.com](http://www.automationdirect.com)

## NEMA 3, 4, and 4X Gasketed Screw Cover - Stainless Steel

Stainless Steel	Price	Body/Door Steel Gauge	Enclosure Size HxWxD
<a href="#">WA060604GSCSS</a>	\$121.00	14/14	6.13 x 6.13 x 4.32 [156 x 156 x 110]
<a href="#">WA060606GSCSS</a>	\$173.00		6.13 x 6.13 x 6.32 [156 x 156 x 161]
<a href="#">WA060804GSCSS</a>	\$137.00		6.13 x 8.13 x 4.32 [156 x 207 x 110]
<a href="#">WA060806GSCSS</a>	\$145.00		6.13 x 8.13 x 6.32 [156 x 207 x 161]
<a href="#">WA080804GSCSS</a>	\$224.00		8.13 x 8.13 x 4.32 [207 x 207 x 110]
<a href="#">WA080806GSCSS</a>	\$180.00		8.13 x 8.13 x 6.32 [207 x 207 x 161]
<a href="#">WA081004GSCSS</a>	\$195.00		8.13 x 10.13 x 4.32 [207 x 257 x 110]
<a href="#">WA101004GSCSS</a>	\$209.00		10.13 x 10.13 x 4.32 [257 x 257 x 110]
<a href="#">WA101006GSCSS</a>	\$235.00		10.13 x 10.13 x 6.32 [257 x 257 x 161]
<a href="#">WA101206GSCSS</a>	\$260.00		10.13 x 12.13 x 6.32 [257 x 308 x 161]
<a href="#">WA121204GSCSS</a>	\$285.00		12.13 x 12.13 x 4.32 [308 x 308 x 110]
<a href="#">WA121206GSCSS</a>	\$304.00		12.13 x 12.13 x 6.32 [308 x 308 x 161]
<a href="#">WA121606GSCSS</a>	\$330.00		12.13 x 16.13 x 6.32 [308 x 410 x 161]
<a href="#">WA121608GSCSS</a>	\$340.00		12.13 x 16.13 x 8.32 [308 x 410 x 211]
<a href="#">WA242408GSCSS</a>	Retired		24.12 x 24.13 x 8.32 [613 x 613 x 211]

Note: Dimensions in inches [millimeters].

# NEMA 3 and 4 Gasketed Screw Cover Wall-Mount



## Dimensions

