

NEMA 4, 4X, 12, and 13 Aluminum Lift-Off Cover Wall-Mount



Applications

Designed as an instrument housing or junction box for electrical, electronic, or pneumatic components. It is ideal for applications where a lightweight, corrosion resistant enclosure is required.

Construction

- Bodies and doors fabricated from 0.08 in [2mm] thick 5052-H32 aluminum
- Continuously-welded seams ground smooth
- Closed-cell oil-resistant neoprene gasket
- External mounting plate, top and bottom of enclosure
- Weldnuts are provided to secure optional subpanel
- Stainless steel screws and clamps on four sides of cover to assure water tight seal
- Optional subpanels and terminal kits must be ordered separately
- Grounding provisions provided
- Uses WABN4JIC clamp

Finish

- Exterior and doors of enclosures have a smooth-grained finish

Listings

- UL 50, 4, 4X, 12, and 13
- NEMA/EEMAC 4, 4X, 12, and 13
- JIC EL-1-71
- UL File E6924, E23553



Note: For current listings, please see www.automationdirect.com

NEMA 4, 4X, 12, and 13 Aluminum Lift-Off Cover Wall-Mount Enclosures




Part Number	Price	Enclosure SizeHxWxD	Painted Steel Subpanel	Stainless Steel Subpanel
<u>BN4060403AL</u>	\$167.00	6.31 x 4.31 x 3.26 [160 x 109 x 83]	<u>P0604</u>	<u>P0604SS</u>
<u>BN4060604AL</u>	\$187.00	6.31 x 6.31 x 4.26 [160 x 160 x 108]	<u>P0606</u>	<u>P0606SS</u>
<u>BN4080603AL</u>	\$195.00	8.31 x 6.31 x 3.76 [211 x 160 x 96]	<u>P0806</u>	<u>P0806SS</u>
<u>BN4100804AL</u>	\$210.00	10.31 x 8.31 x 4.26 [262 x 211 x 108]	<u>P1008</u>	<u>P1008SS</u>
<u>BN4121005AL</u>	\$281.00	12.31 x 10.31 x 5.26 [313 x 262 x 134]	<u>P1210</u>	<u>P1210SS</u>
<u>BN4141206AL</u>	\$342.00	14.31 x 12.31 x 6.26 [363 x 313 x 159]	<u>P1412</u>	<u>P1412SS</u>
<u>BN4161406AL</u>	\$350.00	16.31 x 14.31 x 6.26 [414 x 363 x 159]	<u>P1614</u>	<u>P1614SS</u>

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].
Letters in table correspond to letters on dimensional drawings.

NEMA 4, 4X, 12, and 13 Aluminum Lift-Off Cover Wall-Mount



Dimensions



NOTES;

- 1.) SUBPANELS ARE 14GA STEEL
- 2.) SUBPANELS SCREWS ARE #10-32 PAN HEAD.

Enclosure Subpanels



Subpanels

Subpanels are not included with most enclosures and must be purchased separately.

The specifications table for each enclosure family list the part number of the subpanel that goes with each enclosure.

Subpanels for Small NEMA 12 (B) and NEMA 4 (BN4) Enclosures

- 14-gauge (painted, stainless, and galvanized)
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels fit the following enclosures: B, B_CH, BN4, BN4_CH, BN4_CHQT, BN4_SS, BN4_CHSS, BN4_CHSSA, BN4_CHQTSS, BN4_CHQTSSA ("_" refers to dimensions).



Subpanels for B and BN4 Enclosures					
Painted Steel	Price	304 Stainless Steel	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
P0604	\$5.25	P0604SS	\$15.25	6 x 4	4.88 x 2.88 [124 x 73]
P0606	\$6.25	P0606SS	\$19.00	6 x 6	4.88 x 4.88 [124 x 124]
P0806	\$7.25	P0806SS	\$22.50	8 x 6	6.88 x 4.88 [175 x 124]
P0808	\$8.50	—	—	8 x 8	6.88 x 6.88 [175 x 175]
P1008	\$9.25	P1008SS	\$32.50	10 x 8	8.88 x 6.88 [226 x 175]
P1010	\$11.50	—	—	10 x 10	8.88 x 8.88 [226 x 226]
P1206	\$9.25	—	—	12 x 6	10.88 x 4.88 [276 x 124]
P1210	\$13.25	P1210SS	\$45.50	12 x 10	10.88 x 8.88 [276 x 226]
P1212	\$15.50	P1212SS	\$53.00	12 x 12	10.88 x 10.88 [276 x 276]
P1408	\$12.75	—	—	14 x 8	12.88 x 6.88 [327 x 175]
P1412	\$17.50	P1412SS	\$61.00	14 x 12	12.88 x 10.88 [327 x 276]
P1610	\$17.00	—	—	16 x 10	14.88 x 8.88 [378 x 226]
P1614	\$23.00	P1614SS	\$80.00	16 x 14	14.88 x 12.88 [378 x 327]

Notes: Dimensions in inches [millimeters].
Letters in table correspond to letters on dimensional drawing.

Dimensions

