

NEMA 4 Hinged Cover Wiring Trough



Applications

Designed to protect internal components and wiring from dust, dirt, and water. This trough can be used indoors or outdoors, as well as in corrosive environments.

Construction

- Trough and cover fabricated from carbon steel
- Polyester powder coat
- Seams are continuously-welded and ground smooth
- External clamps and continuous hinge provided
- External mounting feet included
- Cover is sealed with poured-in-place gasket

Listings

- UL 870 1, 4, 4X and 12
- IEC 60529, IP66
- UL Files E32576, E470978

Note: For current listings, please see www.Automationdirect.com



NEMA 4 Hinged Cover Wiring Trough			
Carbon Steel	Price	Enclosure Overall Size HxWxD	Drawing Link
T2212CH	\$197.00	2.50 x 2.50 x 12.00 [64 x 64 x 305]	PDF
T2224CH	\$228.00	2.50 x 2.50 x 24.00 [64 x 64 x 610]	PDF
T2236CH	\$259.00	2.50 x 2.50 x 36.00 [64 x 64 x 914]	PDF
T2248CH	\$279.00	2.50 x 2.50 x 48.00 [64 x 64 x 1219]	PDF
T4412CH	\$229.00	4.00 x 4.00 x 12.00 [102 x 102 x 305]	PDF
T4424CH	\$289.00	4.00 x 4.00 x 24.00 [102 x 102 x 610]	PDF
T4436CH	\$347.00	4.00 x 4.00 x 36.00 [102 x 102 x 914]	PDF
T4448CH	\$419.00	4.00 x 4.00 x 48.00 [102 x 102 x 1219]	PDF
T6612CH	\$272.00	6.00 x 6.00 x 12.00 [152 x 152 x 305]	PDF
T6624CH	\$360.00	6.00 x 6.00 x 24.00 [152 x 152 x 610]	PDF
T6636CH	\$449.00	6.00 x 6.00 x 36.00 [152 x 152 x 914]	PDF
T6648CH	\$538.00	6.00 x 6.00 x 48.00 [152 x 152 x 1219]	PDF
T8812CH	\$328.00	8.00 x 8.00 x 12.00 [203 x 203 x 305]	PDF
T8824CH	\$436.00	8.00 x 8.00 x 24.00 [203 x 203 x 610]	PDF
T8836CH	\$555.00	8.00 x 8.00 x 36.00 [203 x 203 x 914]	PDF
T8848CH	\$693.00	8.00 x 8.00 x 48.00 [203 x 203 x 1219]	PDF
T121224CH	\$605.00	12.00 x 12.00 x 24.00 [305 x 305 x 610]	PDF
T121236CH	\$782.00	12.00 x 12.00 x 36.00 [305 x 305 x 914]	PDF
T121248CH	\$988.00	12.00 x 12.00 x 48.00 [305 x 305 x 1219]	PDF

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].



[T2212CH](#)

NEMA 4 Hinged Cover Wiring Trough



Dimensions

