

# NEMA 4 Hinged Cover Wiring Trough



## Applications

Designed to protect internal components and wiring from dust, dirt, and water. This trough can be used indoors or outdoors, as well as in corrosive environments.

## Construction

- Trough and cover fabricated from carbon steel
- Polyester powder coat
- Seams are continuously-welded and ground smooth
- External clamps and continuous hinge provided
- External mounting feet included
- Cover is sealed with poured-in-place gasket

## Listings

- UL 870 1, 4, 4X and 12
- IEC 60529, IP66
- UL Files E32576, E470978

Note: For current listings, please see [www.automationdirect.com](http://www.automationdirect.com)



| NEMA 4 Hinged Cover Wiring Trough                                                   |          |                                          |                     |
|-------------------------------------------------------------------------------------|----------|------------------------------------------|---------------------|
| Carbon Steel                                                                        | Price    | Enclosure Overall Size HxWxD             | Drawing Link        |
| <a href="#">T2212CH</a>                                                             | \$197.00 | 2.50 x 2.50 x 12.00 [64 x 64 x 305]      | <a href="#">PDF</a> |
| <a href="#">T2224CH</a>                                                             | \$228.00 | 2.50 x 2.50 x 24.00 [64 x 64 x 610]      | <a href="#">PDF</a> |
| <a href="#">T2236CH</a>                                                             | \$259.00 | 2.50 x 2.50 x 36.00 [64 x 64 x 914]      | <a href="#">PDF</a> |
| <a href="#">T2248CH</a>                                                             | \$279.00 | 2.50 x 2.50 x 48.00 [64 x 64 x 1219]     | <a href="#">PDF</a> |
| <a href="#">T4412CH</a>                                                             | \$229.00 | 4.00 x 4.00 x 12.00 [102 x 102 x 305]    | <a href="#">PDF</a> |
| <a href="#">T4424CH</a>                                                             | \$289.00 | 4.00 x 4.00 x 24.00 [102 x 102 x 610]    | <a href="#">PDF</a> |
| <a href="#">T4436CH</a>                                                             | \$347.00 | 4.00 x 4.00 x 36.00 [102 x 102 x 914]    | <a href="#">PDF</a> |
| <a href="#">T4448CH</a>                                                             | \$419.00 | 4.00 x 4.00 x 48.00 [102 x 102 x 1219]   | <a href="#">PDF</a> |
| <a href="#">T6612CH</a>                                                             | \$272.00 | 6.00 x 6.00 x 12.00 [152 x 152 x 305]    | <a href="#">PDF</a> |
| <a href="#">T6624CH</a>                                                             | \$360.00 | 6.00 x 6.00 x 24.00 [152 x 152 x 610]    | <a href="#">PDF</a> |
| <a href="#">T6636CH</a>                                                             | \$449.00 | 6.00 x 6.00 x 36.00 [152 x 152 x 914]    | <a href="#">PDF</a> |
| <a href="#">T6648CH</a>                                                             | \$538.00 | 6.00 x 6.00 x 48.00 [152 x 152 x 1219]   | <a href="#">PDF</a> |
| <a href="#">T8812CH</a>                                                             | \$328.00 | 8.00 x 8.00 x 12.00 [203 x 203 x 305]    | <a href="#">PDF</a> |
| <a href="#">T8824CH</a>                                                             | \$436.00 | 8.00 x 8.00 x 24.00 [203 x 203 x 610]    | <a href="#">PDF</a> |
| <a href="#">T8836CH</a>                                                             | \$555.00 | 8.00 x 8.00 x 36.00 [203 x 203 x 914]    | <a href="#">PDF</a> |
| <a href="#">T8848CH</a>                                                             | \$693.00 | 8.00 x 8.00 x 48.00 [203 x 203 x 1219]   | <a href="#">PDF</a> |
| <a href="#">T121224CH</a>                                                           | \$605.00 | 12.00 x 12.00 x 24.00 [305 x 305 x 610]  | <a href="#">PDF</a> |
| <a href="#">T121236CH</a>                                                           | \$782.00 | 12.00 x 12.00 x 36.00 [305 x 305 x 914]  | <a href="#">PDF</a> |
| <a href="#">T121248CH</a>                                                           | \$988.00 | 12.00 x 12.00 x 48.00 [305 x 305 x 1219] | <a href="#">PDF</a> |
| Notes: Subpanels must be ordered separately.<br>Dimensions in inches [millimeters]. |          |                                          |                     |



[T2212CH](#)

# NEMA 4 Hinged Cover Wiring Trough



## Dimensions

