

NEMA 4, 12, and 13 Lift-Off Cover Wall-Mount



Applications

Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes or electrical junction boxes. Provides protection where equipment is hosed down, very wet or in outdoor applications.



Construction

- Bodies fabricated from 14-gauge steel; Doors fabricated from 16-gauge steel
- Continuously-welded seams ground smooth
- Poured-in-place polyurethane gasket
- External mounting feet, top and bottom of enclosure
- Weldnuts are provided for mounting optional subpanels securely on models 6 x 4 in [152 x 102 mm] and larger
- Stainless steel screws and clamps on four sides of cover to assure watertight seal
- Optional subpanels and terminal kits must be ordered separately
- Grounding provisions provided
- [Uses WABN4JIC clamp](#)

Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

Listings

- UL 50, 4, 12, and 13
- UL 508, 4, 12 and 13 [UL Files E23553, E64791]
- NEMA/EEMAC 4, 12, and 13

Note: For current listings, please see www.automationdirect.com



Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.


NEMA 4, 12, and 13 Lift-Off Cover Wall-Mount

Part Number	Price	Enclosure SizeHxWxD	Painted Steel Subpanel	Stainless Steel Subpanel
BN4040403	\$60.00	4.31 x 4.31 x 3.16 [109 x 109 x 80]	—	—
BN4060403	\$68.00	6.31 x 4.31 x 3.16 [160 x 109 x 80]	P0604	P0604SS
BN4060604	\$80.00	6.31 x 6.31 x 4.16 [160 x 160 x 106]	P0606	P0606SS
BN4080603	\$84.00	8.31 x 6.31 x 3.16 [211 x 160 x 80]	P0806	P0806SS
BN4100804	\$105.00	10.31 x 8.31 x 4.16 [262 x 211 x 106]	P1008	P1008SS
BN4121005	\$134.00	12.31 x 10.31 x 5.16 [313 x 262 x 131]	P1210	P1210SS
BN4141206	\$170.00	14.31 x 12.31 x 6.16 [363 x 313 x 156]	P1412	P1412SS
BN4161406	\$199.00	16.31 x 14.31 x 6.16 [414 x 363 x 156]	P1614	P1614SS

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].

NEMA 4, 12, and 13 Lift-Off Cover Wall-Mount

Dimensions



Enclosure Subpanels



Subpanels

Subpanels are not included with most enclosures and must be purchased separately.

The specifications table for each enclosure family list the part number of the subpanel that goes with each enclosure.

Subpanels for Small NEMA 12 (B) and NEMA 4 (BN4) Enclosures

- 14-gauge (painted, stainless, and galvanized)
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels fit the following enclosures: B, B_CH, BN4, BN4_CH, BN4_CHQT, BN4_SS, BN4_CHSS, BN4_CHSSA, BN4_CHQTSS, BN4_CHQTSSA ("_" refers to dimensions).



Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
Color indicates shipping lead time in business days.				

Subpanels for B and BN4 Enclosures					
Painted Steel	Price	304 Stainless Steel	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
P0604	\$5.00	P0604SS	\$16.75	6 x 4	4.88 x 2.88 [124 x 73]
P0606	\$6.00	P0606SS	\$20.50	6 x 6	4.88 x 4.88 [124 x 124]
P0806	\$6.75	P0806SS	\$24.50	8 x 6	6.88 x 4.88 [175 x 124]
P0808	\$8.00	—	—	8 x 8	6.88 x 6.88 [175 x 175]
P1008	\$8.75	P1008SS	\$35.50	10 x 8	8.88 x 6.88 [226 x 175]
P1010	\$11.00	—	—	10 x 10	8.88 x 8.88 [226 x 226]
P1206	\$8.75	—	—	12 x 6	10.88 x 4.88 [276 x 124]
P1210	\$12.75	P1210SS	\$50.00	12 x 10	10.88 x 8.88 [276 x 226]
P1212	\$15.00	P1212SS	\$58.00	12 x 12	10.88 x 10.88 [276 x 276]
P1408	\$12.00	—	—	14 x 8	12.88 x 6.88 [327 x 175]
P1412	\$16.50	P1412SS	\$67.00	14 x 12	12.88 x 10.88 [327 x 276]
P1610	\$16.25	—	—	16 x 10	14.88 x 8.88 [378 x 226]
P1614	\$22.00	P1614SS	\$88.00	16 x 14	14.88 x 12.88 [378 x 327]

Notes: Dimensions in inches [millimeters].
Letters in table correspond to letters on dimensional drawing.

Dimensions

