


# prosense® RTD Flange Mount Probes



**RTD1-F12L06-01**

## Overview

- Ideal for use with ovens, freezers, ducts, or anywhere through the wall temperature sensing is required.
- 100 ohm platinum RTD 3-wire element
- Class A accuracy
- 1/4" diameter, 316 SS sheath to protect against harsh environments
- 6", 12", or 18" probe lengths
- Mounting is accomplished using the conveniently attached round mounting flange
- 6-foot lead wires with stainless steel overbraid
- Made in the USA

## RTD Flange Mount Probes

Part Number	Pcs/Pkg	Wt (lb)	Price	Type	Probe Insertion Length	Probe Material	Temperature Sensing Range	Mounting
<a href="#">RTD1-F06L06-01</a>	1	0.44	\$78.00	PT 100, Class A, 3-wire	6"	316 stainless steel	-40 to 316°C (-40 to 600°F)	1" diameter 1/16" thick 304 stainless steel flange (2x - ø0.144" mounting holes 0.75" spacing)
<a href="#">RTD1-F12L06-01</a>	1	0.44	\$80.00		12"			
<a href="#">RTD1-F18L06-01</a>	1	0.44	\$82.00		18"			

## Technical Specifications

<b>Sensing Element</b>	Single 100Ω platinum (Pt 100), 3-wire; TCR = 0.00385Ω/Ω/°C
<b>Initial Accuracy</b>	Class A $\pm[0.15 + 0.002  t ]$ °C
<b>Probe</b>	1/4" O.D., 316 stainless steel sheath
<b>Minimum Installation Depth</b>	3" (76mm)
<b>Probe Minimum Bend Radius</b>	Not bendable
<b>Response Time</b>	7 seconds, 63% of a 25 to 77°C step change (ASTM E1137)
<b>Wiring</b>	6 foot stranded 24 AWG wire leads with stripped ends, Kapton insulation and stainless steel overbraid



*Note: Check the chemical compatibility of the sensor's wetted parts with the medium to be measured.*

## Dimensions

inches [mm]

RTD1-FXXL06-01





TABLE A	
PART NUMBER	DIM "A"
RTD1-F06L06-01	6.00[152.4]
RTD1-F12L06-01	12.00[304.8]
RTD1-F18L06-01	18.00[457.2]

## Wiring Information



# prosense® RTD Flange Mount Probe - Accessories

## Accessories

<b>Part No.</b>	<b>Description</b>	<b>Pcs/Pkg</b>	<b>Price</b>
<b><u>RTD-SP</u></b>	RTD 3-pin connector, standard round pin plug, maximum continuous temperature 400°F (200°C), white body, copper pins, 14 AWG maximum (2.0 mm) wire size	1	\$9.25
<b><u>RTD-SJ</u></b>	RTD 3-pin connector, standard round pin jack, maximum continuous temperature 400°F (200°C), white body, copper pins, 14 AWG maximum (2.0 mm) wire size	1	\$12.00
<b><u>WCB-S</u></b>	Wire / cable clamp bracket for use with standard thermocouple and RTD connectors	4	\$12.00

**Note:** RTD extension lead wire available at [www.automationdirect.com](http://www.automationdirect.com)

See end of section for full listing of accessories and dimension information.

**RTD-SJ**

**RTD-SP**



**RTD Connectors**