

OKK Series Swing Panels



Application

Provides an interior mounting surface just behind the exterior door. Panel can swing open to allow access to the interior of the enclosure.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Features

- Includes hinges, screws, and bolts
- Zinc alloy corner pieces.

Listings

- IP44



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



Swing Panels			
Part Number	Price	Fits Enclosure Size HxW	Drawing Link
<u>DBI188</u>	\$259.00	1800 x 800 [70.87 x 31.50]	<u>PDF</u>
<u>DBI18A</u>	\$304.00	1800 x 1000 [70.87 x 39.37]	<u>PDF</u>
<u>DBI208</u>	\$297.00	2000 x 800 [78.74 x 31.50]	<u>PDF</u>
<u>DBI20A</u>	\$344.00	2000 x 1000 [78.74 x 39.37]	<u>PDF</u>
Note: Dimensions in millimeters [inches]. Swing panels kits consist of a panel and a mounting frame; each packaged separately.			



OKK Series Accessories

Galvanized Steel Mounting Channels

Application

Mounting channels can be used to create additional mounting positions at any location inside the enclosure. They can be connected to the inner frame of the enclosure or span between other mounting channels in either a vertical or horizontal orientation.

Features

- Available with a flanged end or a closed end.
 - Either may work depending on the mounting location and orientation.
- Includes pre-punched holes to accept M6 cage nuts and M5 self-threading screws.

Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



Flanged Mounting Channels		
Part Number	Price	For Use with Width/Depth Enclosures
<u>STK445</u>	\$14.00	400.00 x 0.00 [10160]
<u>STK645</u>	\$16.75	600.00 x 0.00 [15240]
<u>STK845</u>	\$18.00	800.00 x 0.00 [20320]
<u>STKA45</u>	\$23.00	1000.00 x 0.00 [25400]
Note: Dimensions in millimeters [inches].		



Closed-End Mounting Channels		
Part Number	Price	For Use with Width/Depth Enclosures
<u>SCK407</u>	\$14.00	400.00 x 0.00 [10160]
<u>SCK607</u>	\$16.75	600.00 x 0.00 [15240]
<u>SCK807</u>	\$18.00	800.00 x 0.00 [20320]
<u>SCKA07</u>	\$23.00	1000.00 x 0.00 [25400]
<u>SCKC07</u>	\$27.50	1200.00 x 0.00 [30480]
Note: Dimensions in millimeters [inches].		





OKK Series Accessories

Folding Desk

Features

- Mounting hardware included
- Installs inside or outside of enclosure.

Folding Desk			
Part Number	Price	Size HxW	Drawing Link
CSTK70	\$396.00	539 x 352 [21.22 x 13.86]	PDF
Note: Dimensions in millimeters [inches].			

Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



OKK Series Accessories



Baying Hardware Kit

Application

Baying kit is used to connect two or more enclosure bays together to form a single multi-door enclosure. Fits all sizes of OKK Series enclosures.

Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



Baying Hardware Kit		
Part Number	Price	Includes
UTK700	\$30.50	Brackets, gaskets, and fasteners



Filler Plates

Application

Used to fill the gap between the subpanels or roof plates of two joined enclosure bays. Not required for all applications.

Features

Mounting hardware included.

Subpanel Filler Plates				
Part Number	Price	Fits Enclosure Height	Description	Drawing Link
FUP188	\$79.00	1800 [70.87]	Quadritalia OKK Series subpanel filler plate, galvanized steel.	PDF
FUP208	\$87.00	2000 [78.74]		PDF

Note: Dimensions in millimeters [inches].



Roof Filler Plates				
Part Number	Price	Fits Enclosures Depth	Description	Drawing Link
TTP040	\$9.75	400 [15.75]	Quadritalia OKK Series roof panel filler plate, carbon steel, RAL 7035 light gray, textured powder coat finish.	PDF
TTP060	\$10.25	600 [23.62]		PDF
TTP080	\$12.25	800 [31.50]		PDF

Note: Dimensions in millimeters [inches].





OKK Series Accessories

Subpanel Mounting Hardware Kits

Application

PPK100 is included with each subpanel and is used to mount the subpanel within the enclosure.

Subpanel Mounting Hardware Kits		
Part Number	Price	Includes
PPK100	\$39.00	Brackets, sliders, conic pins, and fasteners included.



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



Application

APK110 allows the subpanel to be recess mounted flush within the frame rails of the enclosure for maximizing interior space, for side-mounting subpanels, or to form a barrier between adjacent bays.

Subpanel Mounting Hardware Kits		
Part Number	Price	Includes
APK110	\$15.25	Brackets, sliders, conic pins, and fasteners included.



OKK Series Accessories



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



Cage Nuts			
Part Number	Price	Description	Qty
<u>DGM800</u>	\$58.00	M8 cage nut	100
<u>DGM600</u>	\$30.50	M6 zinc plated finish cage nut	100
<u>DGM901</u>	\$36.00	M6 outdoor cage nut	100



Screws			
Part Number	Price	Description	Qty
<u>VTR616</u>	\$26.50	M6 x 16mm, hex head flanged screw	100
<u>VTC122</u>	\$73.00	screw, M12 x 20mm, 8mm Allen	100
<u>VBC614</u>	\$31.50	M6 x 14mm T30 Torx head screw	100
<u>VTS616</u>	\$32.00	M6 x 16mm T30 Torx pan head screw	100
<u>VBC616</u>	\$31.00	M6 x 16mm T30 Torx head screw	100



OKK Series Accessories



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

[Configuration Tool](#)



Latch Handle			
Part Number	Price	Description	Drawing Link
SRR773B	\$81.00	Quadritalia enclosure latch handle, replacement, keylocking, foldaway. (1) Yale-type key included.	PDF



[GLF812-K4](#)

Eyebolts and Lifting Lugs				
Part Number	Price	Description	Qty	Drawing Link
GLF812-K4	\$29.00	Quadritalia eyebolt, M12 x 1.5mm x 22mm, galvanized steel.	4	PDF
GLP830	\$34.50	Quadritalia bolt-on lifting lug, galvanized steel.	1	



[GLP830](#)

Application

Mounting clips are used to attach side and rear panels to the vertical rails.

* Assembly requires a T30 bit.

Mounting Clips			
Part Number	Price	Includes	Qty
CLK013-KIT2F	\$43.50	M6 hex nut and gasket included	12

