

OKK Series Base and Roof Sets



Application

Each set provides the base and roof for one OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Vertical frame rail set
- Exterior side panels
- Door
- Exterior rear panel or additional door
- Subpanel

Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



Features

- Bases have removable flanges for easy cable and wire entry.
- Roof bolts can be replaced with eyebolts (GLF812-K4 for enclosure lifting).
- Base is compatible with [OKK Series Plinth Kits](#) for cable ingress and management.
- Vertical rails are connected with included hardware.

**Assembly requires a T30 bit.*

Material and Finish

- Sendzimir galvanized frame rails
- Zamak corner joints
- Exterior portions are RAL7035 light gray textured powder coat finish

Listings

- Fully-assembled OKK Series Enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with
 - NEMA Type 12
 - IEC EN60529 IP55



Base and Roof Sets			
Part Number	Price	Enclosure Size WxD	Drawing Link
OKKTB6040	\$278.00	600 x 400 [23.62 x 15.75]	PDF
OKKTB6080	\$364.00	600 x 600 [23.62 x 23.62]	PDF
OKKTB6060	\$469.00	600 x 800 [23.62 x 31.50]	PDF
OKKTB8040	\$325.00	800 x 400 [31.50 x 15.75]	PDF
OKKTB8060	\$367.00	800 x 600 [31.50 x 23.62]	PDF
OKKTB8080	\$478.00	800 x 800 [31.50 x 31.50]	PDF
OKKTB1040	\$346.00	1000 x 400 [39.37 x 15.75]	PDF
OKKTB1060	\$398.00	1000 x 600 [39.37 x 23.62]	PDF
OKKTB1080	\$524.00	1000 x 800 [39.37 x 31.50]	PDF
OKKTB1240	\$492.00	1200 x 400 [47.24 x 15.75]	PDF
OKKTB1260	\$544.00	1200 x 600 [47.24 x 23.62]	PDF
OKKTB1280	\$700.00	1200 x 800 [47.24 x 31.50]	PDF

Note: Dimensions in millimeters [inches].