

# OKK Series Base and Roof Sets



## Application

Each set provides the base and roof for one OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Vertical frame rail set
- Exterior side panels
- Door
- Exterior rear panel or additional door
- Subpanel

Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

## Configuration Tool



## Features

- Bases have removable flanges for easy cable and wire entry.
- Roof bolts can be replaced with eyebolts (GLF812-K4 for enclosure lifting).
- Base is compatible with [OKK Series Plinth Kits](#) for cable ingress and management.
- Vertical rails are connected with included hardware.

*\*Assembly requires a T30 bit.*

## Material and Finish

- Sendzimir galvanized frame rails
- Zamak corner joints
- Exterior portions are RAL7035 light gray textured powder coat finish

## Listings

- Fully-assembled OKK Series Enclosures are rated as follows:
  - UL 508a Type 12 [UL File E503249]
  - CSA Type 12 [CSA File 115232]
- Complies with
  - NEMA Type 12
  - IEC EN60529 IP55



Base and Roof Sets			
Part Number	Price	Enclosure Size WxD	Drawing Link
<a href="#">OKKTB6040</a>	\$278.00	600 x 400 [23.62 x 15.75]	<a href="#">PDF</a>
<a href="#">OKKTB6080</a>	\$364.00	600 x 600 [23.62 x 23.62]	<a href="#">PDF</a>
<a href="#">OKKTB6060</a>	\$469.00	600 x 800 [23.62 x 31.50]	<a href="#">PDF</a>
<a href="#">OKKTB8040</a>	\$325.00	800 x 400 [31.50 x 15.75]	<a href="#">PDF</a>
<a href="#">OKKTB8060</a>	\$367.00	800 x 600 [31.50 x 23.62]	<a href="#">PDF</a>
<a href="#">OKKTB8080</a>	\$478.00	800 x 800 [31.50 x 31.50]	<a href="#">PDF</a>
<a href="#">OKKTB1040</a>	\$346.00	1000 x 400 [39.37 x 15.75]	<a href="#">PDF</a>
<a href="#">OKKTB1060</a>	\$398.00	1000 x 600 [39.37 x 23.62]	<a href="#">PDF</a>
<a href="#">OKKTB1080</a>	\$524.00	1000 x 800 [39.37 x 31.50]	<a href="#">PDF</a>
<a href="#">OKKTB1240</a>	\$492.00	1200 x 400 [47.24 x 15.75]	<a href="#">PDF</a>
<a href="#">OKKTB1260</a>	\$544.00	1200 x 600 [47.24 x 23.62]	<a href="#">PDF</a>
<a href="#">OKKTB1280</a>	\$700.00	1200 x 800 [47.24 x 31.50]	<a href="#">PDF</a>

Note: Dimensions in millimeters [inches].



# OKK Series Enclosure Rails

## Application

Each set provides the vertical structure for one OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Base and roof set
- Exterior side panels
- Door
- Exterior rear panel or additional door
- Subpanel

Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

## Configuration Tool



## Features

- Package includes four rails.
- Pre-punched holes on interior surfaces accept M6 cage nuts and M5 self-threading screws.

## Material

- Sendzimir galvanized steel

## Listings

- Fully-assembled OKK Series Enclosure is rated:
  - UL 508a Type 12 [UL File E503249]
  - CSA Type 12 [CSA File 115232]
- Complies with
  - NEMA Type 12
  - IEC EN60529 IP55



OKK Series Enclosure Rails				
Part Number	Price	Qty	Enclosure Height	Drawing Link
<a href="#">MTK180-4</a>	\$215.00	4	1800 [70.87]	<a href="#">PDF</a>
<a href="#">MTK200-4</a>	\$235.00	4	2000 [78.74]	<a href="#">PDF</a>
Note: Dimensions in millimeters [inches].				

# OKK Series Side Exterior Panels



## Application

Each exterior panel provides two side exterior surfaces for an OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Base and roof set
- Vertical frame rail set
- Door
- Exterior rear panel or additional door
- Subpanel

Multiple enclosure extensions bayed together can be sealed with a single set of side panels.

## Material

- 1.5 mm carbon steel

## Finish

- RAL 7035 light gray
- Textured powder coat finish

## Features

- Package of two side panels
- Poured-in-place polyurethane gasket
- Includes mounting clips, screws, and gaskets (CLK013-KIT2F)

## Listings

- Fully-assembled OKK Series Enclosures are rated as follows:
  - UL 508a Type 12 [UL File E503249]
  - CSA Type 12 [CSA File 115232]
- Complies with the following:
  - NEMA Type 12
  - IEC EN60529 IP55



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

### Configuration Tool



Side Exterior Panels			
Part Number	Price	Fits Enclosure Size HxD	Drawing Link
<a href="#">DLK184</a>	\$79.00	1800 x 400 [70.87 x 15.75]	<a href="#">PDF</a>
<a href="#">DLK186</a>	\$113.00	1800 x 600 [70.87 x 23.62]	<a href="#">PDF</a>
<a href="#">DLK188</a>	\$151.00	1800 x 800 [70.87 x 31.50]	<a href="#">PDF</a>
<a href="#">DLK204</a>	\$86.00	2000 x 400 [78.74 x 15.75]	<a href="#">PDF</a>
<a href="#">DLK206</a>	\$123.00	2000 x 600 [78.74 x 23.62]	<a href="#">PDF</a>
<a href="#">DLK208</a>	\$160.00	2000 x 800 [78.74 x 31.50]	<a href="#">PDF</a>
Note: Dimensions in millimeters [inches].			

# OKK Series Rear Exterior Panels



## Application

Each rear exterior panel provides the rear surface for one OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Base and roof set
- Vertical frame rail set
- Exterior side panels
- Door
- Subpanel

An additional door may be used in lieu of a rear exterior panel to create a dual access enclosure.

Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

## Configuration Tool



## Material

- 2.0 mm carbon steel

## Finish

- RAL 7035 light gray
- Textured powder coat finish

## Features

- Poured-in-place polyurethane gasket
- Includes mounting clips, screws, and gaskets (CLK013-KIT2F)

## Listings

- Fully-assembled OKK Series Enclosures are rated as follows:
  - UL 508a Type 12 [UL File E503249]
  - CSA Type 12 [CSA File 115232]
- Complies with the following:
  - NEMA Type 12
  - EC EN60529 IP55



Rear Exterior Panels			
Part Number	Price	Fits Enclosure Size HxW	Drawing Link
<a href="#">RPE186</a>	\$86.00	1800 x 600 [70.87 x 23.62]	<a href="#">PDF</a>
<a href="#">RPE188</a>	\$107.00	1800 x 800 [70.87 x 31.50]	<a href="#">PDF</a>
<a href="#">RPE18A</a>	\$127.00	1800 x 1000 [70.87 x 39.37]	<a href="#">PDF</a>
<a href="#">RPE18C</a>	\$147.00	1800 x 1200 [70.87 x 47.24]	<a href="#">PDF</a>
<a href="#">RPE206</a>	\$104.00	2000 x 600 [78.74 x 23.62]	<a href="#">PDF</a>
<a href="#">RPE208</a>	\$119.00	2000 x 800 [78.74 x 31.50]	<a href="#">PDF</a>
<a href="#">RPE20A</a>	\$134.00	2000 x 1000 [78.74 x 39.37]	<a href="#">PDF</a>
<a href="#">RPE20C</a>	\$156.00	2000 x 1200 [78.74 x 47.24]	<a href="#">PDF</a>
Note: Dimensions in millimeters [inches].			

# OKK Series Doors



## Application

Each door provides interior access to an OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Base and roof set
- Vertical frame rail set
- Exterior side panels
- Exterior rear panel or additional door
- Subpanel

## Material

- 2.0 mm carbon steel

## Finish

- RAL 7035 light gray
- Textured powder coat finish

## Features

- Fully reversible (handle can be oriented on the left or right side)
- 120° opening
- Four hinges
- 3.0mm double-bar 4-point latch with double-bit key
- Poured-in-place two-component polyurethane gasket, foamed on a perimeter external to the latch points
- Doors include a Sendzimir galvanized inner stiffening frame with Zamak zinc alloy corner pieces.

## Listings

- Fully-assembled OKK Series Enclosures are rated as follows:
  - UL 508a Type 12 [UL File E503249]
  - CSA Type 12 [CSA File 115232]
- Complies with the following:
  - NEMA Type 12
  - IEC EN60529 IP55



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

## Configuration Tool



Single-Door			
Part Number	Price	Size HxW	Drawing Link
<a href="#">DBE186</a>	\$199.00	1800 x 600 [70.87 x 23.62]	<a href="#">PDF</a>
<a href="#">DBE188</a>	\$239.00	1800 x 800 [70.87 x 31.50]	<a href="#">PDF</a>
<a href="#">DBE18A</a>	\$257.00	1800 x 1000 [70.87 x 39.37]	<a href="#">PDF</a>
<a href="#">DBE206</a>	\$214.00	2000 x 600 [78.74 x 23.62]	<a href="#">PDF</a>
<a href="#">DBE208</a>	\$255.00	2000 x 800 [78.74 x 31.50]	<a href="#">PDF</a>
<a href="#">DBE20A</a>	\$290.00	2000 x 1000 [78.74 x 39.37]	<a href="#">PDF</a>
Note: Dimensions in millimeters [inches].			

Double-Door			
Part Number	Price	Size HxW	Drawing Link
<a href="#">DBE18C</a>	\$328.00	1800 x 1200 [70.87 x 47.24]	<a href="#">PDF</a>
<a href="#">DBE20C</a>	\$352.00	2000 x 1200 [78.74 x 47.24]	<a href="#">PDF</a>
Note: Dimensions in millimeters [inches]. Double-door sets consist of a master door and slave door which are packaged separately.			

# OKK Series Doors with Window



## Application

Each door provides interior access to an OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Base and roof set
- Vertical frame rail set
- Exterior side panels
- Exterior rear panel or additional door
- Subpanel

## Material

- 2.0 mm carbon steel
- 4.0 mm acrylic window

## Finish

- RAL 7035 light gray
- Textured powder coat finish

## Features

- Fully reversible
- 120° opening
- Four hinges
- 3.0mm double-bar 4-point latch with double-bit key
- Poured-in-place two-component polyurethane gasket, foamed on a perimeter external to the latch points
- Doors include a Sendzimir galvanized inner stiffening frame with Zamak zinc alloy corner pieces.

## Listings

- Fully-assembled OKK Series Enclosures are rated as follows:
  - UL 508a Type 12 [UL File E503249]
  - CSA Type 12 [CSA File 115232]
- Complies with the following:
  - NEMA Type 12
  - IEC EN60529 IP55



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

## Configuration Tool



Doors with Window			
Part Number	Price	Size HxWxD	Drawing Link
<a href="#">DTE188</a>	\$451.00	1800 x 800 [70.87 x 31.50]	<a href="#">PDF</a>
<a href="#">DTE18A</a>	\$529.00	1800 x 1000 [70.87 x 39.37]	<a href="#">PDF</a>
<a href="#">DTE208</a>	\$509.00	2000 x 800 [78.74 x 31.50]	<a href="#">PDF</a>
<a href="#">DTE20A</a>	\$596.00	2000 x 1000 [78.74 x 39.37]	<a href="#">PDF</a>
Note: Dimensions in millimeters [inches].			

# OKK Series Subpanels



## Application

Provides the primary subpanel for an OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Base and roof set
- Vertical frame rail set
- Exterior side panels
- Door
- Exterior rear panel or additional door

Subpanel can be mounted at variable depths or flush mounted. Multiple subpanels can be used in a Dual access enclosure.

Subpanels may also be recess mounted on one or both sides for use as side-mounted panels or to form a barrier between two adjacent bays. For side-mount applications, match subpanel nominal width to enclosure depth.

*APK110 (sold separately) required for all recess mounting applications*

## Material

- 2.5 mm Sendzimir galvanized steel

## Features

- Includes installation hardware ([PPK100](#)).

Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

### Configuration Tool



Subpanels			
Part Number	Price	Fits Enclosure Size HxW	Drawing Link
<a href="#">PNA186</a>	\$95.00	1800 x 600 [70.87 x 23.62]	<a href="#">PDF</a>
<a href="#">PNA188</a>	\$110.00	1800 x 800 [70.87 x 31.50]	<a href="#">PDF</a>
<a href="#">PNA18A</a>	\$126.00	1800 x 1000 [70.87 x 39.37]	<a href="#">PDF</a>
<a href="#">PNA18C</a>	\$145.00	1800 x 1200 [70.87 x 47.24]	<a href="#">PDF</a>
<a href="#">PNA206</a>	\$108.00	2000 x 600 [78.74 x 23.62]	<a href="#">PDF</a>
<a href="#">PNA208</a>	\$133.00	2000 x 800 [78.74 x 31.50]	<a href="#">PDF</a>
<a href="#">PNA20A</a>	\$154.00	2000 x 1000 [78.74 x 39.37]	<a href="#">PDF</a>
<a href="#">PNA20C</a>	\$179.00	2000 x 1200 [78.74 x 47.24]	<a href="#">PDF</a>
Note: Dimensions in millimeters [inches].			