



OKK Series Enclosure Kit – NEMA 12 Freestanding Single-Door



Description

Each OKK Series enclosure kit contains all the components required to assemble one complete enclosure.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Enclosure Kit – NEMA12 Freestanding Single-Door

Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-E180604CSBF	\$845.00	1800 x 600 x 400 [70.87 x 23.62 x 15.75]	(1) MTK180-4, (1) OKKTB6040, (1) PNA186, (1) DBE186, (1) RPE186 and (1) DLK184	PDF
QTA-E180606CSBF	\$957.00	1800 x 600 x 600 [70.87 x 23.62 x 23.62]	(1) MTK180-4, (1) OKKTB6060, (1) PNA186, (1) DBE186, (1) RPE186 and (1) DLK186	PDF
QTA-E180608CSBF	\$1,091.00	1800 x 600 x 800 [70.87 x 23.62 x 31.50]	(1) MTK180-4, (1) OKKTB6080, (1) PNA186, (1) DBE186, (1) RPE186 and (1) DLK188	PDF
QTA-E180804CSBF	\$958.00	1800 x 800 x 400 [70.87 x 31.50 x 15.75]	(1) MTK180-4, (1) OKKTB8040, (1) PNA188, (1) DBE188, (1) RPE188 and (1) DLK184	PDF
QTA-E180806CSBF	\$1,029.00	1800 x 800 x 600 [70.87 x 31.50 x 23.62]	(1) MTK180-4, (1) OKKTB8060, (1) PNA188, (1) DBE188, (1) RPE188 and (1) DLK186	PDF
QTA-E180808CSBF	\$1,169.00	1800 x 800 x 800 [70.87 x 31.50 x 31.50]	(1) MTK180-4, (1) OKKTB8080, (1) PNA188, (1) DBE188, (1) RPE188 and (1) DLK188	PDF
QTA-E181004CSBF	\$1,030.00	1800 x 1000 x 400 [70.87 x 39.37 x 15.75]	(1) MTK180-4, (1) OKKTB1040, (1) PNA18A, (1) DBE18A, (1) RPE18A and (1) DLK184	PDF
QTA-E181006CSBF	\$1,110.00	1800 x 1000 x 600 [70.87 x 39.37 x 23.62]	(1) MTK180-4, (1) OKKTB1060, (1) PNA18A, (1) DBE18A, (1) RPE18A and (1) DLK186	PDF
QTA-E181008CSBF	\$1,264.00	1800 x 1000 x 800 [70.87 x 39.37 x 31.50]	(1) MTK180-4, (1) OKKTB1080, (1) PNA18A, (1) DBE18A, (1) RPE18A and (1) DLK188	PDF
QTA-E200604CSBF	\$960.00	2000 x 600 x 400 [78.74 x 23.62 x 15.75]	(1) MTK200-4, (1) OKKTB6040, (1) PNA206, (1) DBE206, (1) RPE206 and (1) DLK204	PDF
QTA-E200606CSBF	\$1,076.00	2000 x 600 x 600 [78.74 x 23.62 x 23.62]	(1) MTK200-4, (1) OKKTB6060, (1) PNA206, (1) DBE206, (1) RPE206 and (1) DLK206	PDF
QTA-E200608CSBF	\$1,210.00	2000 x 600 x 800 [78.74 x 23.62 x 31.50]	(1) MTK200-4, (1) OKKTB6080, (1) PNA206, (1) DBE206, (1) RPE206 and (1) DLK208	PDF
QTA-E200804CSBF	\$1,078.00	2000 x 800 x 400 [78.74 x 31.50 x 15.75]	(1) MTK200-4, (1) OKKTB8040, (1) PNA208, (1) DBE208, (1) RPE208 and (1) DLK204	PDF
QTA-E200806CSBF	\$1,153.00	2000 x 800 x 600 [78.74 x 31.50 x 23.62]	(1) MTK200-4, (1) OKKTB8060, (1) PNA208, (1) DBE208, (1) RPE208 and (1) DLK206	PDF
QTA-E200808CSBF	\$1,293.00	2000 x 800 x 800 [78.74 x 31.50 x 31.50]	(1) MTK200-4, (1) OKKTB8080, (1) PNA208, (1) DBE208, (1) RPE208 and (1) DLK208	PDF
QTA-E201004CSBF	\$1,165.00	2000 x 1000 x 400 [78.74 x 39.37 x 15.75]	(1) MTK200-4, (1) OKKTB1040, (1) PNA20A, (1) DBE20A, (1) RPE20A and (1) DLK204	PDF
QTA-E201006CSBF	\$1,249.00	2000 x 1000 x 600 [78.74 x 39.37 x 23.62]	(1) MTK200-4, (1) OKKTB1060, (1) PNA20A, (1) DBE20A, (1) RPE20A and (1) DLK206	PDF
QTA-E201008CSBF	\$1,403.00	2000 x 1000 x 800 [78.74 x 39.37 x 31.50]	(1) MTK200-4, (1) OKKTB1080, (1) PNA20A, (1) DBE20A, (1) RPE20A and (1) DLK208	PDF

Note: Dimensions in millimeters [inches].



OKK Series Enclosure Kit – NEMA 12 Freestanding Double-Door



Description

Each OKK Series enclosure kit contains all the components required to assemble one complete enclosure.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

[Configuration Tool](#)



View assembly guide with the link button or QR code below:

[Assembly Guide](#)



OKK Series Enclosure Kit – NEMA12 Freestanding Double-Door

Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-E181204CDBF	\$1,267.00	1800 x 1200 x 400 [70.87 x 47.24 x 15.75]	(1) MTK180-4, (1) OKKTB1240, (1) PNA18C, (1) DBE18C, (1) RPE18C and (1) DLK184	PDF
QTA-E181206CDBF	\$1,348.00	1800 x 1200 x 600 [70.87 x 47.24 x 23.62]	(1) MTK180-4, (1) OKKTB1260, (1) PNA18C, (1) DBE18C, (1) RPE18C and (1) DLK186	PDF
QTA-E181208CDBF	\$1,530.00	1800 x 1200 x 800 [70.87 x 47.24 x 31.50]	(1) MTK180-4, (1) OKKTB1280, (1) PNA18C, (1) DBE18C, (1) RPE18C and (1) DLK188	PDF
QTA-E201204CDBF	\$1,403.00	2000 x 1200 x 400 [78.74 x 47.24 x 15.75]	(1) MTK200-4, (1) OKKTB1240, (1) PNA20C, (1) DBE20C, (1) RPE20C and (1) DLK204	PDF
QTA-E201206CDBF	\$1,488.00	2000 x 1200 x 600 [78.74 x 47.24 x 23.62]	(1) MTK200-4, (1) OKKTB1260, (1) PNA20C, (1) DBE20C, (1) RPE20C and (1) DLK206	PDF
QTA-E201208CDBF	\$1,670.00	2000 x 1200 x 800 [78.74 x 47.24 x 31.50]	(1) MTK200-4, (1) OKKTB1280, (1) PNA20C, (1) DBE20C, (1) RPE20C and (1) DLK208	PDF

Note: Dimensions in millimeters [inches].



OKK Series Enclosure Kit – NEMA 12 Freestanding Single-Door with Window



Description

Each OKK Series enclosure kit contains all the components required to assemble one complete enclosure.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel
- 4.0 mm acrylic window

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Enclosure Kit – NEMA12 Freestanding Single-Door with Window

Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-E180804CSWF	\$1,156.00	1800 x 800 x 400 [70.87 x 31.50 x 15.75]	(1) MTK180-4, (1) OKKTB8040, (1) PNA188, (1) DTE188, (1) RPE188 and (1) DLK184	PDF
QTA-E180806CSWF	\$1,227.00	1800 x 800 x 600 [70.87 x 31.50 x 23.62]	(1) MTK180-4, (1) OKKTB8060, (1) PNA188, (1) DTE188, (1) RPE188 and (1) DLK186	PDF
QTA-E180808CSWF	\$1,367.00	1800 x 800 x 800 [70.87 x 31.50 x 31.50]	(1) MTK180-4, (1) OKKTB8080, (1) PNA188, (1) DTE188, (1) RPE188 and (1) DLK188	PDF
QTA-E181004CSWF	\$1,284.00	1800 x 1000 x 400 [70.87 x 39.37 x 15.75]	(1) MTK180-4, (1) OKKTB1040, (1) PNA18A, (1) DTE18A, (1) RPE18A and (1) DLK184	PDF
QTA-E181006CSWF	\$1,364.00	1800 x 1000 x 600 [70.87 x 39.37 x 23.62]	(1) MTK180-4, (1) OKKTB1060, (1) PNA18A, (1) DTE18A, (1) RPE18A and (1) DLK186	PDF
QTA-E181008CSWF	\$1,518.00	1800 x 1000 x 800 [70.87 x 39.37 x 31.50]	(1) MTK180-4, (1) OKKTB1080, (1) PNA18A, (1) DTE18A, (1) RPE18A and (1) DLK188	PDF
QTA-E200804CSWF	\$1,315.00	2000 x 800 x 400 [78.74 x 31.50 x 15.75]	(1) MTK200-4, (1) OKKTB8040, (1) PNA208, (1) DTE208, (1) RPE208 and (1) DLK204	PDF
QTA-E200806CSWF	\$1,390.00	2000 x 800 x 600 [78.74 x 31.50 x 23.62]	(1) MTK200-4, (1) OKKTB8060, (1) PNA208, (1) DTE208, (1) RPE208 and (1) DLK206	PDF
QTA-E200808CSWF	\$1,530.00	2000 x 800 x 800 [78.74 x 31.50 x 31.50]	(1) MTK200-4, (1) OKKTB8080, (1) PNA208, (1) DTE208, (1) RPE208 and (1) DLK208	PDF
QTA-E201004CSWF	\$1,450.00	2000 x 1000 x 400 [78.74 x 39.37 x 15.75]	(1) MTK200-4, (1) OKKTB1040, (1) PNA20A, (1) DTE20A, (1) RPE20A and (1) DLK204	PDF
QTA-E201006CSWF	\$1,534.00	2000 x 1000 x 600 [78.74 x 39.37 x 23.62]	(1) MTK200-4, (1) OKKTB1060, (1) PNA20A, (1) DTE20A, (1) RPE20A and (1) DLK206	PDF
QTA-E201008CSWF	\$1,688.00	2000 x 1000 x 800 [78.74 x 39.37 x 31.50]	(1) MTK200-4, (1) OKKTB1080, (1) PNA20A, (1) DTE20A, (1) RPE20A and (1) DLK208	PDF

Note: Dimensions in millimeters [inches].



OKK Series Enclosure Kit – NEMA 12 Freestanding Single-Door Dual Access



Description

Each OKK Series enclosure kit contains all the components required to assemble one complete enclosure.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Enclosure Kit – NEMA12 Freestanding Single-Door Dual Access

Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-E180604CSBD	\$1,040.00	1800 x 600 x 400 [70.87 x 23.62 x 15.75]	(1) MTK180-4, (1) OKKTB6040, (2) PNA186, (2) DBE186 and (1) DLK184	PDF
QTA-E180606CSBD	\$1,152.00	1800 x 600 x 600 [70.87 x 23.62 x 23.62]	(1) MTK180-4, (1) OKKTB6060, (2) PNA186, (2) DBE186 and (1) DLK186	PDF
QTA-E180608CSBD	\$1,286.00	1800 x 600 x 800 [70.87 x 23.62 x 31.50]	(1) MTK180-4, (1) OKKTB6080, (2) PNA186, (2) DBE186 and (1) DLK188	PDF
QTA-E180804CSBD	\$1,185.00	1800 x 800 x 400 [70.87 x 31.50 x 15.75]	(1) MTK180-4, (1) OKKTB8040, (2) PNA188, (2) DBE188 and (1) DLK184	PDF
QTA-E180806CSBD	\$1,256.00	1800 x 800 x 600 [70.87 x 31.50 x 23.62]	(1) MTK180-4, (1) OKKTB8060, (2) PNA188, (2) DBE188 and (1) DLK186	PDF
QTA-E180808CSBD	\$1,396.00	1800 x 800 x 800 [70.87 x 31.50 x 31.50]	(1) MTK180-4, (1) OKKTB8080, (2) PNA188, (2) DBE188 and (1) DLK188	PDF
QTA-E181004CSBD	\$1,269.00	1800 x 1000 x 400 [70.87 x 39.37 x 15.75]	(1) MTK180-4, (1) OKKTB1040, (2) PNA18A, (2) DBE18A and (1) DLK184	PDF
QTA-E181006CSBD	\$1,349.00	1800 x 1000 x 600 [70.87 x 39.37 x 23.62]	(1) MTK180-4, (1) OKKTB1060, (2) PNA18A, (2) DBE18A and (1) DLK186	PDF
QTA-E181008CSBD	\$1,503.00	1800 x 1000 x 800 [70.87 x 39.37 x 31.50]	(1) MTK180-4, (1) OKKTB1080, (2) PNA18A, (2) DBE18A and (1) DLK188	PDF
QTA-E200604CSBD	\$1,164.00	2000 x 600 x 400 [78.74 x 23.62 x 15.75]	(1) MTK200-4, (1) OKKTB6040, (2) PNA206, (2) DBE206 and (1) DLK204	PDF
QTA-E200606CSBD	\$1,280.00	2000 x 600 x 600 [78.74 x 23.62 x 23.62]	(1) MTK200-4, (1) OKKTB6060, (2) PNA206, (2) DBE206 and (1) DLK206	PDF
QTA-E200608CSBD	\$1,414.00	2000 x 600 x 800 [78.74 x 23.62 x 31.50]	(1) MTK200-4, (1) OKKTB6080, (2) PNA206, (2) DBE206 and (1) DLK208	PDF
QTA-E200804CSBD	\$1,329.00	2000 x 800 x 400 [78.74 x 31.50 x 15.75]	(1) MTK200-4, (1) OKKTB8040, (2) PNA208, (2) DBE208 and (1) DLK204	PDF
QTA-E200806CSBD	\$1,404.00	2000 x 800 x 600 [78.74 x 31.50 x 23.62]	(1) MTK200-4, (1) OKKTB8060, (2) PNA208, (2) DBE208 and (1) DLK206	PDF
QTA-E200808CSBD	\$1,544.00	2000 x 800 x 800 [78.74 x 31.50 x 31.50]	(1) MTK200-4, (1) OKKTB8080, (2) PNA208, (2) DBE208 and (1) DLK208	PDF
QTA-E201004CSBD	\$1,455.00	2000 x 1000 x 400 [78.74 x 39.37 x 15.75]	(1) MTK200-4, (1) OKKTB1040, (2) PNA20A, (2) DBE20A and (1) DLK204	PDF
QTA-E201006CSBD	\$1,539.00	2000 x 1000 x 600 [78.74 x 39.37 x 23.62]	(1) MTK200-4, (1) OKKTB1060, (2) PNA20A, (2) DBE20A and (1) DLK206	PDF
QTA-E201008CSBD	\$1,693.00	2000 x 1000 x 800 [78.74 x 39.37 x 31.50]	(1) MTK200-4, (1) OKKTB1080, (2) PNA20A, (2) DBE20A and (1) DLK208	PDF

Note: Dimensions in millimeters [inches].



OKK Series Enclosure Kit – NEMA 12 Freestanding Double-Door Dual Access



Description

Each OKK Series enclosure kit contains all the components required to assemble one complete enclosure.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Enclosure Kit – NEMA12 Freestanding Double-Door Dual Access

Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-E181204CDBD	\$1,571.00	1800 x 1200 x 400 [70.87 x 47.24 x 15.75]	(1) MTK180-4, (1) OKKTB1240, (2) PNA18C, (2) DBE18C and (1) DLK184	PDF
QTA-E181206CDBD	\$1,652.00	1800 x 1200 x 600 [70.87 x 47.24 x 23.62]	(1) MTK180-4, (1) OKKTB1260, (2) PNA18C, (2) DBE18C and (1) DLK186	PDF
QTA-E181208CDBD	\$1,834.00	1800 x 1200 x 800 [70.87 x 47.24 x 31.50]	(1) MTK180-4, (1) OKKTB1280, (2) PNA18C, (2) DBE18C and (1) DLK188	PDF
QTA-E201204CDBD	\$1,753.00	2000 x 1200 x 400 [78.74 x 47.24 x 15.75]	(1) MTK200-4, (1) OKKTB1240, (2) PNA20C, (2) DBE20C and (1) DLK204	PDF
QTA-E201206CDBD	\$1,838.00	2000 x 1200 x 600 [78.74 x 47.24 x 23.62]	(1) MTK200-4, (1) OKKTB1260, (2) PNA20C, (2) DBE20C and (1) DLK206	PDF
QTA-E201208CDBD	\$2,020.00	2000 x 1200 x 800 [78.74 x 47.24 x 31.50]	(1) MTK200-4, (1) OKKTB1280, (2) PNA20C, (2) DBE20C and (1) DLK208	PDF

Note: Dimensions in millimeters [inches].

OKK Series Expansion Bay Kit – NEMA 12 Freestanding Single-Door



Description

Each OKK Series expansion bay kit contains all the components required to expand one enclosure of the same height and depth.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

[Configuration Tool](#)



View assembly guide with the link button or QR code below:

[Assembly Guide](#)



OKK Series Expansion Bay Kit – NEMA 12 Freestanding Single-Door



OKK Series Expansion Bay Kit – NEMA12 Freestanding Single-Door				
Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-X180604CSBF	\$883.50	1800 x 600 x 400 [70.87 x 23.62 x 15.75]	(1) MTK180-4, (1) OKKTB6040, (1) PNA186, (1) DBE186, (1) RPE186, (1) UTK700, (1) FUP188 and (1) TTP040	PDF
QTA-X180606CSBF	\$964.00	1800 x 600 x 600 [70.87 x 23.62 x 23.62]	(1) MTK180-4, (1) OKKTB6060, (1) PNA186, (1) DBE186, (1) RPE186, (1) UTK700, (1) FUP188 and (1) TTP060	PDF
QTA-X180608CSBF	\$1,063.75	1800 x 600 x 800 [70.87 x 23.62 x 31.50]	(1) MTK180-4, (1) OKKTB6080, (1) PNA186, (1) DBE186, (1) RPE186, (1) UTK700, (1) FUP188 and (1) TTP080	PDF
QTA-X180804CSBF	\$996.50	1800 x 800 x 400 [70.87 x 31.50 x 15.75]	(1) MTK180-4, (1) OKKTB8040, (1) PNA188, (1) DBE188, (1) RPE188, (1) UTK700, (1) FUP188 and (1) TTP040	PDF
QTA-X180806CSBF	\$1,036.00	1800 x 800 x 600 [70.87 x 31.50 x 23.62]	(1) MTK180-4, (1) OKKTB8060, (1) PNA188, (1) DBE188, (1) RPE188, (1) UTK700, (1) FUP188 and (1) TTP060	PDF
QTA-X180808CSBF	\$1,141.75	1800 x 800 x 800 [70.87 x 31.50 x 31.50]	(1) MTK180-4, (1) OKKTB8080, (1) PNA188, (1) DBE188, (1) RPE188, (1) UTK700, (1) FUP188 and (1) TTP080	PDF
QTA-X181004CSBF	\$1,068.50	1800 x 1000 x 400 [70.87 x 39.37 x 15.75]	(1) MTK180-4, (1) OKKTB1040, (1) PNA18A, (1) DBE18A, (1) RPE18A, (1) UTK700, (1) FUP188 and (1) TTP040	PDF
QTA-X181006CSBF	\$1,117.00	1800 x 1000 x 600 [70.87 x 39.37 x 23.62]	(1) MTK180-4, (1) OKKTB1060, (1) PNA18A, (1) DBE18A, (1) RPE18A, (1) UTK700, (1) FUP188 and (1) TTP060	PDF
QTA-X181008CSBF	\$1,236.75	1800 x 1000 x 800 [70.87 x 39.37 x 31.50]	(1) MTK180-4, (1) OKKTB1080, (1) PNA18A, (1) DBE18A, (1) RPE18A, (1) UTK700, (1) FUP188 and (1) TTP080	PDF
QTA-X200604CSBF	\$995.50	2000 x 600 x 400 [78.74 x 23.62 x 15.75]	(1) MTK200-4, (1) OKKTB6040, (1) PNA206, (1) DBE206, (1) RPE206, (1) UTK700, (1) FUP208 and (1) TTP040	PDF
QTA-X200606CSBF	\$1,076.00	2000 x 600 x 600 [78.74 x 23.62 x 23.62]	(1) MTK200-4, (1) OKKTB6060, (1) PNA206, (1) DBE206, (1) RPE206, (1) UTK700, (1) FUP208 and (1) TTP060	PDF
QTA-X200608CSBF	\$1,175.75	2000 x 600 x 800 [78.74 x 23.62 x 31.50]	(1) MTK200-4, (1) OKKTB6080, (1) PNA206, (1) DBE206, (1) RPE206, (1) UTK700, (1) FUP208 and (1) TTP080	PDF
QTA-X200804CSBF	\$1,113.50	2000 x 800 x 400 [78.74 x 31.50 x 15.75]	(1) MTK200-4, (1) OKKTB8040, (1) PNA208, (1) DBE208, (1) RPE208, (1) UTK700, (1) FUP208 and (1) TTP040	PDF
QTA-X200806CSBF	\$1,153.00	2000 x 800 x 600 [78.74 x 31.50 x 23.62]	(1) MTK200-4, (1) OKKTB8060, (1) PNA208, (1) DBE208, (1) RPE208, (1) UTK700, (1) FUP208 and (1) TTP060	PDF
QTA-X200808CSBF	\$1,258.75	2000 x 800 x 800 [78.74 x 31.50 x 31.50]	(1) MTK200-4, (1) OKKTB8080, (1) PNA208, (1) DBE208, (1) RPE208, (1) UTK700, (1) FUP208 and (1) TTP080	PDF
QTA-X201004CSBF	\$1,200.50	2000 x 1000 x 400 [78.74 x 39.37 x 15.75]	(1) MTK200-4, (1) OKKTB1040, (1) PNA20A, (1) DBE20A, (1) RPE20A, (1) UTK700, (1) FUP208 and (1) TTP040	PDF
QTA-X201006CSBF	\$1,249.00	2000 x 1000 x 600 [78.74 x 39.37 x 23.62]	(1) MTK200-4, (1) OKKTB1060, (1) PNA20A, (1) DBE20A, (1) RPE20A, (1) UTK700, (1) FUP208 and (1) TTP060	PDF
QTA-X201008CSBF	\$1,368.75	2000 x 1000 x 800 [78.74 x 39.37 x 31.50]	(1) MTK200-4, (1) OKKTB1080, (1) PNA20A, (1) DBE20A, (1) RPE20A, (1) UTK700, (1) FUP208 and (1) TTP080	PDF
Note: Dimensions in millimeters [inches].				

OKK Series Expansion Bay Kit – NEMA 12 Freestanding Double-Door



Description

Each OKK Series expansion bay kit contains all the components required to expand one enclosure of the same height and depth.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Expansion Bay Kit – NEMA12 Freestanding Double-Door

Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-X181204CDBF	\$1,305.50	1800 x 1200 x 400 [70.87 x 47.24 x 15.75]	(1) MTK180-4, (1) OKKTB1240, (1) PNA18C, (1) DBE18C, (1) RPE18C, (1) UTK700, (1) FUP188 and (1) TTP040	PDF
QTA-X181206CDBF	\$1,355.00	1800 x 1200 x 600 [70.87 x 47.24 x 23.62]	(1) MTK180-4, (1) OKKTB1260, (1) PNA18C, (1) DBE18C, (1) RPE18C, (1) UTK700, (1) FUP188 and (1) TTP060	PDF
QTA-X181208CDBF	\$1,502.75	1800 x 1200 x 800 [70.87 x 47.24 x 31.50]	(1) MTK180-4, (1) OKKTB1280, (1) PNA18C, (1) DBE18C, (1) RPE18C, (1) UTK700, (1) FUP188 and (1) TTP080	PDF
QTA-X201204CDBF	\$1,438.50	2000 x 1200 x 400 [78.74 x 47.24 x 15.75]	(1) MTK200-4, (1) OKKTB1240, (1) PNA20C, (1) DBE20C, (1) RPE20C, (1) UTK700, (1) FUP208 and (1) TTP040	PDF
QTA-X201206CDBF	\$1,488.00	2000 x 1200 x 600 [78.74 x 47.24 x 23.62]	(1) MTK200-4, (1) OKKTB1260, (1) PNA20C, (1) DBE20C, (1) RPE20C, (1) UTK700, (1) FUP208 and (1) TTP060	PDF
QTA-X201208CDBF	\$1,635.75	2000 x 1200 x 800 [78.74 x 47.24 x 31.50]	(1) MTK200-4, (1) OKKTB1280, (1) PNA20C, (1) DBE20C, (1) RPE20C, (1) UTK700, (1) FUP208 and (1) TTP080	PDF

Note: Dimensions in millimeters [inches].

OKK Series Expansion Bay Kit – NEMA 12 Freestanding Single-Door with Window



Description

Each OKK Series expansion bay kit contains all the components required to expand one enclosure of the same height and depth.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel
- 4.0 mm acrylic window

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Expansion Bay Kit – NEMA 12 Freestanding Single-Door with Window



OKK Series Expansion Bay Kit – NEMA12 Freestanding Single-Door with Window				
Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
<u>QTA-X180804CSWF</u>	\$1,194.50	1800 x 800 x 400 [70.87 x 31.50 x 15.75]	(1) MTK180-4, (1) OKKTB8040, (1) PNA188, (1) DTE188, (1) RPE188, (1) UTK700, (1) FUP188 and (1) TTP040	<u>PDF</u>
<u>QTA-X180806CSWF</u>	\$1,234.00	1800 x 800 x 600 [70.87 x 31.50 x 23.62]	(1) MTK180-4, (1) OKKTB8060, (1) PNA188, (1) DTE188, (1) RPE188, (1) UTK700, (1) FUP188 and (1) TTP060	<u>PDF</u>
<u>QTA-X180808CSWF</u>	\$1,339.75	1800 x 800 x 800 [70.87 x 31.50 x 31.50]	(1) MTK180-4, (1) OKKTB8080, (1) PNA188, (1) DTE188, (1) RPE188, (1) UTK700, (1) FUP188 and (1) TTP080	<u>PDF</u>
<u>QTA-X181004CSWF</u>	\$1,322.50	1800 x 1000 x 400 [70.87 x 39.37 x 15.75]	(1) MTK180-4, (1) OKKTB1040, (1) PNA18A, (1) DTE18A, (1) RPE18A, (1) UTK700, (1) FUP188 and (1) TTP040	<u>PDF</u>
<u>QTA-X181006CSWF</u>	\$1,371.00	1800 x 1000 x 600 [70.87 x 39.37 x 23.62]	(1) MTK180-4, (1) OKKTB1060, (1) PNA18A, (1) DTE18A, (1) RPE18A, (1) UTK700, (1) FUP188 and (1) TTP060	<u>PDF</u>
<u>QTA-X181008CSWF</u>	\$1,490.75	1800 x 1000 x 800 [70.87 x 39.37 x 31.50]	(1) MTK180-4, (1) OKKTB1080, (1) PNA18A, (1) DTE18A, (1) RPE18A, (1) UTK700, (1) FUP188 and (1) TTP080	<u>PDF</u>
<u>QTA-X200804CSWF</u>	\$1,350.50	2000 x 800 x 400 [78.74 x 31.50 x 15.75]	(1) MTK200-4, (1) OKKTB8040, (1) PNA208, (1) DTE208, (1) RPE208, (1) UTK700, (1) FUP208 and (1) TTP040	<u>PDF</u>
<u>QTA-X200806CSWF</u>	\$1,390.00	2000 x 800 x 600 [78.74 x 31.50 x 23.62]	(1) MTK200-4, (1) OKKTB8060, (1) PNA208, (1) DTE208, (1) RPE208, (1) UTK700, (1) FUP208 and (1) TTP060	<u>PDF</u>
<u>QTA-X200808CSWF</u>	\$1,495.75	2000 x 800 x 800 [78.74 x 31.50 x 31.50]	(1) MTK200-4, (1) OKKTB8080, (1) PNA208, (1) DTE208, (1) RPE208, (1) UTK700, (1) FUP208 and (1) TTP080	<u>PDF</u>
<u>QTA-X201004CSWF</u>	\$1,485.50	2000 x 1000 x 400 [78.74 x 39.37 x 15.75]	(1) MTK200-4, (1) OKKTB1040, (1) PNA20A, (1) DTE20A, (1) RPE20A, (1) UTK700, (1) FUP208 and (1) TTP040	<u>PDF</u>
<u>QTA-X201006CSWF</u>	\$1,534.00	2000 x 1000 x 600 [78.74 x 39.37 x 23.62]	(1) MTK200-4, (1) OKKTB1060, (1) PNA20A, (1) DTE20A, (1) RPE20A, (1) UTK700, (1) FUP208 and (1) TTP060	<u>PDF</u>
<u>QTA-X201008CSWF</u>	\$1,653.75	2000 x 1000 x 800 [78.74 x 39.37 x 31.50]	(1) MTK200-4, (1) OKKTB1080, (1) PNA20A, (1) DTE20A, (1) RPE20A, (1) UTK700, (1) FUP208 and (1) TTP080	<u>PDF</u>
Note: Dimensions in millimeters [inches].				

OKK Series Expansion Bay Kit – NEMA 12 Freestanding Single-Door Dual Access



Description

Each OKK Series expansion bay kit contains all the components required to expand one enclosure of the same height and depth.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Expansion Bay Kit – NEMA 12 Freestanding Single-Door Dual Access



OKK Series Expansion Bay Kit – NEMA12 Freestanding Single-Door Dual Access				
Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
<u>QTA-X180604CSBD</u>	\$1,078.50	1800 x 600 x 400 [70.87 x 23.62 x 15.75]	(1) MTK180-4, (1) OKKTB6040, (2) PNA186, (2) DBE186, (1) UTK700, (2) FUP188 and (1) TTP040	<u>PDF</u>
<u>QTA-X180606CSBD</u>	\$1,159.00	1800 x 600 x 600 [70.87 x 23.62 x 23.62]	(1) MTK180-4, (1) OKKTB6060, (2) PNA186, (2) DBE186, (1) UTK700, (2) FUP188 and (1) TTP060	<u>PDF</u>
<u>QTA-X180608CSBD</u>	\$1,258.75	1800 x 600 x 800 [70.87 x 23.62 x 31.50]	(1) MTK180-4, (1) OKKTB6080, (2) PNA186, (2) DBE186, (1) UTK700, (2) FUP188 and (1) TTP080	<u>PDF</u>
<u>QTA-X180804CSBD</u>	\$1,223.50	1800 x 800 x 400 [70.87 x 31.50 x 15.75]	(1) MTK180-4, (1) OKKTB8040, (2) PNA188, (2) DBE188, (1) UTK700, (2) FUP188 and (1) TTP040	<u>PDF</u>
<u>QTA-X180806CSBD</u>	\$1,263.00	1800 x 800 x 600 [70.87 x 31.50 x 23.62]	(1) MTK180-4, (1) OKKTB8060, (2) PNA188, (2) DBE188, (1) UTK700, (2) FUP188 and (1) TTP060	<u>PDF</u>
<u>QTA-X180808CSBD</u>	\$1,368.75	1800 x 800 x 800 [70.87 x 31.50 x 31.50]	(1) MTK180-4, (1) OKKTB8080, (2) PNA188, (2) DBE188, (1) UTK700, (2) FUP188 and (1) TTP080	<u>PDF</u>
<u>QTA-X181004CSBD</u>	\$1,307.50	1800 x 1000 x 400 [70.87 x 39.37 x 15.75]	(1) MTK180-4, (1) OKKTB1040, (2) PNA18A, (2) DBE18A, (1) UTK700, (2) FUP188 and (1) TTP040	<u>PDF</u>
<u>QTA-X181006CSBD</u>	\$1,356.00	1800 x 1000 x 600 [70.87 x 39.37 x 23.62]	(1) MTK180-4, (1) OKKTB1060, (2) PNA18A, (2) DBE18A, (1) UTK700, (2) FUP188 and (1) TTP060	<u>PDF</u>
<u>QTA-X181008CSBD</u>	\$1,475.75	1800 x 1000 x 800 [70.87 x 39.37 x 31.50]	(1) MTK180-4, (1) OKKTB1080, (2) PNA18A, (2) DBE18A, (1) UTK700, (2) FUP188 and (1) TTP080	<u>PDF</u>
<u>QTA-X200604CSBD</u>	\$1,199.50	2000 x 600 x 400 [78.74 x 23.62 x 15.75]	(1) MTK200-4, (1) OKKTB6040, (2) PNA206, (2) DBE206, (1) UTK700, (2) FUP208 and (1) TTP040	<u>PDF</u>
<u>QTA-X200606CSBD</u>	\$1,280.00	2000 x 600 x 600 [78.74 x 23.62 x 23.62]	(1) MTK200-4, (1) OKKTB6060, (2) PNA206, (2) DBE206, (1) UTK700, (2) FUP208 and (1) TTP060	<u>PDF</u>
<u>QTA-X200608CSBD</u>	\$1,379.75	2000 x 600 x 800 [78.74 x 23.62 x 31.50]	(1) MTK200-4, (1) OKKTB6080, (2) PNA206, (2) DBE206, (1) UTK700, (2) FUP208 and (1) TTP080	<u>PDF</u>
<u>QTA-X200804CSBD</u>	\$1,364.50	2000 x 800 x 400 [78.74 x 31.50 x 15.75]	(1) MTK200-4, (1) OKKTB8040, (2) PNA208, (2) DBE208, (1) UTK700, (2) FUP208 and (1) TTP040	<u>PDF</u>
<u>QTA-X200806CSBD</u>	\$1,404.00	2000 x 800 x 600 [78.74 x 31.50 x 23.62]	(1) MTK200-4, (1) OKKTB8060, (2) PNA208, (2) DBE208, (1) UTK700, (2) FUP208 and (1) TTP060	<u>PDF</u>
<u>QTA-X200808CSBD</u>	\$1,509.75	2000 x 800 x 800 [78.74 x 31.50 x 31.50]	(1) MTK200-4, (1) OKKTB8080, (2) PNA208, (2) DBE208, (1) UTK700, (2) FUP208 and (1) TTP080	<u>PDF</u>
<u>QTA-X201004CSBD</u>	\$1,490.50	2000 x 1000 x 400 [78.74 x 39.37 x 15.75]	(1) MTK200-4, (1) OKKTB1040, (2) PNA20A, (2) DBE20A, (1) UTK700, (2) FUP208 and (1) TTP040	<u>PDF</u>
<u>QTA-X201006CSBD</u>	\$1,539.00	2000 x 1000 x 600 [78.74 x 39.37 x 23.62]	(1) MTK200-4, (1) OKKTB1060, (2) PNA20A, (2) DBE20A, (1) UTK700, (2) FUP208 and (1) TTP060	<u>PDF</u>
<u>QTA-X201008CSBD</u>	\$1,658.75	2000 x 1000 x 800 [78.74 x 39.37 x 31.50]	(1) MTK200-4, (1) OKKTB1080, (2) PNA20A, (2) DBE20A, (1) UTK700, (2) FUP208 and (1) TTP080	<u>PDF</u>

Note: Dimensions in millimeters [inches].

OKK Series Expansion Bay Kit – NEMA 12 Freestanding Double-Door Dual Access



Description

Each OKK Series expansion bay kit contains all the components required to expand one enclosure of the same height and depth.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55

Create your own configuration using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Expansion Bay Kit – NEMA12 Freestanding Double-Door Dual Access				
Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-X181204CDBD	\$1,609.50	1800 x 1200 x 400 [70.87 x 47.24 x 15.75]	(1) MTK180-4, (1) OKKTB1240, (2) PNA18C, (2) DBE18C, (1) UTK700, (2) FUP188 and (1) TTP040	PDF
QTA-X181206CDBD	\$1,659.00	1800 x 1200 x 600 [70.87 x 47.24 x 23.62]	(1) MTK180-4, (1) OKKTB1260, (2) PNA18C, (2) DBE18C, (1) UTK700, (2) FUP188 and (1) TTP060	PDF
QTA-X181208CDBD	\$1,806.75	1800 x 1200 x 800 [70.87 x 47.24 x 31.50]	(1) MTK180-4, (1) OKKTB1280, (2) PNA18C, (2) DBE18C, (1) UTK700, (2) FUP188 and (1) TTP080	PDF
QTA-X201204CDBD	\$1,788.50	2000 x 1200 x 400 [78.74 x 47.24 x 15.75]	(1) MTK200-4, (1) OKKTB1240, (2) PNA20C, (2) DBE20C, (1) UTK700, (2) FUP208 and (1) TTP040	PDF
QTA-X201206CDBD	\$1,838.00	2000 x 1200 x 600 [78.74 x 47.24 x 23.62]	(1) MTK200-4, (1) OKKTB1260, (2) PNA20C, (2) DBE20C, (1) UTK700, (2) FUP208 and (1) TTP060	PDF
QTA-X201208CDBD	\$1,985.75	2000 x 1200 x 800 [78.74 x 47.24 x 31.50]	(1) MTK200-4, (1) OKKTB1280, (2) PNA20C, (2) DBE20C, (1) UTK700, (2) FUP208 and (1) TTP080	PDF

Note: Dimensions in millimeters [inches].