

OKK Series Expansion Bay Kit – NEMA 12 Freestanding Double-Door Dual Access



Description

Each OKK Series expansion bay kit contains all the components required to expand one enclosure of the same height and depth.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55

Create your own configuration using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Expansion Bay Kit – NEMA12 Freestanding Double-Door Dual Access				
Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-X181204CDBD	Retired	1800 x 1200 x 400 [70.87 x 47.24 x 15.75]	(1) MTK180-4, (1) OKKTB1240, (2) PNA18C, (2) DBE18C, (1) UTK700, (2) FUP188 and (1) TTP040	PDF
QTA-X181206CDBD	Retired	1800 x 1200 x 600 [70.87 x 47.24 x 23.62]	(1) MTK180-4, (1) OKKTB1260, (2) PNA18C, (2) DBE18C, (1) UTK700, (2) FUP188 and (1) TTP060	PDF
QTA-X181208CDBD	Retired	1800 x 1200 x 800 [70.87 x 47.24 x 31.50]	(1) MTK180-4, (1) OKKTB1280, (2) PNA18C, (2) DBE18C, (1) UTK700, (2) FUP188 and (1) TTP080	PDF
QTA-X201204CDBD	Retired	2000 x 1200 x 400 [78.74 x 47.24 x 15.75]	(1) MTK200-4, (1) OKKTB1240, (2) PNA20C, (2) DBE20C, (1) UTK700, (2) FUP208 and (1) TTP040	PDF
QTA-X201206CDBD	Retired	2000 x 1200 x 600 [78.74 x 47.24 x 23.62]	(1) MTK200-4, (1) OKKTB1260, (2) PNA20C, (2) DBE20C, (1) UTK700, (2) FUP208 and (1) TTP060	PDF
QTA-X201208CDBD	Retired	2000 x 1200 x 800 [78.74 x 47.24 x 31.50]	(1) MTK200-4, (1) OKKTB1280, (2) PNA20C, (2) DBE20C, (1) UTK700, (2) FUP208 and (1) TTP080	PDF

Note: Dimensions in millimeters [inches].