

OKK Series Expansion Bay Kit – NEMA 12 Freestanding Single-Door Dual Access



Description

Each OKK Series expansion bay kit contains all the components required to expand one enclosure of the same height and depth.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Expansion Bay Kit – NEMA 12 Freestanding Single-Door Dual Access



OKK Series Expansion Bay Kit – NEMA12 Freestanding Single-Door Dual Access				
Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-X180604CSBD	\$1,078.50	1800 x 600 x 400 [70.87 x 23.62 x 15.75]	(1) MTK180-4, (1) OKKTB6040, (2) PNA186, (2) DBE186, (1) UTK700, (2) FUP188 and (1) TTP040	PDF
QTA-X180606CSBD	\$1,159.00	1800 x 600 x 600 [70.87 x 23.62 x 23.62]	(1) MTK180-4, (1) OKKTB6060, (2) PNA186, (2) DBE186, (1) UTK700, (2) FUP188 and (1) TTP060	PDF
QTA-X180608CSBD	\$1,258.75	1800 x 600 x 800 [70.87 x 23.62 x 31.50]	(1) MTK180-4, (1) OKKTB6080, (2) PNA186, (2) DBE186, (1) UTK700, (2) FUP188 and (1) TTP080	PDF
QTA-X180804CSBD	\$1,223.50	1800 x 800 x 400 [70.87 x 31.50 x 15.75]	(1) MTK180-4, (1) OKKTB8040, (2) PNA188, (2) DBE188, (1) UTK700, (2) FUP188 and (1) TTP040	PDF
QTA-X180806CSBD	\$1,263.00	1800 x 800 x 600 [70.87 x 31.50 x 23.62]	(1) MTK180-4, (1) OKKTB8060, (2) PNA188, (2) DBE188, (1) UTK700, (2) FUP188 and (1) TTP060	PDF
QTA-X180808CSBD	\$1,368.75	1800 x 800 x 800 [70.87 x 31.50 x 31.50]	(1) MTK180-4, (1) OKKTB8080, (2) PNA188, (2) DBE188, (1) UTK700, (2) FUP188 and (1) TTP080	PDF
QTA-X181004CSBD	\$1,307.50	1800 x 1000 x 400 [70.87 x 39.37 x 15.75]	(1) MTK180-4, (1) OKKTB1040, (2) PNA18A, (2) DBE18A, (1) UTK700, (2) FUP188 and (1) TTP040	PDF
QTA-X181006CSBD	\$1,356.00	1800 x 1000 x 600 [70.87 x 39.37 x 23.62]	(1) MTK180-4, (1) OKKTB1060, (2) PNA18A, (2) DBE18A, (1) UTK700, (2) FUP188 and (1) TTP060	PDF
QTA-X181008CSBD	\$1,475.75	1800 x 1000 x 800 [70.87 x 39.37 x 31.50]	(1) MTK180-4, (1) OKKTB1080, (2) PNA18A, (2) DBE18A, (1) UTK700, (2) FUP188 and (1) TTP080	PDF
QTA-X200604CSBD	\$1,199.50	2000 x 600 x 400 [78.74 x 23.62 x 15.75]	(1) MTK200-4, (1) OKKTB6040, (2) PNA206, (2) DBE206, (1) UTK700, (2) FUP208 and (1) TTP040	PDF
QTA-X200606CSBD	\$1,280.00	2000 x 600 x 600 [78.74 x 23.62 x 23.62]	(1) MTK200-4, (1) OKKTB6060, (2) PNA206, (2) DBE206, (1) UTK700, (2) FUP208 and (1) TTP060	PDF
QTA-X200608CSBD	\$1,379.75	2000 x 600 x 800 [78.74 x 23.62 x 31.50]	(1) MTK200-4, (1) OKKTB6080, (2) PNA206, (2) DBE206, (1) UTK700, (2) FUP208 and (1) TTP080	PDF
QTA-X200804CSBD	\$1,364.50	2000 x 800 x 400 [78.74 x 31.50 x 15.75]	(1) MTK200-4, (1) OKKTB8040, (2) PNA208, (2) DBE208, (1) UTK700, (2) FUP208 and (1) TTP040	PDF
QTA-X200806CSBD	\$1,404.00	2000 x 800 x 600 [78.74 x 31.50 x 23.62]	(1) MTK200-4, (1) OKKTB8060, (2) PNA208, (2) DBE208, (1) UTK700, (2) FUP208 and (1) TTP060	PDF
QTA-X200808CSBD	\$1,509.75	2000 x 800 x 800 [78.74 x 31.50 x 31.50]	(1) MTK200-4, (1) OKKTB8080, (2) PNA208, (2) DBE208, (1) UTK700, (2) FUP208 and (1) TTP080	PDF
QTA-X201004CSBD	\$1,490.50	2000 x 1000 x 400 [78.74 x 39.37 x 15.75]	(1) MTK200-4, (1) OKKTB1040, (2) PNA20A, (2) DBE20A, (1) UTK700, (2) FUP208 and (1) TTP040	PDF
QTA-X201006CSBD	\$1,539.00	2000 x 1000 x 600 [78.74 x 39.37 x 23.62]	(1) MTK200-4, (1) OKKTB1060, (2) PNA20A, (2) DBE20A, (1) UTK700, (2) FUP208 and (1) TTP060	PDF
QTA-X201008CSBD	\$1,658.75	2000 x 1000 x 800 [78.74 x 39.37 x 31.50]	(1) MTK200-4, (1) OKKTB1080, (2) PNA20A, (2) DBE20A, (1) UTK700, (2) FUP208 and (1) TTP080	PDF

Note: Dimensions in millimeters [inches].