

OKK Series Expansion Bay Kit – NEMA 12 Freestanding Single-Door with Window



Description

Each OKK Series expansion bay kit contains all the components required to expand one enclosure of the same height and depth.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel
- 4.0 mm acrylic window

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Expansion Bay Kit – NEMA 12 Freestanding Single-Door with Window



OKK Series Expansion Bay Kit – NEMA12 Freestanding Single-Door with Window				
Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
<u>QTA-X180804CSWF</u>	\$1,194.50	1800 x 800 x 400 [70.87 x 31.50 x 15.75]	(1) MTK180-4, (1) OKKTB8040, (1) PNA188, (1) DTE188, (1) RPE188, (1) UTK700, (1) FUP188 and (1) TTP040	<u>PDF</u>
<u>QTA-X180806CSWF</u>	\$1,234.00	1800 x 800 x 600 [70.87 x 31.50 x 23.62]	(1) MTK180-4, (1) OKKTB8060, (1) PNA188, (1) DTE188, (1) RPE188, (1) UTK700, (1) FUP188 and (1) TTP060	<u>PDF</u>
<u>QTA-X180808CSWF</u>	\$1,339.75	1800 x 800 x 800 [70.87 x 31.50 x 31.50]	(1) MTK180-4, (1) OKKTB8080, (1) PNA188, (1) DTE188, (1) RPE188, (1) UTK700, (1) FUP188 and (1) TTP080	<u>PDF</u>
<u>QTA-X181004CSWF</u>	\$1,322.50	1800 x 1000 x 400 [70.87 x 39.37 x 15.75]	(1) MTK180-4, (1) OKKTB1040, (1) PNA18A, (1) DTE18A, (1) RPE18A, (1) UTK700, (1) FUP188 and (1) TTP040	<u>PDF</u>
<u>QTA-X181006CSWF</u>	\$1,371.00	1800 x 1000 x 600 [70.87 x 39.37 x 23.62]	(1) MTK180-4, (1) OKKTB1060, (1) PNA18A, (1) DTE18A, (1) RPE18A, (1) UTK700, (1) FUP188 and (1) TTP060	<u>PDF</u>
<u>QTA-X181008CSWF</u>	\$1,490.75	1800 x 1000 x 800 [70.87 x 39.37 x 31.50]	(1) MTK180-4, (1) OKKTB1080, (1) PNA18A, (1) DTE18A, (1) RPE18A, (1) UTK700, (1) FUP188 and (1) TTP080	<u>PDF</u>
<u>QTA-X200804CSWF</u>	\$1,350.50	2000 x 800 x 400 [78.74 x 31.50 x 15.75]	(1) MTK200-4, (1) OKKTB8040, (1) PNA208, (1) DTE208, (1) RPE208, (1) UTK700, (1) FUP208 and (1) TTP040	<u>PDF</u>
<u>QTA-X200806CSWF</u>	\$1,390.00	2000 x 800 x 600 [78.74 x 31.50 x 23.62]	(1) MTK200-4, (1) OKKTB8060, (1) PNA208, (1) DTE208, (1) RPE208, (1) UTK700, (1) FUP208 and (1) TTP060	<u>PDF</u>
<u>QTA-X200808CSWF</u>	\$1,495.75	2000 x 800 x 800 [78.74 x 31.50 x 31.50]	(1) MTK200-4, (1) OKKTB8080, (1) PNA208, (1) DTE208, (1) RPE208, (1) UTK700, (1) FUP208 and (1) TTP080	<u>PDF</u>
<u>QTA-X201004CSWF</u>	\$1,485.50	2000 x 1000 x 400 [78.74 x 39.37 x 15.75]	(1) MTK200-4, (1) OKKTB1040, (1) PNA20A, (1) DTE20A, (1) RPE20A, (1) UTK700, (1) FUP208 and (1) TTP040	<u>PDF</u>
<u>QTA-X201006CSWF</u>	\$1,534.00	2000 x 1000 x 600 [78.74 x 39.37 x 23.62]	(1) MTK200-4, (1) OKKTB1060, (1) PNA20A, (1) DTE20A, (1) RPE20A, (1) UTK700, (1) FUP208 and (1) TTP060	<u>PDF</u>
<u>QTA-X201008CSWF</u>	\$1,653.75	2000 x 1000 x 800 [78.74 x 39.37 x 31.50]	(1) MTK200-4, (1) OKKTB1080, (1) PNA20A, (1) DTE20A, (1) RPE20A, (1) UTK700, (1) FUP208 and (1) TTP080	<u>PDF</u>
Note: Dimensions in millimeters [inches].				