

OKK Series Doors with Window



Application

Each door provides interior access to an OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Base and roof set
- Vertical frame rail set
- Exterior side panels
- Exterior rear panel or additional door
- Subpanel

Material

- 2.0 mm carbon steel
- 4.0 mm acrylic window

Finish

- RAL 7035 light gray
- Textured powder coat finish

Features

- Fully reversible
- 120° opening
- Four hinges
- 3.0mm double-bar 4-point latch with double-bit key
- Poured-in-place two-component polyurethane gasket, foamed on a perimeter external to the latch points
- Doors include a Sendzimir galvanized inner stiffening frame with Zamak zinc alloy corner pieces.

Listings

- Fully-assembled OKK Series Enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



Doors with Window			
Part Number	Price	Size HxWxD	Drawing Link
DTE188	\$451.00	1800 x 800 [70.87 x 31.50]	PDF
DTE18A	\$529.00	1800 x 1000 [70.87 x 39.37]	PDF
DTE208	\$509.00	2000 x 800 [78.74 x 31.50]	PDF
DTE20A	\$596.00	2000 x 1000 [78.74 x 39.37]	PDF
Note: Dimensions in millimeters [inches].			