

OKK Series Doors with Window



Application

Each door provides interior access to an OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Base and roof set
- Vertical frame rail set
- Exterior side panels
- Exterior rear panel or additional door
- Subpanel

Material

- 2.0 mm carbon steel
- 4.0 mm acrylic window

Finish

- RAL 7035 light gray
- Textured powder coat finish

Features

- Fully reversible
- 120° opening
- Four hinges
- 3.0mm double-bar 4-point latch with double-bit key
- Poured-in-place two-component polyurethane gasket, foamed on a perimeter external to the latch points
- Doors include a Sendzimir galvanized inner stiffening frame with Zamak zinc alloy corner pieces.

Listings

- Fully-assembled OKK Series Enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



| Doors with Window | | | |
|---|----------|-----------------------------|---------------------|
| Part Number | Price | Size HxWxD | Drawing Link |
| DTE188 | \$451.00 | 1800 x 800 [70.87 x 31.50] | PDF |
| DTE18A | \$529.00 | 1800 x 1000 [70.87 x 39.37] | PDF |
| DTE208 | \$509.00 | 2000 x 800 [78.74 x 31.50] | PDF |
| DTE20A | \$596.00 | 2000 x 1000 [78.74 x 39.37] | PDF |
| Note: Dimensions in millimeters [inches]. | | | |