



OKK Series Enclosure Kit – NEMA 12 Freestanding Double-Door Dual Access



Description

Each OKK Series enclosure kit contains all the components required to assemble one complete enclosure.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

[Configuration Tool](#)



View assembly guide with the link button or QR code below:

[Assembly Guide](#)



OKK Series Enclosure Kit – NEMA12 Freestanding Double-Door Dual Access

Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-E181204CDBD	\$1,571.00	1800 x 1200 x 400 [70.87 x 47.24 x 15.75]	(1) MTK180-4, (1) OKKTB1240, (2) PNA18C, (2) DBE18C and (1) DLK184	PDF
QTA-E181206CDBD	\$1,652.00	1800 x 1200 x 600 [70.87 x 47.24 x 23.62]	(1) MTK180-4, (1) OKKTB1260, (2) PNA18C, (2) DBE18C and (1) DLK186	PDF
QTA-E181208CDBD	\$1,834.00	1800 x 1200 x 800 [70.87 x 47.24 x 31.50]	(1) MTK180-4, (1) OKKTB1280, (2) PNA18C, (2) DBE18C and (1) DLK188	PDF
QTA-E201204CDBD	\$1,753.00	2000 x 1200 x 400 [78.74 x 47.24 x 15.75]	(1) MTK200-4, (1) OKKTB1240, (2) PNA20C, (2) DBE20C and (1) DLK204	PDF
QTA-E201206CDBD	\$1,838.00	2000 x 1200 x 600 [78.74 x 47.24 x 23.62]	(1) MTK200-4, (1) OKKTB1260, (2) PNA20C, (2) DBE20C and (1) DLK206	PDF
QTA-E201208CDBD	\$2,020.00	2000 x 1200 x 800 [78.74 x 47.24 x 31.50]	(1) MTK200-4, (1) OKKTB1280, (2) PNA20C, (2) DBE20C and (1) DLK208	PDF

Note: Dimensions in millimeters [inches].