



OKK Series Enclosure Kit – NEMA 12 Freestanding Single-Door Dual Access



Description

Each OKK Series enclosure kit contains all the components required to assemble one complete enclosure.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Enclosure Kit – NEMA12 Freestanding Single-Door Dual Access

Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-E180604CSBD	\$1,040.00	1800 x 600 x 400 [70.87 x 23.62 x 15.75]	(1) MTK180-4, (1) OKKTB6040, (2) PNA186, (2) DBE186 and (1) DLK184	PDF
QTA-E180606CSBD	\$1,152.00	1800 x 600 x 600 [70.87 x 23.62 x 23.62]	(1) MTK180-4, (1) OKKTB6060, (2) PNA186, (2) DBE186 and (1) DLK186	PDF
QTA-E180608CSBD	\$1,286.00	1800 x 600 x 800 [70.87 x 23.62 x 31.50]	(1) MTK180-4, (1) OKKTB6080, (2) PNA186, (2) DBE186 and (1) DLK188	PDF
QTA-E180804CSBD	\$1,185.00	1800 x 800 x 400 [70.87 x 31.50 x 15.75]	(1) MTK180-4, (1) OKKTB8040, (2) PNA188, (2) DBE188 and (1) DLK184	PDF
QTA-E180806CSBD	\$1,256.00	1800 x 800 x 600 [70.87 x 31.50 x 23.62]	(1) MTK180-4, (1) OKKTB8060, (2) PNA188, (2) DBE188 and (1) DLK186	PDF
QTA-E180808CSBD	\$1,396.00	1800 x 800 x 800 [70.87 x 31.50 x 31.50]	(1) MTK180-4, (1) OKKTB8080, (2) PNA188, (2) DBE188 and (1) DLK188	PDF
QTA-E181004CSBD	\$1,269.00	1800 x 1000 x 400 [70.87 x 39.37 x 15.75]	(1) MTK180-4, (1) OKKTB1040, (2) PNA18A, (2) DBE18A and (1) DLK184	PDF
QTA-E181006CSBD	\$1,349.00	1800 x 1000 x 600 [70.87 x 39.37 x 23.62]	(1) MTK180-4, (1) OKKTB1060, (2) PNA18A, (2) DBE18A and (1) DLK186	PDF
QTA-E181008CSBD	\$1,503.00	1800 x 1000 x 800 [70.87 x 39.37 x 31.50]	(1) MTK180-4, (1) OKKTB1080, (2) PNA18A, (2) DBE18A and (1) DLK188	PDF
QTA-E200604CSBD	\$1,164.00	2000 x 600 x 400 [78.74 x 23.62 x 15.75]	(1) MTK200-4, (1) OKKTB6040, (2) PNA206, (2) DBE206 and (1) DLK204	PDF
QTA-E200606CSBD	\$1,280.00	2000 x 600 x 600 [78.74 x 23.62 x 23.62]	(1) MTK200-4, (1) OKKTB6060, (2) PNA206, (2) DBE206 and (1) DLK206	PDF
QTA-E200608CSBD	\$1,414.00	2000 x 600 x 800 [78.74 x 23.62 x 31.50]	(1) MTK200-4, (1) OKKTB6080, (2) PNA206, (2) DBE206 and (1) DLK208	PDF
QTA-E200804CSBD	\$1,329.00	2000 x 800 x 400 [78.74 x 31.50 x 15.75]	(1) MTK200-4, (1) OKKTB8040, (2) PNA208, (2) DBE208 and (1) DLK204	PDF
QTA-E200806CSBD	\$1,404.00	2000 x 800 x 600 [78.74 x 31.50 x 23.62]	(1) MTK200-4, (1) OKKTB8060, (2) PNA208, (2) DBE208 and (1) DLK206	PDF
QTA-E200808CSBD	\$1,544.00	2000 x 800 x 800 [78.74 x 31.50 x 31.50]	(1) MTK200-4, (1) OKKTB8080, (2) PNA208, (2) DBE208 and (1) DLK208	PDF
QTA-E201004CSBD	\$1,455.00	2000 x 1000 x 400 [78.74 x 39.37 x 15.75]	(1) MTK200-4, (1) OKKTB1040, (2) PNA20A, (2) DBE20A and (1) DLK204	PDF
QTA-E201006CSBD	\$1,539.00	2000 x 1000 x 600 [78.74 x 39.37 x 23.62]	(1) MTK200-4, (1) OKKTB1060, (2) PNA20A, (2) DBE20A and (1) DLK206	PDF
QTA-E201008CSBD	\$1,693.00	2000 x 1000 x 800 [78.74 x 39.37 x 31.50]	(1) MTK200-4, (1) OKKTB1080, (2) PNA20A, (2) DBE20A and (1) DLK208	PDF

Note: Dimensions in millimeters [inches].