



OKK Series Plinth Kits

Description

Provides a mounting base and/or additional space for cable entry for OKK Series enclosures.

Material

- 2.0 mm carbon steel

Finish

- RAL 7024 graphite gray
- Textured powder coat finish

Features

- ZAK0* parts are plinth front/rear
- FLK* are plinth sides
- Kits are available in 100mm [3.94 in] and 200mm [7.87 in] heights.
- Kits may be stacked to provide plinths over 200mm [7.87 in] high, if desired.



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Plinth Kits

Part Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-P010604C	Retired	100 x 600 x 400 [3.94 x 23.62 x 15.75]	(1) ZAK061 and (1) FLK14	PDF
QTA-P010606C	Retired	100 x 600 x 600 [3.94 x 23.62 x 23.62]	(1) ZAK061 and (1) FLK16	PDF
QTA-P010608C	Retired	100 x 600 x 800 [3.94 x 23.62 x 31.50]	(1) ZAK061 and (1) FLK18	PDF
QTA-P010804C	Retired	100 x 800 x 400 [3.94 x 31.50 x 15.75]	(1) ZAK081 and (1) FLK14	PDF
QTA-P010806C	Retired	100 x 800 x 600 [3.94 x 31.50 x 23.62]	(1) ZAK081 and (1) FLK16	PDF
QTA-P010808C	Retired	100 x 800 x 800 [3.94 x 31.50 x 31.50]	(1) ZAK081 and (1) FLK18	PDF
QTA-P011004C	Retired	100 x 1000 x 400 [3.94 x 39.37 x 15.75]	(1) ZAK0A1 and (1) FLK14	PDF
QTA-P011006C	Retired	100 x 1000 x 600 [3.94 x 39.37 x 23.62]	(1) ZAK0A1 and (1) FLK16	PDF
QTA-P011008C	Retired	100 x 1000 x 800 [3.94 x 39.37 x 31.50]	(1) ZAK0A1 and (1) FLK18	PDF
QTA-P011204C	Retired	100 x 1200 x 400 [3.94 x 47.24 x 15.75]	(1) ZAK0C1 and (1) FLK14	PDF
QTA-P011206C	Retired	100 x 1200 x 600 [3.94 x 47.24 x 23.62]	(1) ZAK0C1 and (1) FLK16	PDF
QTA-P011208C	Retired	100 x 1200 x 800 [3.94 x 47.24 x 31.50]	(1) ZAK0C1 and (1) FLK18	PDF
QTA-P020604C	Retired	200 x 600 x 400 [7.87 x 23.62 x 15.75]	(1) ZAK062 and (2) FLK14	PDF
QTA-P020606C	Retired	200 x 600 x 600 [7.87 x 23.62 x 23.62]	(1) ZAK062 and (2) FLK16	PDF
QTA-P020608C	Retired	200 x 600 x 800 [7.87 x 23.62 x 31.50]	(1) ZAK062 and (2) FLK18	PDF
QTA-P020804C	Retired	200 x 800 x 400 [7.87 x 31.50 x 15.75]	(1) ZAK082 and (2) FLK14	PDF
QTA-P020806C	Retired	200 x 800 x 600 [7.87 x 31.50 x 23.62]	(1) ZAK082 and (2) FLK16	PDF
QTA-P020808C	Retired	200 x 800 x 800 [7.87 x 31.50 x 31.50]	(1) ZAK082 and (2) FLK18	PDF
QTA-P021004C	Retired	200 x 1000 x 400 [7.87 x 39.37 x 15.75]	(1) ZAK0A2 and (2) FLK14	PDF
QTA-P021006C	Retired	200 x 1000 x 600 [7.87 x 39.37 x 23.62]	(1) ZAK0A2 and (2) FLK16	PDF
QTA-P021008C	Retired	200 x 1000 x 800 [7.87 x 39.37 x 31.50]	(1) ZAK0A2 and (2) FLK18	PDF
QTA-P021204C	Retired	200 x 1200 x 400 [7.87 x 47.24 x 15.75]	(1) ZAK0C2 and (2) FLK14	PDF
QTA-P021206C	Retired	200 x 1200 x 600 [7.87 x 47.24 x 23.62]	(1) ZAK0C2 and (2) FLK16	PDF
QTA-P021208C	Retired	200 x 1200 x 800 [7.87 x 47.24 x 31.50]	(1) ZAK0C2 and (2) FLK18	PDF

Note: Dimensions in millimeters [inches].