

OKK Series Plinths

**ZAK081****ZAK082**

Description

Components for custom-designed plinths for OKK Series enclosures.

Material

- 2.0 mm carbon steel

Finish

- RAL 7024 graphite gray
- Textured powder coat finish

Features

- Both front/rear plates and side flanges are sold in pairs.
- Mix and match front/rear plates and side flanges to match enclosure WxD dimensions.
- Use two sets of 100mm [3.94 in] height side flanges with 200mm [7.87 in] height front/rear plate sets.
- Plinth assemblies can be stacked to form greater plinth heights.



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



Plinth Front and Rear Plate Sets

Part Number	Price	Size HxW	Drawing Link
ZAK061	\$62.00	100 x 600 [3.94 x 23.62]	PDF
ZAK062	\$123.00	200 x 600 [7.87 x 23.62]	PDF
ZAK081	\$79.00	100 x 800 [3.94 x 31.50]	PDF
ZAK082	\$158.00	200 x 800 [7.87 x 31.50]	PDF
ZAK0A1	\$91.00	100 x 1000 [3.94 x 39.37]	PDF
ZAK0A2	\$181.00	200 x 1000 [7.87 x 39.37]	PDF
ZAK0C1	\$92.00	100 x 1200 [3.94 x 47.24]	PDF
ZAK0C2	\$185.00	200 x 1200 [7.87 x 47.24]	PDF

Note: Dimensions in millimeters [inches].

**FLK16**

Plinth Side Flanges

Part Number	Price	Size HxD	Drawing Link
FLK14	\$4.75	100 x 400 [3.94 x 15.75]	PDF
FLK16	\$6.50	100 x 600 [3.94 x 23.62]	PDF
FLK18	\$7.25	100 x 800 [3.94 x 31.50]	PDF

Note: Dimensions in millimeters [inches].