

# OKK Series Rear Exterior Panels



## Application

Each rear exterior panel provides the rear surface for one OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Base and roof set
- Vertical frame rail set
- Exterior side panels
- Door
- Subpanel

An additional door may be used in lieu of a rear exterior panel to create a dual access enclosure.

## Material

- 2.0 mm carbon steel

## Finish

- RAL 7035 light gray
- Textured powder coat finish

## Features

- Poured-in-place polyurethane gasket
- Includes mounting clips, screws, and gaskets (CLK013-KIT2F)

## Listings

- Fully-assembled OKK Series Enclosures are rated as follows:
  - UL 508a Type 12 [UL File E503249]
  - CSA Type 12 [CSA File 115232]
- Complies with the following:
  - NEMA Type 12
  - EC EN60529 IP55



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

### Configuration Tool



Rear Exterior Panels			
Part Number	Price	Fits Enclosure Size HxW	Drawing Link
<a href="#">RPE186</a>	\$80.00	1800 x 600 [70.87 x 23.62]	<a href="#">PDF</a>
<a href="#">RPE188</a>	\$99.00	1800 x 800 [70.87 x 31.50]	<a href="#">PDF</a>
<a href="#">RPE18A</a>	\$119.00	1800 x 1000 [70.87 x 39.37]	<a href="#">PDF</a>
<a href="#">RPE18C</a>	\$137.00	1800 x 1200 [70.87 x 47.24]	<a href="#">PDF</a>
<a href="#">RPE206</a>	\$97.00	2000 x 600 [78.74 x 23.62]	<a href="#">PDF</a>
<a href="#">RPE208</a>	\$111.00	2000 x 800 [78.74 x 31.50]	<a href="#">PDF</a>
<a href="#">RPE20A</a>	\$125.00	2000 x 1000 [78.74 x 39.37]	<a href="#">PDF</a>
<a href="#">RPE20C</a>	\$146.00	2000 x 1200 [78.74 x 47.24]	<a href="#">PDF</a>

Note: Dimensions in millimeters [inches].