

OKK Series Rear Exterior Panels



Application

Each rear exterior panel provides the rear surface for one OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Base and roof set
- Vertical frame rail set
- Exterior side panels
- Door
- Subpanel

An additional door may be used in lieu of a rear exterior panel to create a dual access enclosure.

Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Features

- Poured-in-place polyurethane gasket
- Includes mounting clips, screws, and gaskets (CLK013-KIT2F)

Listings

- Fully-assembled OKK Series Enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - EC EN60529 IP55



Rear Exterior Panels			
Part Number	Price	Fits Enclosure Size HxW	Drawing Link
RPE186	\$86.00	1800 x 600 [70.87 x 23.62]	PDF
RPE188	\$107.00	1800 x 800 [70.87 x 31.50]	PDF
RPE18A	\$127.00	1800 x 1000 [70.87 x 39.37]	PDF
RPE18C	\$147.00	1800 x 1200 [70.87 x 47.24]	PDF
RPE206	\$104.00	2000 x 600 [78.74 x 23.62]	PDF
RPE208	\$119.00	2000 x 800 [78.74 x 31.50]	PDF
RPE20A	\$134.00	2000 x 1000 [78.74 x 39.37]	PDF
RPE20C	\$156.00	2000 x 1200 [78.74 x 47.24]	PDF
Note: Dimensions in millimeters [inches].			