

OKK Series Subpanels



Application

Provides the primary subpanel for an OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Base and roof set
- Vertical frame rail set
- Exterior side panels
- Door
- Exterior rear panel or additional door

Subpanel can be mounted at variable depths or flush mounted. Multiple subpanels can be used in a Dual access enclosure.

Subpanels may also be recess mounted on one or both sides for use as side-mounted panels or to form a barrier between two adjacent bays. For side-mount applications, match subpanel nominal width to enclosure depth.

APK110 (sold separately) required for all recess mounting applications

Material

- 2.5 mm Sendzimir galvanized steel

Features

- Includes installation hardware ([PPK100](#)).

Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



Subpanels			
Part Number	Price	Fits Enclosure Size HxW	Drawing Link
PNA186	\$95.00	1800 x 600 [70.87 x 23.62]	PDF
PNA188	\$110.00	1800 x 800 [70.87 x 31.50]	PDF
PNA18A	\$126.00	1800 x 1000 [70.87 x 39.37]	PDF
PNA18C	\$145.00	1800 x 1200 [70.87 x 47.24]	PDF
PNA206	\$108.00	2000 x 600 [78.74 x 23.62]	PDF
PNA208	\$133.00	2000 x 800 [78.74 x 31.50]	PDF
PNA20A	\$154.00	2000 x 1000 [78.74 x 39.37]	PDF
PNA20C	\$179.00	2000 x 1200 [78.74 x 47.24]	PDF
Note: Dimensions in millimeters [inches].			