

OKK Series Swing Panels



Application

Provides an interior mounting surface just behind the exterior door. Panel can swing open to allow access to the interior of the enclosure.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Features

- Includes hinges, screws, and bolts
- Zinc alloy corner pieces.

Listings

- IP44



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

[Configuration Tool](#)



Swing Panels			
Part Number	Price	Fits Enclosure Size HxW	Drawing Link
DBI188	\$259.00	1800 x 800 [70.87 x 31.50]	PDF
DBI18A	\$304.00	1800 x 1000 [70.87 x 39.37]	PDF
DBI208	\$297.00	2000 x 800 [78.74 x 31.50]	PDF
DBI20A	\$344.00	2000 x 1000 [78.74 x 39.37]	PDF
Note: Dimensions in millimeters [inches]. Swing panels kits consist of a panel and a mounting frame; each packaged separately.			