


Enclosure Accessories – Rack Mounting

Swing-Out Rack Mounting Frames for Freestanding Enclosures



Fabricated from 10-gauge steel, these swing-out rack mounting frames are available for mounting 19 in [483 mm] rack-mounted equipment. Mounting holes are tapped with #10-32 threads spaced per E.I.A. standard.

Frames are painted with white polyester powder.

Note: If used in a two-door enclosure, a center panel support must be ordered.

Shipping Schedule

Same day	1 - 5 days	1 - 7 days	1 - 10 days	1 - 15 days	1 - 20 days
----------	------------	------------	-------------	-------------	-------------

Color indicates shipping lead time in business days.

Mounting Frames	Price	Fits Enclosure HxW	Usable Angle Length "T"	Wt. [lb]
WA7230SOF19	Retired	72 x 30 [1829 x 762]	57.88 [1470]	61
WA7236SOF19	Retired	72x36 [1829x914]	57.88 [1470]	73
WA9036SOF19	Retired	90x36 [2286x914]	75.38 [1915]	87

Note: Dimensions in inches [millimeters].

Rack Mounting Angles for Ultimate Series

Rack mounting angles allow the installation of 19 in [483 mm] rack equipment in 24-inch wide NEMA 412 enclosures. "L" shaped thru-hole angles may be fixed to the enclosure flange, or used in combination with the Adjustable Depth Mounting Kits. Thru-hole diameters are 0.281in [7.14mm]. Brackets are fabricated from 14-gauge galvanized steel. Mounting hardware and two angles are provided.



Note: W1032N clip nuts must be purchased separately.

Rack Mounting Angles	Price	For Enclosure Height in [mm]	Wt. [lb]
HFWRA20C	Retired	20 [508]	3
HFWRA24C	Retired	24 [609]	
HFWRA30C	Retired	30 [762]	
HFWRA36C	Retired	36 [914]	4
HFWRA48C	Retired	48 [1219]	7

Console Rack Angles

Angle brackets for mounting 19 in [483 mm] rack equipment in the WC14B console.



Rack Mounting Angle For Wall-Mounts

Designed for mounting 19 in [483 mm] rack mounted equipment in 24-inch wide NEMA 12, NEMA 4 and NEMA 412 wall-mount enclosures. Small holes are tapped # 10-32. Sealing washers are also provided to maintain original NEMA rating after installation.

Console Rack Angle	Price	Description	Wt. [lb]
WC14R	Retired	Wiegmann enclosure rack angle, white polyester powder finish, for WC14B enclosure. For use on WC series consoles but provides standard rack hole spacing for only WC14B. Includes mounting hardware. Package of 2.	11

Rack Mounting Angle	Price	For Enclosure Height in [mm]	Description	Wt. [lb]
WARAK24	Retired	24 [609]	Enclosure rack mounting angle, white polyester powder finish. Includes mounting hardware. Package of 2.	8
WARAK30	Retired	30 [762]		10
WARAK36	Retired	36 [914]		12

Enclosure Accessories – Rack Mounting



Rack Mounting For Freestanding Enclosures

Type RP Angles

Full or half-length rack angles for installing rack-mounted equipment in freestanding NEMA 12 enclosures

- 10-gauge steel
- If used in two-door enclosures a center panel support must be ordered
- White polyester powder
- Package of 2 angles includes mounting hardware


Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1-10 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

Rack Mounting Angles	Price	Fits Enclosure Size (HxW) in [mm]	Length	Wt. [lb]
WA60RP24F5	Retired	60x24 [1524X610]	49.00 [1244]	15
WA60RP24F6	Retired		26.25 [667]	8
WA72RP24F5	Retired	90x24 [2286x610]	61.25 [1556]	19
WA72RP24F6	Retired		31.50 [800]	10
WA90RP24F5	Retired	90x24 [228.60x60.96cm]	78.75 [2000]	24
WA90RP24F6	Retired		40.25 [1022]	14

Note: Dimensions in inches [millimeters].



WA60RP24F5

Type RA Channel

U-shaped channel for installing 19 in [483 mm] rack-mounted equipment in all freestanding NEMA 12 and NEMA 4 enclosures:

- Through holes (7/32-inch diameter) are provided and require a W1032N clip nut (must be ordered separately)
- Mounted on unistrut within the enclosure
- Adjustable
- If used in two-door enclosures, a center panel support must be ordered
- White polyester powder finish



WA60RA19TH

Rack Mounting Channel	Price	Fits Enclosure Size (HxW) in [mm]	Length in [mm]	Wt. [lb]
WA60RA19TH	Retired	60 x 24 [1524 x 610]	49.00 [1245]	14
WA72RA19TH	Retired	72 x 24 [1829 x 610]	61.25 [1556]	18
WA90RA19TH	Retired	90 x 24 [2286 x 610]	78.78 [2001]	23

Note: Dimensions in inches [millimeters].