



PSRT Series Switching Power Supplies

Overview

AutomationDirect's RHINO TOUGH PSRT series of switching power supplies are designed for industrial applications outside of the control cabinet. These field-mountable power supplies offer a compact footprint and allow machine mounting near the load.

Features

- High efficiency
- Compact size
- Integrated device protection
- Quick connection with 7/8" connectors
- Internal isolating transformer with reinforced insulation
- IP67 protection class - safe to touch even at full load



PSRT-24-100



PSRT-24-200

PSRT Series Switching Power Supplies Selection Chart

Part Number	Price	Output Voltage	Output Current	Output Power	Drawing Link
PSRT-24-100	\$263.00	24VDC	3.8 A	91.2 W	PDF
PSRT-24-200	\$341.00		8A	192W	PDF

PSRT Series Switching Power Supplies Input Specifications

Part Number	Nominal Input Voltage	Input Voltage Range	Nominal Frequency Range	Max. Input Current	Max. Inrush Current (after 1ms)	Nominal Watts	Efficiency	Circuit Breaker
PSRT-24-100	120/240 VAC	90-265 VAC/VDC	50/60 Hz ±6 %	1.1 A @ 100VAC 0.5 A @ 240VAC	8.9A @ 230VAC	0.95 kW @ 230VAC	91.4% @ 115VAC 92.1% @ 230VAC	C4
PSRT-24-200	100/230 VDC	90-265 VAC 90-372 VDC		2.1 A @ 100 VAC 0.9 A @ 240 VAC	7A @ 230VAC	0.95 kW @ 230VAC	93.7% @ 115VAC 94.4% @ 230VAC	B or C

PSRT Series Switching Power Supplies Output Specifications

Part Number	Output Voltage	Output Hold-up Time (Min.)	Output Current (Continuous 24VDC)	Output Current (Power Boost)	Output Current (Short-Circuit)	MTBF (@ 40°C)
PSRT-24-100	24VDC (SELV) ±2%	80ms (230VAC) 3.8 A (24VDC)	3.8 A (+60 °C) 2.4 A (+70 °C)	N/A	4.4 A	> 1,000,000h
PSRT-24-200		≥ 35ms (230VAC) 8A (24VDC)	8A (+60 °C) 4.8 A (+70 °C)	150% for 5s	9A	> 700,000h



PSRT Series Switching Power Supplies

PSRT Series Switching Power Supplies General Specifications		
Part Number	PSRT-24-100	PSRT-24-200
Temperature	Operating	-40 to 85°C [-40 to 185°F]
	Storage	-40 to 85°C [-40 to 185°F]
Humidity	4 to 100%	
Line Regulation	5mV	
Load Regulation	110mV	
Short Circuit Protection	Yes	
Leakage Current	< 1mA @ 230VAC / 50 Hz	
Start-up Time	≤ 330ms @ 100VAC ≤ 330ms @ 230VAC	≤ 500 ms
Short Circuit Protection	Yes	
Overload Protection	Yes	
Overvoltage Shutdown	N/A	
Status Indicators	LED (green): output voltage OK LED (red): overload, overheating or short-circuit No color - No input voltage	
Ripple (max.)	50 mVrms	< 30 mVeffi/rms
Spikes (max.)	130 mVp-p	300 mVss/pp
Vibration	IEC 60068-2-6; 2-17.8Hz: 7.84 mm, 17.8-500 Hz: 5g	
Shock	IEC 60068-2-27 [50g / 8ms]	
Enclosure Rating	IP67	
Mounting	Chassis	
Housing Material	Aluminum (encapsulated)	
Connection	(1) 7/8in - 16 UN2 4-pin female (1) 7/8in - 16 UN2 3-pin male Diagram 1	(1) 7/8in - 16 UN2 3-pin male (1) 7/8in - 16 UN2 5-pin female Diagram 2
Tightening Torque	1.5 N•m [13.27 lb-in]	
Weight kg [lb]	1.22 [2.68]	1.65 [3.63]
Agency Approval	UL 508 File E197592, CE	

Wiring Diagrams

Diagram 1




Diagram 2

