



Tools – Pneumatic Die Grinder

Pneumatic Die Grinder

The RUKO pneumatic grinder has a rubberized, non-slip handle that absorbs vibration and protects the users' hand from slipping while working. Speed is adjusted by a governor on top of the grinder. It has a tool adapter made of hardened steel. The exhaust port directs air backwards through the handle. It features an integrated air filter.



RUKO Pneumatic Die Grinder Specifications

Speed Range	0 - 25,000 RPM
Tool Adapter	1/4 in, collet type
Average Air Consumption	4.00 cfm (113 liters/min)
Air Inlet	1/4 in
Recommended Air Pressure	90 psi (6.2 bar)
Recommended Hose Size	3/8 in
Noise Level	77 dB(A)
Overall Length	7.75 in (196.9 mm)
Weight	1.26 lb (570 g)

RUKO Pneumatic Die Grinder

Part #	Price	Description
<u>116100US</u>	Retired	RUKO compact pneumatic grinder, 25,000 rpm, adjustable governor, rear exhaust, rubberized non-slip handle. 116101L coupling plug and (2) collet wrenches included.

RUKO Pneumatic Die Grinder Kits

<u>116112US</u>	Retired	RUKO compact pneumatic grinder set, 14 pieces, includes 116100US compact pneumatic grinder, 116101L coupling plug, 116002US tungsten carbide rotary burr set and (2) collet wrenches.
<u>116113US</u>	Retired	RUKO compact pneumatic grinder set, 7 pieces, includes 116100US compact pneumatic grinder, 116101L coupling plug, 116001US tungsten carbide rotary burr set and (2) collet wrenches.

Spare Parts

<u>116101L</u>	Retired	RUKO coupling plug, pneumatic, European, 1/4 inch nominal hose size, G1/4 male, steel (fits universal couplings)
<u>116119</u>	Retired	RUKO collet, 1/4 inch, replacement. For use with 116100US.



116112US



116119



116101L