

# Hand Taps

## Fractional and Metric Thread Hand Taps

High-speed steel fractional and metric size hand taps.



231100

### High-Speed Steel Fractional Size Hand Taps

| Coarse Thread | Part #                     | Pcs/Pkg | Price   | Thread Size | Overall Length (in.) | Use With                | Fine Thread | Part #                     | Pcs/Pkg | Price   | Thread Size | Overall Length (in.) | Use With                |
|---------------|----------------------------|---------|---------|-------------|----------------------|-------------------------|-------------|----------------------------|---------|---------|-------------|----------------------|-------------------------|
|               | <a href="#">246080UNC3</a> | 1       | \$10.50 | 8-32 UNC    | 1.77                 | <a href="#">2149029</a> |             | <a href="#">246100UNF2</a> | 1       | \$10.50 | 10-32 UNF   | 1.77                 | <a href="#">2149021</a> |
|               | <a href="#">246100UNC3</a> | 1       | \$10.50 | 10-24 UNC   | 1.97                 | <a href="#">2149025</a> |             |                            |         |         |             |                      |                         |
|               | <a href="#">246014UNC3</a> | 1       | \$6.25  | 1/4-20 UNC  | 1.97                 | <a href="#">2149007</a> |             |                            |         |         |             |                      |                         |
|               | <a href="#">246516UNC3</a> | 1       | \$6.25  | 5/16-18 UNC | 2.20                 | <a href="#">214900F</a> |             |                            |         |         |             |                      |                         |

### High-Speed Steel Metric Hand Taps


| Coarse Thread | Part #                 | Pcs/Pkg | Price  | Thread Size | Overall Length (mm) | Use With                                        | Fine Thread | Part #                   | Pcs/Pkg | Price   | Thread Size | Overall Length (mm) | Use With                                        |
|---------------|------------------------|---------|--------|-------------|---------------------|-------------------------------------------------|-------------|--------------------------|---------|---------|-------------|---------------------|-------------------------------------------------|
|               | <a href="#">231030</a> | 1       | \$4.25 | M3x0.5      | 40.0                | <a href="#">214025</a> , <a href="#">215025</a> |             | <a href="#">235041-2</a> | 1       | \$8.50  | M4x0.5      | 45.0                | <a href="#">214035</a> , <a href="#">215035</a> |
|               | <a href="#">231040</a> | 1       | \$4.25 | M4x0.7      | 45.0                | <a href="#">214033</a> , <a href="#">215033</a> |             | <a href="#">235050-2</a> | 1       | \$9.00  | M5x0.5      | 50.0                | <a href="#">214045</a> , <a href="#">215045</a> |
|               | <a href="#">231050</a> | 1       | \$4.25 | M5x0.8      | 50.0                | <a href="#">214042</a> , <a href="#">215042</a> |             | <a href="#">235081-2</a> | 1       | \$11.00 | M8x1        | 56.0                | <a href="#">214070</a> , <a href="#">215070</a> |
|               | <a href="#">231060</a> | 1       | \$4.50 | M6x1        | 50.0                | <a href="#">214050</a> , <a href="#">215050</a> |             | <a href="#">235122-2</a> | 1       | \$12.00 | M12x1       | 70.0                | <a href="#">214110</a> , <a href="#">215110</a> |
|               | <a href="#">231080</a> | 1       | \$5.00 | M8x1.25     | 56.0                | <a href="#">214068</a> , <a href="#">215068</a> |             | <a href="#">235181-2</a> | 1       | \$23.50 | M18x1       | 80.0                | 17.0 mm                                         |
|               | <a href="#">231100</a> | 1       | \$7.00 | M10x1.5     | 70.0                | <a href="#">214085</a> , <a href="#">215085</a> |             | <a href="#">235301-2</a> | 1       | \$48.50 | M30x1.5     | 90.0                | 28.5 mm                                         |
|               | <a href="#">231120</a> | 1       | \$8.50 | M12x1.75    | 75.0                | <a href="#">214102</a> , <a href="#">215102</a> |             |                          |         |         |             |                     |                                                 |

## NPT Thread Hand Taps

High-speed steel National Pipe Taper hand taps.

### High-Speed Steel NPT Hand Taps

| Part #                    | Pcs/Pkg | Price   | Thread Size | Overall Length (in.) | Use With                                                                  |
|---------------------------|---------|---------|-------------|----------------------|---------------------------------------------------------------------------|
| <a href="#">231116NPT</a> | 1       | \$16.00 | 1/16-27 NPT | 2.56                 | <a href="#">214813</a> , <a href="#">250813T</a> , <a href="#">215813</a> |
| <a href="#">231018NPT</a> | 1       | \$14.50 | 1/8-27 NPT  | 2.56                 | <a href="#">214900R</a>                                                   |
| <a href="#">231014NPT</a> | 1       | \$15.50 | 1/4-18 NPT  | 2.76                 | <a href="#">214825</a> , <a href="#">250825T</a> , <a href="#">215825</a> |
| <a href="#">231038NPT</a> | 1       | \$22.00 | 3/8-18 NPT  | 2.95                 | 37/64"                                                                    |
| <a href="#">231012NPT</a> | 1       | \$27.00 | 1/2-14 NPT  | 3.15                 | 23/32"                                                                    |



231038NPT

## Conduit Thread Hand Taps

High-speed steel DIN 40430 conduit thread hand taps.

### High-Speed Steel Conduit Thread Hand Taps

| Part #                 | Pcs/Pkg | Price   | Thread Size | Overall Length (mm) | Use With |
|------------------------|---------|---------|-------------|---------------------|----------|
| <a href="#">264009</a> | 1       | \$21.50 | PG-9        | 70.0                | 14.0 mm  |
| <a href="#">264011</a> | 1       | \$29.50 | PG-11       | 80.0                | 17.25 mm |
| <a href="#">264016</a> | 1       | \$42.00 | PG-16       | 80.0                | 21.25 mm |
| <a href="#">264021</a> | 1       | \$63.00 | PG-21       | 90.0                | 26.75 mm |
| <a href="#">264029</a> | 1       | \$97.00 | PG-29       | 100.0               | 35.5 mm  |



264029


# **RUKO** Hand Taps

245004RO

| Drill and Hand Tap Sets |         |                                                                                                                                                                                                                                                                                          |
|-------------------------|---------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Part #                  | Price   | Description                                                                                                                                                                                                                                                                              |
| <u>245004RO</u>         | \$78.00 | RUKO hand tap set, high-speed steel (HSS), 15-piece set includes: (7) metric size taps (M3, M4, M5, M6, M8, M10, M12), (7) jobber length drill bits (one for each tap), (1) tap wrench with two-jaw chuck. Includes heavy-duty plastic case.                                             |
| <u>245004USRO</u>       | \$93.00 | RUKO hand tap set, high-speed steel (HSS), 15-piece set includes: (7) SAE taps (8-32 UNC, 10-24 UNC, 10-32 UNF, 1/4-20 UNC, 1/4-28 UNF, 5/16-18 UNC, 5/16-24 UNF), (7) jobber length drill bits (one for each tap), (1) tap wrench with two-jaw chuck. Includes heavy-duty plastic case. |

# **RUKO** Tools – Hand Tap Wrenches

## Hand Tap Wrenches

241103241010

| Hand Tap Wrenches |             |         |                                        |                                                           |                               |
|-------------------|-------------|---------|----------------------------------------|-----------------------------------------------------------|-------------------------------|
| Part #            | Pcs/<br>Pkg | Price   | Description                            | Construction Material                                     | Use With                      |
| <u>241010</u>     | 1           | \$26.00 | Sliding T-handle ratcheting tap wrench | Chrome plated steel                                       | M3 to M10, 1/8" to 3/8" taps  |
| <u>241020</u>     | 1           | \$29.50 | Sliding T-handle ratcheting tap wrench | Chrome plated steel                                       | M5 to M12, 7/32" to 1/2" taps |
| <u>241112</u>     | 1           | \$7.50  | Two-jaw chuck tap wrench               | Die cast zinc housing, steel handles, hardened chuck jaws | M1 to M12, 1/8" to 1/2" taps  |