

# Enviroline Junction Series NEMA 3R, 4, 12 and 13 Operator Consolets



Your Enclosure Source®



## Applications

Designed to house electrical and electronic controls, instruments, and components. Provides protection from dust, dirt, oil and water. Consolets can be mounted on either of two sides to give a control surface inclined at 30° or 60°. Can be mounted on desks, machines, or pedestals.

## Construction

- 16-gauge carbon steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Removable hinges
- Poured-in-place oil- and water-resistant gasket
- Standoffs are provided for mounting optional subpanels.
- Cable door stops included on SCE-12C\_, SCE-16C\_ and SCE-20C\_
- Black, mini 1/4-turn latches as required.
- Latches are opened or closed with a screwdriver.
- Ground studs on door and body
- Mounting holes in back/bottom, depending on orientation

## Finish

- ANSI 61 Gray powder coated inside and out
- Optional subpanels are power coated white.

## Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4, and 12 [File E69392]
- IEC 60529 IP66



### Shipping Schedule

|          |             |
|----------|-------------|
| Same day | 1 - 15 days |
|----------|-------------|

Color indicates shipping lead time in business days.

### Enviroline Junction Series NEMA 3R, 4, 12 and 13 Operator Consolets

| Part Number                  | Price    | Size<br>HxWxD                           | Drawing<br>Link     | Optional<br>Subpanel       | Price   |
|------------------------------|----------|---|---------------------|----------------------------|---------|
| <a href="#">SCE-8C8ELJ</a>   | \$132.00 | 7.44 x 8.00 x 7.09 [189 x 203 x 180]    | <a href="#">PDF</a> | <a href="#">SCE-8P8C</a>   | \$7.25  |
| <a href="#">SCE-8C12ELJ</a>  | \$145.00 | 7.44 x 12.00 x 7.09 [189 x 305 x 180]   | <a href="#">PDF</a> | <a href="#">SCE-8P12C</a>  | \$11.75 |
| <a href="#">SCE-8C16ELJ</a>  | \$161.00 | 7.44 x 16.00 x 7.09 [189 x 406 x 180]   | <a href="#">PDF</a> | <a href="#">SCE-8P16C</a>  | \$16.00 |
| <a href="#">SCE-8C20ELJ</a>  | \$174.00 | 7.44 x 20.00 x 7.09 [189 x 508 x 180]   | <a href="#">PDF</a> | <a href="#">SCE-8P20C</a>  | \$20.50 |
| <a href="#">SCE-12C12ELJ</a> | \$171.00 | 10.91 x 12.00 x 9.09 [277 x 305 x 231]  | <a href="#">PDF</a> | <a href="#">SCE-12P12C</a> | \$18.50 |
| <a href="#">SCE-12C16ELJ</a> | \$190.00 | 10.91 x 16.00 x 9.09 [277 x 406 x 231]  | <a href="#">PDF</a> | <a href="#">SCE-12P16C</a> | \$25.50 |
| <a href="#">SCE-12C20ELJ</a> | \$210.00 | 10.91 x 20.00 x 9.09 [277 x 508 x 231]  | <a href="#">PDF</a> | <a href="#">SCE-12P20C</a> | \$32.00 |
| <a href="#">SCE-12C24ELJ</a> | \$226.00 | 10.91 x 24.00 x 9.09 [277 x 610 x 231]  | <a href="#">PDF</a> | <a href="#">SCE-12P24C</a> | \$39.00 |
| <a href="#">SCE-16C16ELJ</a> | \$223.00 | 14.38 x 16.00 x 11.09 [365 x 406 x 282] | <a href="#">PDF</a> | <a href="#">SCE-16P14</a>  | \$27.50 |
| <a href="#">SCE-16C20ELJ</a> | \$245.00 | 14.38 x 20.00 x 11.09 [365 x 508 x 282] | <a href="#">PDF</a> | <a href="#">SCE-16P20C</a> | \$43.50 |
| <a href="#">SCE-16C24ELJ</a> | \$268.00 | 14.38 x 24.00 x 11.09 [365 x 610 x 282] | <a href="#">PDF</a> | <a href="#">SCE-16P24C</a> | \$53.00 |
| <a href="#">SCE-16C30ELJ</a> | \$307.00 | 14.38 x 30.00 x 11.09 [365 x 762 x 282] | <a href="#">PDF</a> | <a href="#">SCE-16P30C</a> | \$62.00 |
| <a href="#">SCE-20C20ELJ</a> | \$281.00 | 14.38 x 36.00 x 11.09 [365 x 914 x 282] | <a href="#">PDF</a> | <a href="#">SCE-20P20C</a> | \$54.00 |
| <a href="#">SCE-20C24ELJ</a> | \$313.00 | 17.84 x 20.00 x 13.09 [453 x 508 x 332] | <a href="#">PDF</a> | <a href="#">SCE-20P24C</a> | \$59.00 |
| <a href="#">SCE-20C30ELJ</a> | \$358.00 | 17.84 x 24.00 x 13.09 [453 x 610 x 332] | <a href="#">PDF</a> | <a href="#">SCE-20P30C</a> | \$66.00 |

Note: Dimensions in inches [millimeters].