

Enviroline Junction Series NEMA 3R, 4, 12 and 13 Operator Consoles



Your Enclosure Source®



Applications

Designed to house electrical and electronic controls, instruments, and components. Provides protection from dust, dirt, oil and water. Consoles can be mounted on either of two sides to give a control surface inclined at 30° or 60°. Can be mounted on desks, machines, or pedestals.

Construction

- 16-gauge carbon steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Removable hinges
- Poured-in-place oil- and water-resistant gasket
- Standoffs are provided for mounting optional subpanels.
- Cable door stops included on SCE-12C_, SCE-16C_ and SCE-20C_
- Black, mini 1/4-turn latches as required.
- Latches are opened or closed with a screwdriver.
- Ground studs on door and body
- Mounting holes in back/bottom, depending on orientation

Finish

- ANSI 61 Gray powder coated inside and out
- Optional subpanels are power coated white.

Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Junction Series NEMA 3R, 4, 12 and 13 Operator Consoles

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-8C8ELJ	\$135.00	7.44 x 8.00 x 7.09 [189 x 203 x 180]	PDF	SCE-8P8C	\$8.25
SCE-8C12ELJ	\$149.00	7.44 x 12.00 x 7.09 [189 x 305 x 180]	PDF	SCE-8P12C	\$13.00
SCE-8C16ELJ	\$165.00	7.44 x 16.00 x 7.09 [189 x 406 x 180]	PDF	SCE-8P16C	\$18.00
SCE-8C20ELJ	\$178.00	7.44 x 20.00 x 7.09 [189 x 508 x 180]	PDF	SCE-8P20C	\$23.00
SCE-12C12ELJ	\$175.00	10.91 x 12.00 x 9.09 [277 x 305 x 231]	PDF	SCE-12P12C	\$20.50
SCE-12C16ELJ	\$195.00	10.91 x 16.00 x 9.09 [277 x 406 x 231]	PDF	SCE-12P16C	\$28.50
SCE-12C20ELJ	\$215.00	10.91 x 20.00 x 9.09 [277 x 508 x 231]	PDF	SCE-12P20C	\$36.00
SCE-12C24ELJ	\$231.00	10.91 x 24.00 x 9.09 [277 x 610 x 231]	PDF	SCE-12P24C	\$43.50
SCE-16C16ELJ	\$228.00	14.38 x 16.00 x 11.09 [365 x 406 x 282]	PDF	SCE-16P14	\$31.00
SCE-16C20ELJ	\$251.00	14.38 x 20.00 x 11.09 [365 x 508 x 282]	PDF	SCE-16P20C	\$49.00
SCE-16C24ELJ	\$274.00	14.38 x 24.00 x 11.09 [365 x 610 x 282]	PDF	SCE-16P24C	\$59.00
SCE-16C30ELJ	\$314.00	14.38 x 30.00 x 11.09 [365 x 762 x 282]	PDF	SCE-16P30C	\$70.00
SCE-20C20ELJ	\$287.00	17.84 x 20.00 x 13.09 [453 x 508 x 332]	PDF	SCE-20P20C	\$61.00
SCE-20C24ELJ	\$320.00	17.84 x 24.00 x 13.09 [453 x 610 x 332]	PDF	SCE-20P24C	\$66.00
SCE-20C30ELJ	\$367.00	17.84 x 30.00 x 13.09 [453 x 762 x 332]	PDF	SCE-20P30C	\$74.00

Note: Dimensions in inches [millimeters].