

NEMA 3R, 12, and 13 Desk Consoles



Applications

Intended for indoor use to provide a degree of protection to personnel against access to hazardous parts, also to provide a degree of protection for the equipment inside the enclosure against ingress of solid foreign objects and falling dirt, to provide a degree of protection with respect to harmful effects on the equipment due to the ingress of water, splashing water. Designed for use in a standing or sitting position with single or dual access and top that opens for easy accessibility.

Construction

- 14-gauge carbon steel
- Seams continuously welded and ground smooth
- 25° slope top
- Door props on sloped door to hold in the open position
- Poured-in-place oil- and water-resistant gasket
- Flange trough collar around all sides of door opening
- Concealed hinges
- Removable doors
- Removable print pocket
- Ground studs on door and body
- Rubber pads with provision for leveling pads on bottom of enclosure
- Black, 1/4-turn latches on top door
- Keylocking, black 3-point flush swing handle in front door of single access, front and rear doors on dual access
- Mounting studs welded on interior back for mounting optional subpanels on single access console
- Mounting channels welded on sides of interior body for mounting optional subpanels on dual access console
- Mounting hardware is included for one optional subpanel.
- Use [SCE-FSPS](#) mounting hardware Kits to mount additional subpanels on dual access consoles.

Finish

- ANSI 61 gray powder coated inside and out
- Optional panels are powder coated white.

Listings

- NEMA Type 3R, 12, and 13
- cULus Listed Type 3R and 12 [File E69392]
- IEC 60529 IP55



NEMA 3R, 12, and 13 Desk Consoles



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

NEMA 3R, 12, and 13 Desk Consoles

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
Single-Access Single-Door					
<u>SCE-403716SDC</u>	\$1,511.00	41.18 x 37.25 x 21.50 [1046 x 946 x 546]	<u>PDF</u>	<u>SCE-36P30</u>	\$157.00
<u>SCE-463719SDC</u>	\$2,032.00	47.18 x 37.25 x 24.50 [1198 x 946 x 622]	<u>PDF</u>	<u>SCE-36P36</u>	\$185.00
Dual-Access Single-Door					
<u>SCE-463719DC</u>	\$2,147.00	47.18 x 37.25 x 25.57 [1198 x 946 x 649]	<u>PDF</u>	<u>SCE-36P36</u>	\$185.00
Single-Access Double-Door					
<u>SCE-464919SDC</u>	\$2,351.00	47.18 x 49.25 x 24.50 [1198 x 1251 x 622]	<u>PDF</u>	<u>SCE-48P36</u>	\$240.00
<u>SCE-466019SDC</u>	\$3,043.00	47.18 x 59.88 x 24.50 [1198 x 1521 x 622]	<u>PDF</u>	<u>SCE-60PC36</u>	\$282.00
Dual-Access Double-Door					
<u>SCE-464919DC</u>	\$2,472.00	47.18 x 49.25 x 25.57 [1198 x 1251 x 649]	<u>PDF</u>	<u>SCE-48P36</u>	\$240.00
<u>SCE-466019DC</u>	\$3,286.00	47.18 x 59.88 x 25.57 [1198 x 1521 x 649]	<u>PDF</u>	<u>SCE-60PC36</u>	\$282.00
Note: Dimensions in inches [millimeters].					