

# Series 14 NEMA 3R, 12, and 13 Single-Door Operator Consoles



Your Enclosure Source®



## Applications

Designed for electronic controls and instruments. Equipment can be mounted on the sloping control panel door. Interior components mount to stationary panels. Heavy duty construction provides protection from dirt, oil, dust, and water.

## Construction

- 14-gauge carbon steel
- Sloping control panel door is attached with concealed hinge on bottom edge.
- Door opens 90°
- Black zinc diecast keylocking/padlocking handles on front and rear doors
- 3-point latching mechanism
- Seams continuously welded and ground smooth
- Poured-in-place oil- and water-resistant gasket on door
- Optional equipment mounts to horizontal channels welded to sides.
- Optional writing desk and top section available
- Interior print pocket
- Removable eyebolts in console body
- Ground stud on door and body
- Hole plugs are provided to seal holes in bottom of enclosure.

## Finish

- ANSI 61 gray powder coated inside and out
- Optional panels are powder coated white.

## Listings

- NEMA Type 3R, 12, and 13
- cULus Listed Type 3R and 12 [File E69392]
- IEC 60529 IP55



## Shipping Schedule

|          |             |
|----------|-------------|
| Same day | 1 - 15 days |
|----------|-------------|

Color indicates shipping lead time in business days.

## Series 14 NEMA 3R, 12, and 13 Single-Door Operator Consoles

| Console Base                     | Price      | Console Base Size<br>HxWxD                  | Drawing<br>Link     | Console Top                      | Price    | Drawing<br>Link     | Rack Mounting<br>Angle         | Price    | Writing<br>Desk                  | Price    | Drawing<br>Link     |
|----------------------------------|------------|---------------------------------------------|---------------------|----------------------------------|----------|---------------------|--------------------------------|----------|----------------------------------|----------|---------------------|
| <a href="#"><b>SCE-14B</b></a>   | \$2,426.00 | 50.00 x 24.00 x 25.06<br>[1270 x 610 x 637] | <a href="#">PDF</a> | <a href="#"><b>SCE-14T</b></a>   | \$619.00 | <a href="#">PDF</a> | <a href="#"><b>SCE-14R</b></a> | \$199.00 | <a href="#"><b>SCE-14W</b></a>   | \$179.00 | <a href="#">PDF</a> |
| <a href="#"><b>SCE-1436B</b></a> | \$2,837.00 | 50.00 x 36.00 x 25.06<br>[1270 x 914 x 637] | <a href="#">PDF</a> | <a href="#"><b>SCE-1436T</b></a> | \$767.00 | <a href="#">PDF</a> | —                              | —        | <a href="#"><b>SCE-1436W</b></a> | \$231.00 | <a href="#">PDF</a> |

Note: Dimensions in inches [millimeters].

## Series 14 NEMA 3R, 12, and 13 Single-Door Operator Console Subpanels

| Console Base                     | Optional<br>Swing-Out Panel       | Price    | Optional<br>Full-Height Subpanel  | Price    | Optional Half-Height<br>Subpanel  | Price    |
|----------------------------------|-----------------------------------|----------|-----------------------------------|----------|-----------------------------------|----------|
| <a href="#"><b>SCE-14B</b></a>   | <a href="#"><b>SCE-14P3</b></a>   | \$288.00 | <a href="#"><b>SCE-14P3</b></a>   | \$288.00 | <a href="#"><b>SCE-14P2</b></a>   | \$200.00 |
| <a href="#"><b>SCE-1436B</b></a> | <a href="#"><b>SCE-1436P3</b></a> | \$380.00 | <a href="#"><b>SCE-1436P3</b></a> | \$380.00 | <a href="#"><b>SCE-1436P2</b></a> | \$246.00 |