

NEMA 3R, 12, and 13 Single-Door Freestanding



Applications

Designed to house a variety of electrical and electronic controls and instruments. Provisions for optional surface mounting or rack mounting of almost any type of equipment. Provides protection from dust, dirt, water and oil. For outdoor application a drip shield and drain holes are required. The enclosures are extra deep for applications requiring more interior space.

Construction

- 12-gauge carbon steel
- Concealed hinges
- Removable and interchangeable doors
- Flange trough collar around all sides of door opening
- Seams continuously welded and ground smooth— no holes or knockouts
- Lifting eyes for easy handling
- Black zinc diecast keylocking/padlocking handle
- 3-point latching mechanism
- Latch rods have ramp shoes for easier door closing.
- Removable print pocket is provided on door.
- Black, 1/4-turn latches, as required
- Mounting channels are welded horizontally on sides of interior body at top, bottom and middle for mounting optional panels or rack mounting angles.
- Hole plugs are provided to seal holes in bottom of enclosure.
- Poured-in-place oil- and water-resistant gasket
- Ground stud on door and body
- Provisions for light kit

Finish

- ANSI 61 Gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 12, and 13
- cULus Listed Type 3R and 12 [File E69392]
- IEC 60529 IP55



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

NEMA 3R, 12, and 13 Single-Door Freestanding Enclosures

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-603624FS	\$1,843.00	60.00 x 36.00 x 25.05 [1524 x 914 x 636]	PDF	SCE-60P36F1	\$314.00
SCE-723618FS	\$1,864.00	72.00 x 36.00 x 19.05 [1829 x 914 x 484]	PDF	SCE-72P36F1	\$359.00
SCE-723624FS	\$2,057.00	72.00 x 36.00 x 25.05 [1829 x 914 x 636]	PDF	SCE-72P36F1	\$359.00
SCE-723630FS	\$2,253.00	72.00 x 36.00 x 31.05 [1829 x 914 x 789]	PDF	SCE-72P36F1	\$359.00
SCE-723636FS	\$2,446.00	72.00 x 36.00 x 37.05 [1829 x 914 x 941]	PDF	SCE-72P36F1	\$359.00
SCE-903620FS	\$2,421.00	90.00 x 36.00 x 21.05 [2286 x 914 x 535]	PDF	SCE-90P36F1	\$431.00
SCE-903624FS	\$2,575.00	90.00 x 36.00 x 25.05 [2286 x 914 x 636]	PDF	SCE-90P36F1	\$431.00
SCE-903636FS	\$3,027.00	90.00 x 36.00 x 37.05 [2286 x 914 x 941]	PDF	SCE-90P36F1	\$431.00

Note: Dimensions in inches [millimeters].