

NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Double-Door Freestanding



Your Enclosure Source®



Applications

Designed to house a variety of electrical and electronic controls and instruments. Provisions for optional surface mounting or rack mounting of almost any type of equipment. Provides a degree of protection from dust, dirt, water and oil. The enclosures are extra deep for applications requiring more interior space.

Construction

- 12-gauge stainless steel Type 304
- Removable and interchangeable doors
- Stainless steel concealed hinges
- Seams continuously welded and ground smooth
- Strong, rigid construction with stiffeners welded on backs of single access boxes
- Lifting eyes for easy handling
- Black zinc diecast keylocking/padlocking handle
- 3-point latching mechanism
- Latch rods have ramp shoes for easier door closing.
- Flange trough collar around all sides of door opening
- A removable print pocket is provided on door with 3-point latch.
- Mounting channels are welded horizontally on sides of interior body at top, bottom and middle for mounting optional panels or rack mounting angles.
- Poured-in-place oil- and water-resistant gasket
- Ground stud on door and body
- Provisions for light kit

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 12, and 13
- cULus Listed Type 3R and 12 [File E69392]
- IEC 60529 IP55



Shipping Schedule

| | |
|----------|-------------|
| Same day | 1 - 15 days |
|----------|-------------|

Color indicates shipping lead time in business days.

NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Double-Door Freestanding

| Part Number | Price | Size HxWxD | Drawing Link | Optional Subpanel | Price |
|---------------------------------|-------------|---|---------------------|-----------------------------|----------|
| SCE-604818SSFSD | \$8,299.00 | 60.00 x 48.00 x 19.05 [1524 x 1219 x 484] | PDF | SCE-60P48F1 | \$503.00 |
| SCE-724818SSFSD | \$9,141.00 | 72.00 x 48.00 x 19.05 [1829 x 1219 x 484] | PDF | SCE-72P48F1 | \$569.00 |
| SCE-724824SSFSD | \$9,903.00 | 72.00 x 48.00 x 25.05 [1829 x 1219 x 636] | PDF | SCE-72P48F1 | \$569.00 |
| SCE-726018SSFSD | \$10,284.00 | 72.00 x 60.00 x 19.05 [1829 x 1524 x 484] | PDF | SCE-72P60F1 | \$658.00 |
| SCE-726024SSFSD | \$11,126.00 | 72.00 x 60.00 x 25.05 [1829 x 1524 x 636] | PDF | SCE-72P60F1 | \$658.00 |
| SCE-726036SSFSD | \$12,800.00 | 72.00 x 60.00 x 37.05 [1829 x 1524 x 941] | PDF | SCE-72P60F1 | \$658.00 |
| SCE-727218SSFSD | \$11,426.00 | 72.00 x 72.00 x 19.05 [1829 x 1829 x 484] | PDF | SCE-72P72F1 | \$752.00 |
| SCE-727224SSFSD | \$12,350.00 | 72.00 x 72.00 x 25.05 [1829 x 1829 x 636] | PDF | SCE-72P72F1 | \$752.00 |
| SCE-904820SSFSD | \$10,861.00 | 90.00 x 48.00 x 21.05 [2286 x 1219 x 535] | PDF | SCE-90P48F1 | \$669.00 |
| SCE-907220SSFSD | \$13,654.00 | 90.00 x 72.00 x 21.05 [2286 x 1829 x 535] | PDF | SCE-90P72F1 | \$903.00 |
| SCE-907224SSFSD | \$14,335.00 | 90.00 x 72.00 x 25.05 [2286 x 1829 x 636] | PDF | SCE-90P72F1 | \$903.00 |
| SCE-907236SSFSD | \$16,401.00 | 90.00 x 72.00 x 37.05 [2286 x 1829 x 941] | PDF | SCE-90P72F1 | \$903.00 |

Note: Dimensions in inches [millimeters].

NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Double-Door Freestanding



Dimensions

