

NEMA 4, 4X, 12, and 13 30mm Stainless Steel Wall-Mount Pushbutton



Applications

Designed to house standard pushbuttons, switches and pilot lights in wet and hosed down areas and in corrosive atmospheres.

Construction

- 16-gauge stainless steel Type 304 or 316/316L
- Continuously-welded seams
- Captivated cover screws thread into sealed wells.
- 4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights.
 - Hole diameter is 1.20in [30.5 mm]
- Fully-removable cover
- Poured-in-place oil- and water-resistant gasket
- Welded mounting provision top and bottom of back

Finish

- #4 brushed finish on all exterior surfaces

Listings

- NEMA Type 4, 4X, 12, and 13
- cULus Listed Type 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

30mm NEMA 4, 4X, 12, and 13 Stainless Steel Wall-Mount Pushbutton

304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Holes	Drawing Link
SCE-1PBSS	\$149.00	SCE-1PBSS6	\$185.00	3.81 x 3.56 x 2.91 [97 x 90 x 74]	1	PDF
SCE-1PBXSS	\$198.00	SCE-1PBXSS6	\$247.00	4.31 x 4.31 x 4.91 [109 x 109 x 125]	1	PDF
SCE-2PBSS	\$186.00	SCE-2PBSS6	\$232.00	6.06 x 3.56 x 2.91 [154 x 90 x 74]	2	PDF
SCE-2PBXSS	\$248.00	SCE-2PBXSS6	\$309.00	6.31 x 4.31 x 4.91 [160 x 109 x 125]	2	PDF
SCE-3PBSS	\$203.00	SCE-3PBSS6	\$253.00	8.31 x 3.56 x 2.91 [211 x 90 x 74]	3	PDF
SCE-3PBXSS	\$264.00	—	—	8.31 x 4.31 x 4.91 [211 x 109 x 125]	3	PDF
SCE-4PBSS	\$230.00	SCE-4PBSS6	\$286.00	10.56 x 3.56 x 2.91 [268 x 90 x 74]	4	PDF
SCE-4PBXSS	\$274.00	SCE-4PBXSS6	\$341.00	10.31 x 4.31 x 4.91 [262 x 109 x 125]	4	PDF
SCE-4SPBSS	\$253.00	SCE-4SPBSS6	\$315.00	7.56 x 6.56 x 3.16 [192 x 167 x 80]	4	PDF
SCE-6PBSS	\$302.00	SCE-6PBSS6	\$376.00	9.81 x 6.56 x 3.16 [249 x 167 x 80]	6	PDF
SCE-9PBSS	\$341.00	SCE-9PBSS6	\$425.00	9.81 x 8.81 x 3.16 [249 x 224 x 80]	9	PDF
SCE-12PBSS	\$390.00	SCE-12PBSS6	\$485.00	12.06 x 8.81 x 3.16 [306 x 224 x 80]	12	PDF

Note: Dimensions in inches [millimeters].