

NEMA 1 Single-Door Wall-Mount



Applications

Designed to house electrical controls, instruments, and components in areas that do not require oil, water and dust tight protection.

Construction

- 14-gauge, 16-gauge, or 18-gauge carbon steel depending on size
 - See drawings for details
- Spot weld construction
- Standoffs are provided for mounting optional subpanels.
- Butt hinge
- Doors open 180°
- Black, 1/4-turn latches
- Latches are opened or closed with a screwdriver.
- Ground stud on door and body
- Mounting holes in back of enclosure
- Subpanel mounting hardware included
- Optional mounting straps are available.

Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 1
- cULus Listed Type 1
- IEC 60529 IP30



NEMA 1 Single-Door Wall-Mount



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

NEMA 1 Single-Door Wall-Mount

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-6N604LP	\$47.50	6.38 x 6.38 x 4.12 [162 x 162 x 105]	PDF	SCE-6N6MP	\$4.75
SCE-8N604LP	\$52.00	8.38 x 6.38 x 4.12 [213 x 162 x 105]	PDF	SCE-8N6MP	\$5.50
SCE-8N804LP	\$58.00	8.38 x 8.38 x 4.12 [213 x 213 x 105]	PDF	SCE-8N8MP	\$6.50
SCE-8N806LP	\$65.00	8.38 x 8.38 x 6.12 [213 x 213 x 155]	PDF	SCE-8N8MP	\$6.50
SCE-10N804LP	\$63.00	10.38 x 8.38 x 4.12 [264 x 213 x 105]	PDF	SCE-10N8MP	\$7.50
SCE-10N806LP	\$72.00	10.38 x 8.38 x 6.12 [264 x 213 x 155]	PDF	SCE-10N8MP	\$7.50
SCE-10N1004LP	\$64.00	10.38 x 10.38 x 4.12 [264 x 264 x 105]	PDF	SCE-10N10MP	\$8.75
SCE-10N1006LP	\$79.00	10.38 x 10.38 x 6.12 [264 x 264 x 155]	PDF	SCE-10N10MP	\$8.75
SCE-12N1004LP	\$76.00	12.38 x 10.38 x 4.12 [314 x 264 x 105]	PDF	SCE-12N10MP	\$10.00
SCE-12N1006LP	\$86.00	12.38 x 10.38 x 6.12 [314 x 264 x 155]	PDF	SCE-12N10MP	\$10.00
SCE-12N1204LP	\$84.00	12.38 x 12.38 x 4.12 [314 x 314 x 105]	PDF	SCE-12N12MP	\$12.00
SCE-12N1206LP	\$95.00	12.38 x 12.38 x 6.12 [314 x 314 x 155]	PDF	SCE-12N12MP	\$12.00
SCE-12N1208LP	\$106.00	12.38 x 12.38 x 8.12 [314 x 314 x 206]	PDF	SCE-12N12MP	\$12.00
SCE-14N1204LP	\$91.00	14.38 x 12.38 x 4.12 [365 x 314 x 105]	PDF	SCE-14N12MP	\$13.25
SCE-14N1206LP	\$103.00	14.38 x 12.38 x 6.12 [365 x 314 x 155]	PDF	SCE-14N12MP	\$13.25
SCE-14N1208LP	\$115.00	14.38 x 12.38 x 8.12 [365 x 314 x 206]	PDF	SCE-14N12MP	\$13.25
SCE-16N1206LP	\$154.00	16.38 x 12.38 x 6.12 [416 x 314 x 155]	PDF	SCE-16N12MP	\$19.50
SCE-16N1208LP	\$168.00	16.38 x 12.38 x 8.12 [416 x 314 x 206]	PDF	SCE-16N12MP	\$19.50
SCE-16N1606LP	\$172.00	16.38 x 16.38 x 6.12 [416 x 416 x 155]	PDF	SCE-16N16MP	\$32.00
SCE-16N1608LP	\$188.00	16.38 x 16.38 x 8.12 [416 x 416 x 206]	PDF	SCE-16N16MP	\$32.00
SCE-16N2006LP	\$191.00	16.38 x 20.38 x 6.12 [416 x 518 x 155]	PDF	SCE-20N16MP	\$36.50
SCE-20N1606LP	\$191.00	20.38 x 16.38 x 6.12 [518 x 416 x 155]	PDF	SCE-20N16MP	\$36.50
SCE-20N1608LP	\$208.00	20.38 x 16.38 x 8.12 [518 x 416 x 206]	PDF	SCE-20N16MP	\$36.50
SCE-20N2006LP	\$209.00	20.38 x 20.38 x 6.12 [518 x 518 x 155]	PDF	SCE-20N20MP	\$46.50
SCE-20N2008LP	\$229.00	20.38 x 20.38 x 8.12 [518 x 518 x 206]	PDF	SCE-20N20MP	\$46.50
SCE-20N2010LP	\$249.00	20.38 x 20.38 x 10.12 [518 x 518 x 257]	PDF	SCE-20N20MP	\$46.50
SCE-24N1606LP	\$208.00	24.38 x 16.38 x 6.12 [619 x 416 x 155]	PDF	SCE-24N16MP	\$38.50
SCE-24N2006LP	\$232.00	24.38 x 20.38 x 6.12 [619 x 518 x 155]	PDF	SCE-24N20MP	\$53.00
SCE-24N2008LP	\$253.00	24.38 x 20.38 x 8.12 [619 x 518 x 206]	PDF	SCE-24N20MP	\$53.00
SCE-24N2406LP	\$235.00	24.38 x 24.38 x 6.12 [619 x 619 x 155]	PDF	SCE-24N24MP	\$62.00
SCE-24N2408LP	\$259.00	24.38 x 24.38 x 8.12 [619 x 619 x 206]	PDF	SCE-24N24MP	\$62.00
SCE-24N2010LP	\$275.00	24.38 x 20.38 x 10.12 [619 x 518 x 257]	PDF	SCE-24N20MP	\$53.00
SCE-24N2412LP	\$306.00	24.38 x 24.38 x 12.12 [619 x 619 x 308]	PDF	SCE-24N24MP	\$62.00
SCE-30N2406LP	\$261.00	30.38 x 24.38 x 6.12 [772 x 619 x 155]	PDF	SCE-30N24MP	\$74.00
SCE-30N2408LP	\$290.00	30.38 x 24.38 x 8.12 [772 x 619 x 206]	PDF	SCE-30N24MP	\$74.00
SCE-30N2412LP	\$341.00	30.38 x 24.38 x 12.12 [772 x 619 x 308]	PDF	SCE-30N24MP	\$74.00
SCE-30N3008LP	\$327.00	30.38 x 30.38 x 8.12 [772 x 772 x 206]	PDF	SCE-30N30MP	\$97.00
SCE-36N2406LP	\$494.00	36.38 x 24.38 x 6.12 [924 x 619 x 155]	PDF	SCE-36N24MP	\$89.00
SCE-36N2408LP	\$515.00	36.38 x 24.38 x 8.12 [924 x 619 x 206]	PDF	SCE-36N24MP	\$89.00
SCE-36N2412LP	\$552.00	36.38 x 24.38 x 12.12 [924 x 619 x 308]	PDF	SCE-36N24MP	\$89.00
SCE-36N3006LP	\$514.00	36.38 x 30.38 x 6.12 [924 x 772 x 155]	PDF	SCE-36N30MP	\$118.00
SCE-36N3008LP	\$537.00	36.38 x 30.38 x 8.12 [924 x 772 x 206]	PDF	SCE-36N30MP	\$118.00
SCE-36N3012LP	\$584.00	36.38 x 30.38 x 12.12 [924 x 772 x 308]	PDF	SCE-36N30MP	\$118.00

Note: Dimensions in inches [millimeters].