

NEMA 3R, 4, 12, and 13 Padlocking Single-Door Wall-Mount



Your Enclosure Source®



Applications

Designed to house electrical and electronic controls, instrumentation and components. Provides protection from dust, dirt, oil and water.

Construction

- 14-gauge carbon steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Door clamps are quick and easy to operate.
- Concealed hinges
- Hasp and staple for padlocking
- Poured-in-place oil- and water-resistant gasket
- Collar studs for mounting optional subpanels
- Ground studs on door and body
- Removable print pocket furnished if height and width of enclosure is greater than 12in [305mm].
- Mounting provision top and bottom of back
- Provision for lifting lugs included on enclosures with height greater than 48in [1219mm] and with depth greater than 16in [406mm].
- Lifting lug assembly included with the enclosure bolt pack

Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-12H2406LP	\$307.00	12.00 x 24.00 x 7.07 [305 x 610 x 180]	PDF	SCE-12P24	\$38.50
SCE-12H2408LP	\$327.00	12.00 x 24.00 x 9.07 [305 x 610 x 230]	PDF	SCE-12P24	\$38.50
SCE-16H1206LP	\$275.00	16.00 x 12.00 x 7.07 [406 x 305 x 180]	PDF	SCE-16P12	\$20.50
SCE-16H1208LP	\$288.00	16.00 x 12.00 x 9.07 [406 x 305 x 230]	PDF	SCE-16P12	\$20.50
SCE-16H1210LP	\$301.00	16.00 x 12.00 x 11.07 [406 x 305 x 281]	PDF	SCE-16P12	\$20.50
SCE-16H1606LP	\$294.00	16.00 x 16.00 x 7.07 [406 x 406 x 180]	PDF	SCE-16P16	\$34.00
SCE-16H1608LP	\$310.00	16.00 x 16.00 x 9.07 [406 x 406 x 230]	PDF	SCE-16P16	\$34.00
SCE-16H2006LP	\$317.00	16.00 x 20.00 x 7.07 [406 x 508 x 180]	PDF	SCE-20P16	\$42.00
SCE-16H2008LP	\$333.00	16.00 x 20.00 x 9.07 [406 x 508 x 230]	PDF	SCE-20P16	\$42.00
SCE-20H1206LP	\$291.00	20.00 x 12.00 x 7.07 [508 x 305 x 180]	PDF	SCE-20P12	\$32.00
SCE-20H1208LP	\$307.00	20.00 x 12.00 x 9.07 [508 x 305 x 230]	PDF	SCE-20P12	\$32.00
SCE-20H1606LP	\$317.00	20.00 x 16.00 x 7.07 [508 x 406 x 180]	PDF	SCE-20P16	\$42.00
SCE-20H1608LP	\$333.00	20.00 x 16.00 x 9.07 [508 x 406 x 230]	PDF	SCE-20P16	\$42.00
SCE-20H1610LP	\$349.00	20.00 x 16.00 x 11.07 [508 x 406 x 281]	PDF	SCE-20P16	\$42.00
SCE-20H1612LP	\$369.00	20.00 x 16.00 x 13.07 [508 x 406 x 332]	PDF	SCE-20P16	\$42.00
SCE-20H2006LP	\$340.00	20.00 x 20.00 x 7.07 [508 x 508 x 180]	PDF	SCE-20P20	\$49.00
SCE-20H2008LP	\$359.00	20.00 x 20.00 x 9.07 [508 x 508 x 230]	PDF	SCE-20P20	\$49.00
SCE-20H2010LP	\$378.00	20.00 x 20.00 x 11.07 [508 x 508 x 281]	PDF	SCE-20P20	\$49.00

Note: Dimensions in inches [millimeters].

Table continued on next page

NEMA 3R, 4, 12, and 13 Padlocking Single-Door Wall-Mount

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.



Your Enclosure Source®

Table continued from previous page.

NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount					
Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-20H2406LP	\$365.00	20.00 x 24.00 x 7.07 [508 x 610 x 180]	PDF	SCE-24P20	\$63.00
SCE-20H2408LP	\$387.00	20.00 x 24.00 x 9.07 [508 x 610 x 230]	PDF	SCE-24P20	\$63.00
SCE-20H3006LP	\$440.00	20.00 x 30.00 x 7.07 [508 x 762 x 180]	PDF	SCE-30P20	\$77.00
SCE-24H1206LP	\$307.00	24.00 x 12.00 x 7.07 [610 x 305 x 180]	PDF	SCE-12P24	\$38.50
SCE-24H1208LP	\$327.00	24.00 x 12.00 x 9.07 [610 x 305 x 230]	PDF	SCE-12P24	\$38.50
SCE-24H1210LP	\$343.00	24.00 x 12.00 x 11.07 [610 x 305 x 281]	PDF	SCE-12P24	\$38.50
SCE-24H1606LP	\$336.00	24.00 x 16.00 x 7.07 [610 x 406 x 180]	PDF	SCE-24P16	\$45.50
SCE-24H1608LP	\$356.00	24.00 x 16.00 x 9.07 [610 x 406 x 230]	PDF	SCE-24P16	\$45.50
SCE-24H2006LP	\$365.00	24.00 x 20.00 x 7.07 [610 x 508 x 180]	PDF	SCE-24P20	\$63.00
SCE-24H2008LP	\$388.00	24.00 x 20.00 x 9.07 [610 x 508 x 230]	PDF	SCE-24P20	\$63.00
SCE-24H2010LP	\$408.00	24.00 x 20.00 x 11.07 [610 x 508 x 281]	PDF	SCE-24P20	\$63.00
SCE-24H2012LP	\$430.00	24.00 x 20.00 x 13.07 [610 x 508 x 332]	PDF	SCE-24P20	\$63.00
SCE-24H2016LP	\$472.00	24.00 x 20.00 x 17.07 [610 x 508 x 434]	PDF	SCE-24P20	\$63.00
SCE-24H2406LP	\$395.00	24.00 x 24.00 x 7.07 [610 x 610 x 180]	PDF	SCE-24P24	\$74.00
SCE-24H2408LP	\$417.00	24.00 x 24.00 x 9.07 [610 x 610 x 230]	PDF	SCE-24P24	\$74.00
SCE-24H2410LP	\$440.00	24.00 x 24.00 x 11.07 [610 x 610 x 281]	PDF	SCE-24P24	\$74.00
SCE-24H2412LP	\$462.00	24.00 x 24.00 x 13.07 [610 x 610 x 332]	PDF	SCE-24P24	\$74.00
SCE-24H2416LP	\$508.00	24.00 x 24.00 x 17.07 [610 x 610 x 434]	PDF	SCE-24P24	\$74.00
SCE-24H3008LP	\$462.00	24.00 x 30.00 x 9.07 [610 x 762 x 230]	PDF	SCE-30P24	\$88.00
SCE-30H1606LP	\$369.00	30.00 x 16.00 x 7.07 [762 x 406 x 180]	PDF	SCE-30P16	\$63.00
SCE-30H2006LP	\$401.00	30.00 x 20.00 x 7.07 [762 x 508 x 180]	PDF	SCE-30P20	\$77.00
SCE-30H2008LP	\$427.00	30.00 x 20.00 x 9.07 [762 x 508 x 230]	PDF	SCE-30P20	\$77.00
SCE-30H2010LP	\$450.00	30.00 x 20.00 x 11.07 [762 x 508 x 281]	PDF	SCE-30P20	\$77.00
SCE-30H2406LP	\$437.00	30.00 x 24.00 x 7.07 [762 x 610 x 180]	PDF	SCE-30P24	\$88.00
SCE-30H2408LP	\$462.00	30.00 x 24.00 x 9.07 [762 x 610 x 230]	PDF	SCE-30P24	\$88.00
SCE-30H2410LP	\$488.00	30.00 x 24.00 x 11.07 [762 x 610 x 281]	PDF	SCE-30P24	\$88.00
SCE-30H2412LP	\$514.00	30.00 x 24.00 x 13.07 [762 x 610 x 332]	PDF	SCE-30P24	\$88.00
SCE-30H2416LP	\$566.00	30.00 x 24.00 x 17.07 [762 x 610 x 434]	PDF	SCE-30P24	\$88.00
SCE-30H2420LP	\$618.00	30.00 x 24.00 x 21.07 [762 x 610 x 535]	PDF	SCE-30P24	\$88.00
SCE-30H2424LP	\$670.00	30.00 x 24.00 x 25.07 [762 x 610 x 637]	PDF	SCE-30P24	\$88.00
SCE-30H3008LP	\$517.00	30.00 x 30.00 x 9.07 [762 x 762 x 230]	PDF	SCE-30P30	\$116.00
SCE-30H3012LP	\$576.00	30.00 x 30.00 x 13.07 [762 x 762 x 332]	PDF	SCE-30P30	\$116.00
SCE-30H3608LP	\$572.00	30.00 x 36.00 x 9.07 [762 x 914 x 230]	PDF	SCE-36P30	\$141.00
SCE-36H1606LP	\$391.00	36.00 x 16.00 x 7.07 [914 x 406 x 180]	PDF	SCE-36P16	\$74.00
SCE-36H2406LP	\$479.00	36.00 x 24.00 x 7.07 [914 x 610 x 180]	PDF	SCE-36P24	\$105.00
SCE-36H2408LP	\$508.00	36.00 x 24.00 x 9.07 [914 x 610 x 230]	PDF	SCE-36P24	\$105.00
SCE-36H2410LP	\$537.00	36.00 x 24.00 x 11.07 [914 x 610 x 281]	PDF	SCE-36P24	\$105.00
SCE-36H2412LP	\$566.00	36.00 x 24.00 x 13.07 [914 x 610 x 332]	PDF	SCE-36P24	\$105.00
SCE-36H2416LP	\$631.00	36.00 x 24.00 x 17.07 [914 x 610 x 434]	PDF	SCE-36P24	\$105.00
SCE-36H3006LP	Retired	36.00 x 30.00 x 7.07 [914 x 762 x 180]	PDF	SCE-36P30	\$141.00

Note: Dimensions in inches [millimeters].

Table continued on next page

NEMA 3R, 4, 12, and 13 Padlocking Single-Door Wall-Mount

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.



Your Enclosure Source®

Table continued from previous page.

NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount					
Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-36H3008LP	\$572.00	36.00 x 30.00 x 9.07 [914 x 762 x 230]	PDF	SCE-36P30	\$141.00
SCE-36H3010LP	\$605.00	36.00 x 30.00 x 11.07 [914 x 762 x 281]	PDF	SCE-36P30	\$141.00
SCE-36H3012LP	\$634.00	36.00 x 30.00 x 13.07 [914 x 762 x 332]	PDF	SCE-36P30	\$141.00
SCE-36H3016LP	\$699.00	36.00 x 30.00 x 17.07 [914 x 762 x 434]	PDF	SCE-36P30	\$141.00
SCE-36H3020LP	\$760.00	36.00 x 30.00 x 21.07 [914 x 762 x 535]	PDF	SCE-36P30	\$141.00
SCE-36H3608LP	\$634.00	36.00 x 36.00 x 9.07 [914 x 914 x 230]	PDF	SCE-36P36	\$165.00
SCE-36H3612LP	\$705.00	36.00 x 36.00 x 13.07 [914 x 914 x 332]	PDF	SCE-36P36	\$165.00
SCE-36H3616LP	\$773.00	36.00 x 36.00 x 17.07 [914 x 914 x 434]	PDF	SCE-36P36	\$165.00
SCE-42H2408LP	\$556.00	42.00 x 24.00 x 9.07 [1067 x 610 x 230]	PDF	SCE-42P24	\$127.00
SCE-42H3008LP	\$627.00	42.00 x 30.00 x 9.07 [1067 x 762 x 230]	PDF	SCE-42P30	\$162.00
SCE-42H3010LP	\$660.00	42.00 x 30.00 x 11.07 [1067 x 762 x 281]	PDF	SCE-42P30	\$162.00
SCE-42H3012LP	\$695.00	42.00 x 30.00 x 13.07 [1067 x 762 x 332]	PDF	SCE-42P30	\$162.00
SCE-42H3016LP	\$767.00	42.00 x 30.00 x 17.07 [1067 x 762 x 434]	PDF	SCE-42P30	\$162.00
SCE-42H3608LP	\$699.00	42.00 x 36.00 x 9.07 [1067 x 914 x 230]	PDF	SCE-42P36	\$190.00
SCE-42H3610LP	\$734.00	42.00 x 36.00 x 11.07 [1067 x 914 x 281]	PDF	SCE-42P36	\$190.00
SCE-42H3612LP	\$773.00	42.00 x 36.00 x 13.07 [1067 x 914 x 332]	PDF	SCE-42P36	\$190.00
SCE-42H3616LP	\$847.00	42.00 x 36.00 x 17.07 [1067 x 914 x 434]	PDF	SCE-42P36	\$190.00
SCE-48H2408LP	\$602.00	48.00 x 24.00 x 9.07 [1219 x 610 x 230]	PDF	SCE-48P24	\$137.00
SCE-48H3008LP	\$682.00	48.00 x 30.00 x 9.07 [1219 x 762 x 230]	PDF	SCE-48P30	\$179.00
SCE-48H3010LP	\$718.00	48.00 x 30.00 x 11.07 [1219 x 762 x 281]	PDF	SCE-48P30	\$179.00
SCE-48H3016LP	\$831.00	48.00 x 30.00 x 17.07 [1219 x 762 x 434]	PDF	SCE-48P30	\$179.00
SCE-48H3608LP	\$760.00	48.00 x 36.00 x 9.07 [1219 x 914 x 230]	PDF	SCE-48P36	\$214.00
SCE-48H3610LP	\$802.00	48.00 x 36.00 x 11.07 [1219 x 914 x 281]	PDF	SCE-48P36	\$214.00
SCE-48H3612LP	\$841.00	48.00 x 36.00 x 13.07 [1219 x 914 x 332]	PDF	SCE-48P36	\$214.00
SCE-48H3616LP	\$922.00	48.00 x 36.00 x 17.07 [1219 x 914 x 434]	PDF	SCE-48P36	\$214.00
SCE-48H3620LP	\$1,003.00	48.00 x 36.00 x 21.07 [1219 x 914 x 535]	PDF	SCE-48P36	\$214.00
SCE-60H3608LP	\$886.00	60.00 x 36.00 x 9.07 [1524 x 914 x 230]	PDF	SCE-60P36	\$264.00
SCE-60H3610LP	\$935.00	60.00 x 36.00 x 11.07 [1524 x 914 x 281]	PDF	SCE-60P36	\$264.00
SCE-60H3612LP	\$980.00	60.00 x 36.00 x 13.07 [1524 x 914 x 332]	PDF	SCE-60P36	\$264.00
SCE-60H3616LP	\$1,071.00	60.00 x 36.00 x 17.07 [1524 x 914 x 434]	PDF	SCE-60P36	\$264.00
SCE-60H3620LP	\$1,164.00	60.00 x 36.00 x 21.07 [1524 x 914 x 535]	PDF	SCE-60P36	\$264.00
SCE-72H3012LP	\$1,048.00	72.00 x 30.00 x 13.07 [1829 x 762 x 332]	PDF	SCE-72P30	\$292.00
SCE-72H3016LP	\$1,198.00	72.00 x 30.00 x 17.07 [1829 x 762 x 434]	PDF	SCE-72P30	\$292.00
SCE-72H3024LP	\$1,316.00	72.00 x 30.00 x 25.07 [1829 x 762 x 637]	PDF	SCE-72P30	\$292.00
SCE-72H3612LP	\$1,119.00	72.00 x 36.00 x 13.07 [1829 x 914 x 332]	PDF	SCE-72P36	\$313.00
SCE-72H3616LP	\$1,271.00	72.00 x 36.00 x 17.07 [1829 x 914 x 434]	PDF	SCE-72P36	\$313.00

Note: Dimensions in inches [millimeters].

NEMA 3R, 4, 12, and 13 Padlocking Single-Door Wall-Mount



Dimensions

