

NEMA 3R, 4, 12, and 13 Padlocking Single-Door Wall-Mount



Your Enclosure Source®



Applications

Designed to house electrical and electronic controls, instrumentation and components. Provides protection from dust, dirt, oil and water.

Construction

- 14-gauge carbon steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Door clamps are quick and easy to operate.
- Concealed hinges
- Hasp and staple for padlocking
- Poured-in-place oil- and water-resistant gasket
- Collar studs for mounting optional subpanels
- Ground studs on door and body
- Removable print pocket furnished if height and width of enclosure is greater than 12in [305mm].
- Mounting provision top and bottom of back
- Provision for lifting lugs included on enclosures with height greater than 48in [1219mm] and with depth greater than 16in [406mm].
- Lifting lug assembly included with the enclosure bolt pack

Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-12H2406LP	\$317.00	12.00 x 24.00 x 7.07 [305 x 610 x 180]	PDF	SCE-12P24	\$43.50
SCE-12H2408LP	\$337.00	12.00 x 24.00 x 9.07 [305 x 610 x 230]	PDF	SCE-12P24	\$43.50
SCE-16H1206LP	\$284.00	16.00 x 12.00 x 7.07 [406 x 305 x 180]	PDF	SCE-16P12	\$23.00
SCE-16H1208LP	\$297.00	16.00 x 12.00 x 9.07 [406 x 305 x 230]	PDF	SCE-16P12	\$23.00
SCE-16H1210LP	\$311.00	16.00 x 12.00 x 11.07 [406 x 305 x 281]	PDF	SCE-16P12	\$23.00
SCE-16H1606LP	\$304.00	16.00 x 16.00 x 7.07 [406 x 406 x 180]	PDF	SCE-16P16	\$38.00
SCE-16H1608LP	\$321.00	16.00 x 16.00 x 9.07 [406 x 406 x 230]	PDF	SCE-16P16	\$38.00
SCE-16H2006LP	\$327.00	16.00 x 20.00 x 7.07 [406 x 508 x 180]	PDF	SCE-20P16	\$47.00
SCE-16H2008LP	\$344.00	16.00 x 20.00 x 9.07 [406 x 508 x 230]	PDF	SCE-20P16	\$47.00
SCE-20H1206LP	\$301.00	20.00 x 12.00 x 7.07 [508 x 305 x 180]	PDF	SCE-20P12	\$36.00
SCE-20H1208LP	\$317.00	20.00 x 12.00 x 9.07 [508 x 305 x 230]	PDF	SCE-20P12	\$36.00
SCE-20H1606LP	\$327.00	20.00 x 16.00 x 7.07 [508 x 406 x 180]	PDF	SCE-20P16	\$47.00
SCE-20H1608LP	\$344.00	20.00 x 16.00 x 9.07 [508 x 406 x 230]	PDF	SCE-20P16	\$47.00
SCE-20H1610LP	\$361.00	20.00 x 16.00 x 11.07 [508 x 406 x 281]	PDF	SCE-20P16	\$47.00
SCE-20H1612LP	\$381.00	20.00 x 16.00 x 13.07 [508 x 406 x 332]	PDF	SCE-20P16	\$47.00
SCE-20H2006LP	\$351.00	20.00 x 20.00 x 7.07 [508 x 508 x 180]	PDF	SCE-20P20	\$55.00
SCE-20H2008LP	\$371.00	20.00 x 20.00 x 9.07 [508 x 508 x 230]	PDF	SCE-20P20	\$55.00
SCE-20H2010LP	\$391.00	20.00 x 20.00 x 11.07 [508 x 508 x 281]	PDF	SCE-20P20	\$55.00

Note: Dimensions in inches [millimeters].

Table continued on next page

NEMA 3R, 4, 12, and 13 Padlocking Single-Door Wall-Mount

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.



Your Enclosure Source®

Table continued from previous page.

NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount					
Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-20H2406LP	\$378.00	20.00 x 24.00 x 7.07 [508 x 610 x 180]	PDF	SCE-24P20	\$71.00
SCE-20H2408LP	\$400.00	20.00 x 24.00 x 9.07 [508 x 610 x 230]	PDF	SCE-24P20	\$71.00
SCE-20H3006LP	\$454.00	20.00 x 30.00 x 7.07 [508 x 762 x 180]	PDF	SCE-30P20	\$87.00
SCE-24H1206LP	\$317.00	24.00 x 12.00 x 7.07 [610 x 305 x 180]	PDF	SCE-12P24	\$43.50
SCE-24H1208LP	\$337.00	24.00 x 12.00 x 9.07 [610 x 305 x 230]	PDF	SCE-12P24	\$43.50
SCE-24H1210LP	\$354.00	24.00 x 12.00 x 11.07 [610 x 305 x 281]	PDF	SCE-12P24	\$43.50
SCE-24H1606LP	\$347.00	24.00 x 16.00 x 7.07 [610 x 406 x 180]	PDF	SCE-24P16	\$51.00
SCE-24H1608LP	\$368.00	24.00 x 16.00 x 9.07 [610 x 406 x 230]	PDF	SCE-24P16	\$51.00
SCE-24H2006LP	\$378.00	24.00 x 20.00 x 7.07 [610 x 508 x 180]	PDF	SCE-24P20	\$71.00
SCE-24H2008LP	\$401.00	24.00 x 20.00 x 9.07 [610 x 508 x 230]	PDF	SCE-24P20	\$71.00
SCE-24H2010LP	\$421.00	24.00 x 20.00 x 11.07 [610 x 508 x 281]	PDF	SCE-24P20	\$71.00
SCE-24H2012LP	\$444.00	24.00 x 20.00 x 13.07 [610 x 508 x 332]	PDF	SCE-24P20	\$71.00
SCE-24H2016LP	\$625.00	24.00 x 20.00 x 17.07 [610 x 508 x 434]	PDF	SCE-24P20	\$71.00
SCE-24H2406LP	\$408.00	24.00 x 24.00 x 7.07 [610 x 610 x 180]	PDF	SCE-24P24	\$83.00
SCE-24H2408LP	\$431.00	24.00 x 24.00 x 9.07 [610 x 610 x 230]	PDF	SCE-24P24	\$83.00
SCE-24H2410LP	\$454.00	24.00 x 24.00 x 11.07 [610 x 610 x 281]	PDF	SCE-24P24	\$83.00
SCE-24H2412LP	\$478.00	24.00 x 24.00 x 13.07 [610 x 610 x 332]	PDF	SCE-24P24	\$83.00
SCE-24H2416LP	\$651.00	24.00 x 24.00 x 17.07 [610 x 610 x 434]	PDF	SCE-24P24	\$83.00
SCE-24H3008LP	\$618.00	24.00 x 30.00 x 9.07 [610 x 762 x 230]	PDF	SCE-30P24	\$98.00
SCE-30H1606LP	\$381.00	30.00 x 16.00 x 7.07 [762 x 406 x 180]	PDF	SCE-30P16	\$71.00
SCE-30H2006LP	\$414.00	30.00 x 20.00 x 7.07 [762 x 508 x 180]	PDF	SCE-30P20	\$87.00
SCE-30H2008LP	\$441.00	30.00 x 20.00 x 9.07 [762 x 508 x 230]	PDF	SCE-30P20	\$87.00
SCE-30H2010LP	\$464.00	30.00 x 20.00 x 11.07 [762 x 508 x 281]	PDF	SCE-30P20	\$87.00
SCE-30H2406LP	\$599.00	30.00 x 24.00 x 7.07 [762 x 610 x 180]	PDF	SCE-30P24	\$98.00
SCE-30H2408LP	\$618.00	30.00 x 24.00 x 9.07 [762 x 610 x 230]	PDF	SCE-30P24	\$98.00
SCE-30H2410LP	\$637.00	30.00 x 24.00 x 11.07 [762 x 610 x 281]	PDF	SCE-30P24	\$98.00
SCE-30H2412LP	\$656.00	30.00 x 24.00 x 13.07 [762 x 610 x 332]	PDF	SCE-30P24	\$98.00
SCE-30H2416LP	\$694.00	30.00 x 24.00 x 17.07 [762 x 610 x 434]	PDF	SCE-30P24	\$98.00
SCE-30H2420LP	\$732.00	30.00 x 24.00 x 21.07 [762 x 610 x 535]	PDF	SCE-30P24	\$98.00
SCE-30H2424LP	\$770.00	30.00 x 24.00 x 25.07 [762 x 610 x 637]	PDF	SCE-30P24	\$98.00
SCE-30H3008LP	\$658.00	30.00 x 30.00 x 9.07 [762 x 762 x 230]	PDF	SCE-30P30	\$130.00
SCE-30H3012LP	\$701.00	30.00 x 30.00 x 13.07 [762 x 762 x 332]	PDF	SCE-30P30	\$130.00
SCE-30H3608LP	\$698.00	30.00 x 36.00 x 9.07 [762 x 914 x 230]	PDF	SCE-36P30	\$157.00
SCE-36H1606LP	\$565.00	36.00 x 16.00 x 7.07 [914 x 406 x 180]	PDF	SCE-36P16	\$83.00
SCE-36H2406LP	\$629.00	36.00 x 24.00 x 7.07 [914 x 610 x 180]	PDF	SCE-36P24	\$118.00
SCE-36H2408LP	\$651.00	36.00 x 24.00 x 9.07 [914 x 610 x 230]	PDF	SCE-36P24	\$118.00
SCE-36H2410LP	\$672.00	36.00 x 24.00 x 11.07 [914 x 610 x 281]	PDF	SCE-36P24	\$118.00
SCE-36H2412LP	\$694.00	36.00 x 24.00 x 13.07 [914 x 610 x 332]	PDF	SCE-36P24	\$118.00
SCE-36H2416LP	\$741.00	36.00 x 24.00 x 17.07 [914 x 610 x 434]	PDF	SCE-36P24	\$118.00
SCE-36H3006LP	Retired	36.00 x 30.00 x 7.07 [914 x 762 x 180]	PDF	SCE-36P30	\$157.00

Note: Dimensions in inches [millimeters].

Table continued on next page

NEMA 3R, 4, 12, and 13 Padlocking Single-Door Wall-Mount

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.



Your Enclosure Source®

Table continued from previous page.

NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount					
Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-36H3008LP	\$698.00	36.00 x 30.00 x 9.07 [914 x 762 x 230]	PDF	SCE-36P30	\$157.00
SCE-36H3010LP	\$722.00	36.00 x 30.00 x 11.07 [914 x 762 x 281]	PDF	SCE-36P30	\$157.00
SCE-36H3012LP	\$743.00	36.00 x 30.00 x 13.07 [914 x 762 x 332]	PDF	SCE-36P30	\$157.00
SCE-36H3016LP	\$791.00	36.00 x 30.00 x 17.07 [914 x 762 x 434]	PDF	SCE-36P30	\$157.00
SCE-36H3020LP	\$836.00	36.00 x 30.00 x 21.07 [914 x 762 x 535]	PDF	SCE-36P30	\$157.00
SCE-36H3608LP	\$743.00	36.00 x 36.00 x 9.07 [914 x 914 x 230]	PDF	SCE-36P36	\$185.00
SCE-36H3612LP	\$796.00	36.00 x 36.00 x 13.07 [914 x 914 x 332]	PDF	SCE-36P36	\$185.00
SCE-36H3616LP	\$846.00	36.00 x 36.00 x 17.07 [914 x 914 x 434]	PDF	SCE-36P36	\$185.00
SCE-42H2408LP	\$686.00	42.00 x 24.00 x 9.07 [1067 x 610 x 230]	PDF	SCE-42P24	\$142.00
SCE-42H3008LP	\$739.00	42.00 x 30.00 x 9.07 [1067 x 762 x 230]	PDF	SCE-42P30	\$181.00
SCE-42H3010LP	\$762.00	42.00 x 30.00 x 11.07 [1067 x 762 x 281]	PDF	SCE-42P30	\$181.00
SCE-42H3012LP	\$789.00	42.00 x 30.00 x 13.07 [1067 x 762 x 332]	PDF	SCE-42P30	\$181.00
SCE-42H3016LP	\$841.00	42.00 x 30.00 x 17.07 [1067 x 762 x 434]	PDF	SCE-42P30	\$181.00
SCE-42H3608LP	\$791.00	42.00 x 36.00 x 9.07 [1067 x 914 x 230]	PDF	SCE-42P36	\$213.00
SCE-42H3610LP	\$817.00	42.00 x 36.00 x 11.07 [1067 x 914 x 281]	PDF	SCE-42P36	\$213.00
SCE-42H3612LP	\$846.00	42.00 x 36.00 x 13.07 [1067 x 914 x 332]	PDF	SCE-42P36	\$213.00
SCE-42H3616LP	\$900.00	42.00 x 36.00 x 17.07 [1067 x 914 x 434]	PDF	SCE-42P36	\$213.00
SCE-48H2408LP	\$720.00	48.00 x 24.00 x 9.07 [1219 x 610 x 230]	PDF	SCE-48P24	\$154.00
SCE-48H3008LP	\$779.00	48.00 x 30.00 x 9.07 [1219 x 762 x 230]	PDF	SCE-48P30	\$201.00
SCE-48H3010LP	\$805.00	48.00 x 30.00 x 11.07 [1219 x 762 x 281]	PDF	SCE-48P30	\$201.00
SCE-48H3016LP	\$888.00	48.00 x 30.00 x 17.07 [1219 x 762 x 434]	PDF	SCE-48P30	\$201.00
SCE-48H3608LP	\$836.00	48.00 x 36.00 x 9.07 [1219 x 914 x 230]	PDF	SCE-48P36	\$240.00
SCE-48H3610LP	\$867.00	48.00 x 36.00 x 11.07 [1219 x 914 x 281]	PDF	SCE-48P36	\$240.00
SCE-48H3612LP	\$895.00	48.00 x 36.00 x 13.07 [1219 x 914 x 332]	PDF	SCE-48P36	\$240.00
SCE-48H3616LP	\$955.00	48.00 x 36.00 x 17.07 [1219 x 914 x 434]	PDF	SCE-48P36	\$240.00
SCE-48H3620LP	\$1,036.00	48.00 x 36.00 x 21.07 [1219 x 914 x 535]	PDF	SCE-48P36	\$240.00
SCE-60H3608LP	\$929.00	60.00 x 36.00 x 9.07 [1524 x 914 x 230]	PDF	SCE-60P36	\$295.00
SCE-60H3610LP	\$966.00	60.00 x 36.00 x 11.07 [1524 x 914 x 281]	PDF	SCE-60P36	\$295.00
SCE-60H3612LP	\$1,012.00	60.00 x 36.00 x 13.07 [1524 x 914 x 332]	PDF	SCE-60P36	\$295.00
SCE-60H3616LP	\$1,106.00	60.00 x 36.00 x 17.07 [1524 x 914 x 434]	PDF	SCE-60P36	\$295.00
SCE-60H3620LP	\$1,203.00	60.00 x 36.00 x 21.07 [1524 x 914 x 535]	PDF	SCE-60P36	\$295.00
SCE-72H3012LP	\$1,082.00	72.00 x 30.00 x 13.07 [1829 x 762 x 332]	PDF	SCE-72P30	\$327.00
SCE-72H3016LP	\$1,238.00	72.00 x 30.00 x 17.07 [1829 x 762 x 434]	PDF	SCE-72P30	\$327.00
SCE-72H3024LP	\$1,360.00	72.00 x 30.00 x 25.07 [1829 x 762 x 637]	PDF	SCE-72P30	\$327.00
SCE-72H3612LP	\$1,156.00	72.00 x 36.00 x 13.07 [1829 x 914 x 332]	PDF	SCE-72P36	\$350.00
SCE-72H3616LP	\$1,313.00	72.00 x 36.00 x 17.07 [1829 x 914 x 434]	PDF	SCE-72P36	\$350.00

Note: Dimensions in inches [millimeters].

NEMA 3R, 4, 12, and 13 Padlocking Single-Door Wall-Mount



Dimensions

