

NEMA 3R, 12, and 13 Double-Door Wall-Mount



Applications

Designed to house electrical and electronic controls, instrumentation and components. Provides protection from dust, oil and water. For outdoor applications a drip shield is recommended.

Construction

- 14-gauge carbon steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Gasketed overlapping doors eliminate need for a center post
- Black zinc diecast keylocking/padlocking handle
- 3-point latching mechanism
- Latch rods have ramp shoes for easier door closing.
- Concealed hinges
- Removable and interchangeable doors
- A removable print pocket is provided on door with 3-point latch.
- Poured-in-place oil- and water-resistant gasket
- Collar studs for mounting optional subpanel
- Ground studs on door and body
- Mounting hardware, sealing washers, and hole plugs are included.

Options

- Optional mounting feet are available (SCE-ELMFK4).

Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 12, and 13
- cULus Listed Type 3R and 12 [File E69392]
- IEC 60529 IP55



NEMA 3R, 12, and 13 Double-Door Wall-Mount



Your Enclosure Source®

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

NEMA 3R, 12, and 13 Double-Door Wall-Mount

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-244208WFLP	\$700.00	24.00 x 42.00 x 9.10 [610 x 1067 x 231]	PDF	SCE-42P24	\$127.00
SCE-244212WFLP	\$772.00	24.00 x 42.00 x 13.10 [610 x 1067 x 333]	PDF	SCE-42P24	\$127.00
SCE-244808WFLP	\$759.00	24.00 x 48.00 x 9.10 [610 x 1219 x 231]	PDF	SCE-48P24	\$137.00
SCE-244812WFLP	\$811.00	24.00 x 48.00 x 13.10 [610 x 1219 x 333]	PDF	SCE-48P24	\$137.00
SCE-304210WFLP	\$838.00	30.00 x 42.00 x 11.10 [762 x 1067 x 282]	PDF	SCE-42P30	\$162.00
SCE-304810WFLP	\$910.00	30.00 x 48.00 x 11.10 [762 x 1219 x 282]	PDF	SCE-48P30	\$179.00
SCE-306010WFLP	\$1,054.00	30.00 x 60.00 x 11.10 [762 x 1524 x 282]	PDF	SCE-60P30	\$221.00
SCE-306012WFLP	\$1,135.00	30.00 x 60.00 x 13.10 [762 x 1524 x 333]	PDF	SCE-60P30	\$221.00
SCE-364212WFLP	\$975.00	36.00 x 42.00 x 13.10 [914 x 1067 x 333]	PDF	SCE-42P36	\$190.00
SCE-364216WFLP	\$1,061.00	36.00 x 42.00 x 17.10 [914 x 1067 x 434]	PDF	SCE-42P36	\$190.00
SCE-364810WFLP	\$1,047.00	36.00 x 48.00 x 11.10 [914 x 1219 x 282]	PDF	SCE-48P36	\$214.00
SCE-364812WFLP	\$1,064.00	36.00 x 48.00 x 13.10 [914 x 1219 x 333]	PDF	SCE-48P36	\$214.00
SCE-364816WFLP	\$1,162.00	36.00 x 48.00 x 17.10 [914 x 1219 x 434]	PDF	SCE-48P36	\$214.00
SCE-366012WFLP	\$1,240.00	36.00 x 60.00 x 13.10 [914 x 1524 x 333]	PDF	SCE-60P36	\$264.00
SCE-366016WFLP	\$1,382.00	36.00 x 60.00 x 17.10 [914 x 1524 x 434]	PDF	SCE-60P36	\$264.00
SCE-424212WFLP	\$1,077.00	42.00 x 42.00 x 13.10 [1067 x 1067 x 333]	PDF	SCE-42P42	\$218.00
SCE-424216WFLP	\$1,223.00	42.00 x 42.00 x 17.10 [1067 x 1067 x 434]	PDF	SCE-42P42	\$218.00
SCE-424812WFLP	\$1,175.00	42.00 x 48.00 x 13.10 [1067 x 1219 x 333]	PDF	SCE-48P42	\$246.00
SCE-424816WFLP	\$1,318.00	42.00 x 48.00 x 17.10 [1067 x 1219 x 434]	PDF	SCE-48P42	\$246.00
SCE-426012WFALP	\$1,371.00	42.00 x 60.00 x 13.10 [1067 x 1524 x 333]	PDF	SCE-60BFP42	\$320.00
SCE-426016WFALP	\$1,572.00	42.00 x 60.00 x 17.10 [1067 x 1524 x 434]	PDF	SCE-60BFP42	\$320.00
SCE-484812WFLP	\$1,283.00	48.00 x 48.00 x 13.10 [1219 x 1219 x 333]	PDF	SCE-48P48	\$295.00
SCE-484816WFLP	\$1,500.00	48.00 x 48.00 x 17.10 [1219 x 1219 x 434]	PDF	SCE-48P48	\$295.00

Note: Dimensions in inches [millimeters].